

General description

This document describes a switch mode power supply unit (AC/DC converter). The unit is designed as wall plug device. It is available with a plug for Europe, US (Japan, Canada) and UK with a wide range input voltage (100 - 264V AC). Other plugtypes can be tooled on request. The output voltage is fixed with a tolerance of $\pm 3\%$. Output voltages are available between 9V and 24V DC. Secondary cable connection to power supply is available fixed or pluggable. Secondary plug is available in different forms. The power supply is for indoor use only.

The standard power supply is meant for use with medical applications.

Features

- § Wide Input Range (100-264V)
- § Output voltage fixed
- § Output voltage stability $\pm 3\%$
- § Output power 24W
- § High efficiency, typically 80%
- § Protection Class II
- § Europe, UK, US Plug available
- § Europe and US housing have folding plugs
- § Secondary plug customer specific
- § Manufacturing according to ISO 9001
- § Smallest available size



Applications

- § Electronic organiser (PDA)
- § Mobile phones (Travel charger)
- § Computer Accessories (Modem, Scanner)
- § Personal entertainment (CD-Player, MD)
- § Consumer electronic (camera, calculator)
- § Medical applications (Fusion pump)
- § Measuring Equipment

Approvals

- § CE
- § ÖVE (CCA)
- § cUL 1310

Test standards

- § EN 50 075, IEC 83
- § EN 50 081-1
- § EN 50 082-1
- § EN 55 022
- § EN 60 950

Copyright © 1999 EGSTON GmbH.
All Rights Reserved

Revision history of this document

Actual Revision: 07/2001
Previous Revision: none

Page of	Page of	Changes since last release
---------	---------	----------------------------



EGSTON POWER SUPPLY

N2xxSW 24W

actual Rev.	prev. Rev.	
		Contact Adress

Table of Contents

1	CERTIFICATIONS	4
1.1	AREA SPECIFIC APPROVALS	4
1.2	TESTS	4
2	TECHNICAL INPUT SPECIFICATION	5
2.1	INPUT PARAMETERS	5
3	TECHNICAL OUTPUT SPECIFICATION	5
3.1	OUTPUT PARAMETERS	5
3.2	TYPICAL OUTPUT CHARACTERISTIC	6
3.3	TYPICAL EFFICIENCY CHARACTERISTIC	6
3.4	OUTPUT VOLTAGE TRANSIENTS	7
3.5	OUTPUT RIPPLE VOLTAGE	7
4	ELECTROMAGNETIC SPECIFICATION	8
4.1	ELECTROMAGNETIC CHARACTERISTIC	8
4.2	IMMUNITY TO FAST TRANSIENTS (BURST)	9
4.3	IMMUNITY TO RADIATED ELECTROMAGNETIC FIELD	9
4.4	SURGE CAPABILITY	9
5	ENVIRONMENTAL CONDITION	9
5.1	TEMPERATURE RANGE	9
5.2	HUMIDITY	9
6	MECHANICAL PARAMETERS	10
6.1	HOUSING	10
6.2	WEIGHT	11
6.3	TYPICAL MARKING	11
6.4	SECONDARY CABLE AND PLUG	12
7	ORDERING INFORMATION	13
7.1	GENERIC PRODUCT CODE	13
7.2	PACKAGING	14
7.2.1	Cardboard box	14
7.2.2	Bulk packaging	14
7.3	SALES OFFICE	FEHLER! TEXTMARKE NICHT DEFINIERT.

1 Certifications

1.1 Area specific approvals

- CE
- ÖVE (CCA) Austrian approval
- cUL 1310 Class 2 power units

1.2 Tests

- EN 50 075, IEC 83 Flat non-wireable two-pole plugs
- EN 50 081-1 EMC generic emission standard
- EN 50 082-1 EMC generic immunity standard
- EN 55 022 Limits and methods of measurements of radio interference
- EN 60 950 Safety of information technology equipment

In addition the following testapprovals are in process:

- IEC 68-2-1, Test Ab Cold test: -10°C, 0% .. 10% R.H., 96 hours, power supply full load
- IEC 68-2-2, Test Bb Dry heat: +40°C, 0% .. 10% R.H., 96 hours, power supply full load
- IEC 68-2-14, Test Na Rapid temperature changes: from -10°C to +40°C, 30 times, Time period 1 hour, Temperature change time <5sec, 0% .. 10% R.H., power supply full load
- IEC 68-2-30, Test Cb Damp heat test: 40°C, 90% .. 95% R.H., 48 hours
- IEC 68-2-32, Test Ed Free fall: 1m
- IEC 68-2-6, Test Fc Vibrations: 3 times in each direction
amplitude 0.8 mmp-p, frequency 10Hz .. 30Hz, 5 minutes
amplitude 0.4 mmp-p, frequency 30Hz .. 60Hz, 5 minutes

2 Technical Input Specification

2.1 Input Parameters

Table 1

Input parameters for power supplies with wide input voltage range

Parameter	Key	Min	Tvn	Max	Unit	Condition
Input voltage	U_1	100		264	V	Full load
Input current	I_1	5		500	mA	
Input frequency	f_1	47	50	63	Hz	
Efficiency	η	65	80	90	%	With load
Switching frequency	$f_{1,sw}$	35		250	kHz	

3 Technical Output Specification

3.1 Output Parameters

Table 2

Output parameters for power supplies with different fixed output voltages

Idle mode		Short circuit		Full load (resistive load)		
U_2	P_1	U_2	I_2	U_2	I_2	P_2
[V]	[W]	[V]	[A]	[V]	[A]	[W]
9.0	<2.5	<1	<3.0	9.0	2.66	24
12.0	<2.5	<1	<2.4	12.0	2.0	24
15.0	<2.5	<1	<2.0	15.0	1.6	24
18.0	<2.5	<1	<1.6	18.0	1.33	24
24.0	<2.5	<1	<1.3	24.0	1.0	24

Table 3

Output parameters for power supplies

Parameter	Key	Min	Tvn	Max	Unit	Condition
Ripple voltage at switching freq	$U_{D-D, hf}$		75	150	mV	Full load
Reverse current $U_2=15V$	I_r		2.5	5	mA	Disconnected from mains

3.2 Typical Output Characteristic




Figure 1
Output Characteristic: $U_1=230V$; $f_1=50$ Hz; resistive load

3.3 Typical Efficiency Characteristic




Figure 2
Typical Efficiency characteristic: $U_1=230V$; $f_1=50$ Hz; resistive load
Egston Power Supply N2GFSW 24W 15V representative sample

3.4 Output Voltage Transients




Figure 3
Output voltage transients
Egston Power Supply N2GFSW 24W 15V representative sample,
10% to 100% resistive load change at 1kHz

3.5 Output Ripple Voltage




Figure 4
Output ripple voltage
Egston Power Supply N2GFSW 24W 15V representative sample

4 Electromagnetic Specification

4.1 Electromagnetic Characteristic

Test according to EN 55 022 class B passed.




Figure 5
Electromagnetic characteristics (Peak and average measurement, conducted EMC)
Egston Power Supply N2GFSW 24W 15V representative sample

4.2 Immunity to fast Transients (Burst)

According to EN 61 000 -4 -4 1kV passed.

4.3 Immunity to Radiated Electromagnetic Field

According to EN 61 000 -4 -3 10V/m passed.

4.4 Surge Capability

According to EN 61 000 -4 -5 1kV passed.

5 Environmental Condition

5.1 Temperature Range

Table 4
Temperature ranges for storage and operation

	Min	Max	Unit
Storage Temperature	-30	80	°C
	-22	176	°F
Operation Temperature	0	40	°C
	32	104	°F

5.2 Humidity

Maximum 95% without condensation

6 Mechanical Parameters

6.1 Housing

Plastic Housing Material: ABS/PC blend (UL 94 V0)
Colour: Black




Figure 6
Dimensions in mm
Euro and US housing have folding plugs

6.2 Weight

Table 5

Weight of power supply without cable and secondary plug

Version	Weight (n)	Weight (n2)
Euro-, US-, UK-Housing	115	4.0

6.3 Typical Marking

On power supply unit:



Figure 7

Example of Label on plastic housing by laser marking

Marking on power supply unit is possible according to customer requirements. Further markings like approval logos (CE, ÖVE, UL) and company name (EGSTON) are directly moulded onto plastic material of housing.

6.4 Secondary Cable and Plug

A fixed or plugable cable to the power supply can be chosen. Refer to the Product Code in the ordering information section of this document.

Table 6
Cable length

	Length	Unit
Standard cable	1.5	m
Maximum length to pass specifications	3	m

We offer a universal plug set with 5 different types. Other plugs available.




Figure 8
Universal plug set

The polarity of the universal plugs can be set by the user.

7 Ordering Information

7.1 Generic Product Code

N	2	E	F	S	[W]	1	6V	1000mA	
									OUTPUT CURRENT
									OUTPUT VOLTAGE
									OUTPUT STABILITY
									1 ± 1%
									3 ± 3%
									INPUT RANGE (optional)
									W Wide input range (90-264V)
									APPLICATION
									S Standard
									M Medical
									T Telecom version for grounded appliances
									CABLE CONNECTION
									S Cable pluggable
									F Cable fix
									PLUG
									E Euro plug
									U US/Japan, Canada Plug
									G United Kingdom Plug
									P PCB design
									DESIGN, OPERATION TEMPERATURE RANGE
									1 SMPS, -20 .. 50°C
									2 SMPS, 0 .. 40°C
									SUPPLY TYPE
									N Egston Power Supply

Table 7
Product code

7.2 Packaging

7.2.1 Cardboard box

The power supply (with cable, secondary plug and manual) is available in a cardboard box with Egston-design or user-specific-design. Marking on the cardboard can be provided on a printed label, according customer requirements. 50 cardboard boxes are packed in one outer box.

Table 8
Dimensions of cardboard box

Version	Length	Width	Height	Unit
Euro-, US-, UK-housing	100	110	72	mm

7.2.2 Bulk packaging

The Euro-, US- and UK-units (without individual cardboard box) can be delivered in bulk packaging in lots of 50 pieces / package.

Table 9
Weight per package

Version	Weight	Weight (oz)
Euro-, US-, UK-housing	~10	~350



EGSTON POWER SUPPLY N2xxSW 24W

7.3 For more information or a commercial quote please contact:



Grafenbergerstraße 37
A-3730 Eggenburg, Austria
<http://www.egston.com>

Tel: (+43) 2984/2226-0
Fax: (+43) 2984/2226-61
E-Mail: info@egston.com

or your nearest distributor (for details please check our website:
www.egston.com)