



LOC	DIST	P	F	REVISIONS			
				ZONE	LTR	DESCRIPTION	DATE
FT	38				C	REDRAWN WITHOUT CHANGE	09-14-93
					D	REV PER EC 0020-186-96	28 JUN 96
					E	REV PER EC 0320-385-97	19 NOV 97



- 1 SCREW: CARBON STEEL.
MOUNTING SCREW & HEX NUT: CARBON STEEL PER ASTM A108.
CABLE CLAMP: ZINC.
- 2 SCREW: ZINC PLATED.
MOUNTING SCREW & HEX NUT: 5.08µm [.000200] MIN ZINC PER,
ASTM B633 TYPE III, CLASS SCI, CLEAR CHROMATE.
CABLE CLAMP: 5.08µm [.000200] MIN NICKEL PER QQ-N-290
OVER 5.08µm [.000200] MIN COPPER PER MIL-C-14550.

I	9.53 [.375]	745175-6
L	11.43 [.450]	745175-5
O	13.34 [.525]	745175-4
S	15.24 [.600]	745175-3
U	17.15 [.675]	745175-2
V	19.05 [.750]	745175-1
NECK SIZE I.D.		CABLE DIA
		PART NO

		NECK SIZE I.D.		CABLE DIA		PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± .013 [.005] 3 PLC DEC ± - ANGLES ± - MATERIAL 1 -		DR 09-15-93 D.BROCKWAY		AMP AMP Incorporated Harrisburg, PA 17105-3608 NAME CABLE CLAMP KIT, UNASSEMBLED SIZE 5, 50 POSN, 180° AMPLIMITE™			
		CHK 09-17-93 B.LENKER					
		APPD 09-17-93 S.BRINSER					
FINISH 2 -		APPD 09-17-93 S.BRINSER					
		PRODUCT SPEC -					
		APPLICATION SPEC -		SIZE C	CAGE CODE 00779	DRAWING NO C-745175	
		WEIGHT -		SCALE 2:1		SHEET 1 OF 1	

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.