


HEX40-AB-00-25-A17-1 Product Details

 [Share](#) |
  [Print](#) |
  [Email](#)



HEX40-AB-00-25-A17-1

TE Internal Number: 684778-000
 [Active](#)

HexaShield Adapters and Ferrule Kits

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- Connector Code = 40
- Aluminum Alloy Material
- Cadmium Plating over Electroless Nickel Finish
- Straight
- Shell Size = 25, J

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) |
  [Request Sample](#) |
  [Find Similar Products](#) |
  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [HexaShield Adaptor for Code 40 Connectors, Plain Cla...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Material](#) = Aluminum Alloy
- [Finish](#) = Cadmium Plating over Electroless Nickel
- [Angle](#) = Straight
- [Shell Size](#) = 25, J
- Color = Olive Drab

Electrical Characteristics:

- [Number of Ferrules](#) = 17
- [Overbraid Termination](#) = No Overbraid
- Star Style = Split and Standard
- Recommended Boot = 202K185-25-G03-0

Body Features:

- [Connector Code](#) = 40
- [Length of Adapter](#) = Standard

Configuration Features:

- Braid = None
- Number of 22 AWG Shielded Pairs, Max. = 68
- Number of 20 AWG Shielded Pairs, Max. = 51

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

Conditions for Usage:

- Salt Spray Resistance (Hr) = 500

Other:

- Brand = Raychem

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address 

