


Military Fuseholders

Panel Mount


FHN42W
HWA-AF



Dimensional Data



MOUNTING HOLE $\pm 0.002"$
(0.5mm)



CATALOG SYMBOL: FHN42W
PANEL MOUNT
MEETS MILITARY SPECIFICATION - MIL-F-19207/26
NO AGENCY LISTINGS
FOR MILITARY FUSES: FM01 SERIES
COMMERCIAL EQUIVALENT: HWA-AF
SUB-MINIATURE FOR LIMITED SPACE APPLICATIONS

Specifications

Knob	Screw type.
Terminals	Solder lug type.
Enclosure	Watertight.
Panel Thickness	0.125 Max.
Rating	5 amperes. 125 volts.
Body and Knob	MAI-60 or MIL-M-14
Material	Grey Diallyl Phthalate.
Temperature Rise	45°C Max.
Fuses	Per MIL-23419/1 FM01.
Qualified and tested per MIL-F-19207. Group A, B and C.	
Mechanical	MIL-STD-202. Method 207. Method I.
Shock	
Torque Capacity	4 lbs.-inches.
Mounting Torque	10 lbs.-inches.

The only controlled copy of this BIF document is the electronic read-only version located on the Bussmann Network Drive. All other copies of this BIF document are by definition uncontrolled. This bulletin is intended to clearly present comprehensive product data and provide technical information that will help the end user with design applications. Bussmann reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Bussmann also reserves the right to change or update, without notice, any technical information contained in this bulletin. Once a product has been selected, it should be tested by the user in all possible applications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cooper Bussmann:](#)

[FHN42W](#) [BK/FHN42W](#)