


ALPHANUMERIC INDEX — CROSS-REFERENCE (Continued)

Industry Part Number	Motorola Direct Replacement	Motorola Similar Replacement	Page Number	Industry Part Number	Motorola Direct Replacement	Motorola Similar Replacement	Page Number
2N3790	2N3790		3-56	2N4311		2N5337	3-97
2N3791	2N3791		3-56	2N4314		2N3868	3-32
2N3791JAN	2N3791JAN		3-56	2N4347		2N3055A	3-9
2N3791JTX	2N3791JTX		3-56	2N4348		2N5630	3-105
2N3791JTXV	2N3791JTXV		3-56	2N4387		2N3740	3-41
2N3792	2N3792		3-56	2N4388		2N3740	3-41
2N3792JAN	2N3792JAN		3-56	2N4398	2N4398		3-68
2N3792JTX	2N3792JTX		3-56	2N4399	2N4399		3-68
2N3792JTXV	2N3792JTXV		3-56	2N4399JAN	2N4399JAN		3-68
2N3863		2N3715	3-26	2N4399JTX	2N4399JTX		3-68
2N3864		2N5882	3-123	2N4399JTXV	2N4399JTXV		3-68
2N3865		MJ15001	3-710	2N4877		2N5337	3-97
2N3867	2N3867		3-32	2N4898		2N3741	3-41
2N3867JAN		2N3867SJAN	3-32	2N4899		2N3741	3-41
2N3867JTX		2N3867SJTX	3-32	2N4900		2N3741	3-41
2N3867JTXV		2N3867SJTXV	3-32	2N4901		MJ15016	3-9
2N3867SJAN	2N3867SJAN		3-32	2N4902		MJ15016	3-9
2N3867SJTX	2N3867SJTX		3-32	2N4903		MJ15016	3-9
2N3867SJTXV	2N3867SJTXV		3-32	2N4904		MJ15016	3-9
2N3868	2N3868		3-32	2N4905		MJ15016	3-9
2N3868JAN		2N3868SJAN	3-32	2N4906		MJ15016	3-9
2N3868JTX		2N3868SJTX	3-32	2N4907		2N3791	3-56
2N3868JTXV		2N3868SJTXV	3-32	2N4908		2N3791	3-56
2N3868SJAN	2N3868SJAN		3-32	2N4909		2N3792	3-56
2N3868SJTX	2N3868SJTX		3-32	2N4910		2N3054	3-2
2N3868SJTXV	2N3868SJTXV		3-32	2N4911		2N3054	3-2
2N3878		2N5428	3-101	2N4912	2N4912		3-72
2N3879		2N5430	3-101	2N4913		2N5758	3-116
2N3902	2N3902		3-60	2N4914		2N5758	3-116
2N3996		2N5339	3-97	2N4915		2N5758	3-116
2N3997		2N5339	3-97	2N4918	2N4918		3-75
2N3998		2N5339	3-97	2N4919	2N4919		3-75
2N3999		2N5339	3-97	2N4920	2N4920		3-75
2N4000		2N5339	3-97	2N4921	2N4921		3-79
2N4001		2N5339	3-97	2N4922	2N4922		3-79
2N4002		2N6274	3-168	2N4923	2N4923		3-79
2N4032		2N6274	3-168	2N4998		2N5339	3-97
2N4070		2N6306	3-181	2N4999		2N6191	3-158
2N4071		2N6306	3-181	2N5000		2N5339	3-97
2N4111		2N3715	3-26	2N5001		2N6191	3-158
2N4113		2N3716	3-26	2N5002		2N5339	3-97
2N4115		2N5339	3-97	2N5003		2N6191	3-158
2N4116		2N5339	3-97	2N5004		2N5339	3-97
2N4150		2N5337	3-97	2N5005		2N6191	3-158
2N4150JAN		2N5337JAN	3-97	2N5034		2N3055	3-6
2N4150JTX		2N5337JTX	3-97	2N5035		2N3055	3-6
2N4150JTXV		2N5337JTXV	3-97	2N5036		2N3055	3-6
2N4231A		2N3054A	3-2	2N5037		2N3055	3-6
2N4232A		2N3054A	3-2	2N5038	2N5038		3-83
2N4233A	2N4233A		3-64	2N5038JAN	2N5038JAN		3-83
2N4240	2N4240		3-20	2N5038JTX	2N5038JTX		3-83
2N4296		2N3738	3-37	2N5038JTXV	2N5038JTXV		3-83
2N4297		2N3738	3-37	2N5039	2N5039		3-83
2N4298		2N3585	3-20	2N5039JAN	2N5039JAN		3-83
2N4299		2N3585	3-20	2N5039JTX	2N5039JTX		3-83
2N4300		2N5337	3-97	2N5039JTXV	2N5039JTXV		3-83
2N4301		2N5337	3-97	2N5050		2N3584	3-20
2N4305		2N5337	3-97	2N5051		2N3584	3-20
2N4307		2N5337	3-97	2N5052		2N3584	3-20
2N4309		2N5339	3-97	2N5067		2N5758	3-116

*Consult Motorola if a direct replacement is necessary.

TABLE 7 — PLASTIC TO-225 Type (Formerly TO-126 Type)

STYLE 1:
PIN 1. EMITTER
2. COLLECTOR
3. BASE



STYLE 3:
PIN 1. BASE
2. COLLECTOR
3. EMITTER

CASE 77-06

I _C Cont Amps Max	V _{CEO(sus)} Volts Min	Device Type		h _{FE} Min/Max	@ I _C Amp	Resistive Switching			f _T MHz Min	P _D (Case) Watts @ 25°C
		NPN	PNP			t _s μs Max	t _f μs Max	@ I _C Amp		
0.3	250	MJE3440		40/160	0.02				15	15
	350	MJE3439		40/160	0.02				15	15
0.5	150	MJE341		25/200	0.05				15	20.8
	200	MJE344		30/300	0.05				15	20.8
	250	2N5655 BD157		30/250 30/240	0.1 0.05	3.5 typ	0.24 typ	0.1	10	20 20
	300	BD158 BD232 MJE340 2N5656	MJE350	30/240 20 min 30/240 30/250	0.05 0.15 0.05 0.1	3.5 typ	0.24 typ	0.1	10	20 20 20.8 20
	350	2N5657 BD159		30/250 30/240	0.1 0.05	3.5 typ	0.24 typ	0.1	10	20 20
1	40	2N4921	2N4918	20/100	0.5	0.6 typ	0.3 typ	0.5	3	30
	60	2N4922	2N4919	20/100	0.5	0.6 typ	0.3 typ	0.5	3	30
	80	2N4923	2N4920	20/100	0.5	0.6 typ	0.3 typ	0.5	3	30
1.5	45	BD165 BD135 BD135.6 BD135.10 BD135.16	BD166 BD136 BD136.6 BD136.10 BD136.16	15 min 40/250 40/100 63/160 100/250	0.5 0.15 0.15 0.15 0.15				6	20 12.5 12.5 12.5 12.5
	60	BD167 BD137 BD137.6 BD137.10 BD137.16	BD138 BD138.6 BD138.10 BD138.16	15 min 40/250 40/100 63/160 100/250	0.5 0.15 0.15 0.15 0.15				6	20 12.5 12.5 12.5 12.5
	80	BD169 BD139 BD139.6 BD139.10 BD139.16	BD140 BD140.6 BD140.10 BD140.16	15 min 40/250 40/100 63/160 100/250	0.5 0.15 0.15 0.15 0.15				6	20 12.5 12.5 12.5 12.5
	300	MJE13002•		5/25	1	4	0.7	1	5	40
	400	MJE13003•		5/25	1	4	0.7	1	5	40
2	45		BD234	25 min	1				3	25
	60	BD235	BD236	25 min	1				3	25
	80	BD237		25 min	1				3	25
	100	MJE270##	MJE271##	1.5k min	0.12				6	15
3	30	MJE520	MJE370	25 min	1					25
	40	MJE180	MJE170	50/250	0.1	0.6 typ	0.12 typ	0.1	50	12.5

• Case 77 (Style 3), # |h_{FE}| @ 1 MHz, ## Darlington

(continued)

2N4918
thru
2N4920

MEDIUM-POWER PLASTIC PNP SILICON TRANSISTORS

... designed for driver circuits, switching, and amplifier applications.
These high-performance plastic devices feature:

- Low Saturation Voltage — $V_{CE(sat)} = 0.6 \text{ Vdc (Max) @ } I_C = 1.0 \text{ Amp}$
- Excellent Power Dissipation Due to Thermopad Construction — $P_D = 30 \text{ W @ } T_C = 25^\circ\text{C}$
- Excellent Safe Operating Area
- Gain Specified to $I_C = 1.0 \text{ Amp}$
- Complement to NPN 2N4921, 2N4922, 2N4923

***MAXIMUM RATINGS**

Ratings	Symbol	2N4918	2N4919	2N4920	Unit
Collector-Emitter Voltage	V_{CEO}	40	60	80	Vdc
Collector-Base Voltage	V_{CB}	40	60	80	Vdc
Emitter-Base Voltage	V_{EB}	5.0			Vdc
Collector Current — Continuous (1)	I_C^*	1.0			Adc
		3.0			Adc
Base Current	I_B	1.0			Adc
Total Power Dissipation @ $T_C = 25^\circ\text{C}$ Derate above 25°C	P_D	30 0.24			Watts W/ $^\circ\text{C}$
Operating & Storage Junction Temperature Range	T_J, T_{stg}	-65 to +150			$^\circ\text{C}$


THERMAL CHARACTERISTICS (2)

Characteristic	Symbol	Max	Unit
Thermal Resistance, Junction to Case	θ_{JC}	4.16	$^\circ\text{C/W}$

*Indicates JEDEC Registered Data for 2N4918 Series



- (1) The 1.0 Amp maximum I_C value is based upon JEDEC current gain requirements.
The 3.0 Amp maximum value is based upon actual current-handling capability of the device (See Figure 5).
- (2) Recommend use of thermal compound for lowest thermal resistance.

FIGURE 1 — POWER DERATING



3 AMPERE
GENERAL-PURPOSE
POWER TRANSISTORS

40-80 VOLTS
30 WATTS



DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	10.80	11.04	0.425	0.435
B	7.50	7.74	0.295	0.305
C	2.42	2.66	0.095	0.105
D	0.51	0.66	0.020	0.026
F	2.93	3.17	0.115	0.125
G	2.39 BSC		0.094 BSC	
H	1.27	2.41	0.050	0.095
J	0.39	0.63	0.015	0.025
K	14.61	16.63	0.575	0.655
M	3° TYP		3° TYP	
Q	3.76	4.01	0.148	0.158
R	1.15	1.39	0.045	0.055
S	0.64	0.88	0.025	0.035
T	3.69	3.93	0.145	0.155
V	1.02	—	0.040	—

CASE 77-06
TO-225AA TYPE

2N4918 thru 2N4920

ELECTRICAL CHARACTERISTICS ($T_C = 25^\circ\text{C}$ unless otherwise noted)

Characteristic		Symbol	Min	Max	Unit
OFF CHARACTERISTICS					
Collector-Emitter Sustaining Voltage (1) ($I_C = 0.1 \text{ A dc}$, $I_B = 0$)	2N4918 2N4919 2N4920	$V_{CEO(sus)}$	40 60 80	--	Vdc
Collector Cutoff Current ($V_{CE} = 20 \text{ Vdc}$, $I_B = 0$) ($V_{CE} = 30 \text{ Vdc}$, $I_B = 0$) ($V_{CE} = 40 \text{ Vdc}$, $I_B = 0$)	2N4918 2N4919 2N4920	I_{CEO}	-- -- --	0.5 0.5 0.5	mA dc
Collector Cutoff Current ($V_{CE} = \text{Rated } V_{CEO}$, $V_{BE(off)} = 1.5 \text{ Vdc}$) ($V_{CE} = \text{Rated } V_{CEO}$, $V_{BE(off)} = 1.5 \text{ Vdc}$, $T_C = 125^\circ\text{C}$)		I_{CEX}	-- --	0.1 0.5	mA dc
Collector Cutoff Current ($V_{CB} = \text{Rated } V_{CB}$, $I_E = 0$)		I_{CBO}	--	0.1	mA dc
Emitter Cutoff Current ($V_{BE} = 5.0 \text{ Vdc}$, $I_C = 0$)		I_{EBO}	--	1.0	mA dc
ON CHARACTERISTICS					
DC Current Gain (1) ($I_C = 50 \text{ mA dc}$, $V_{CE} = 1.0 \text{ Vdc}$) ($I_C = 500 \text{ mA dc}$, $V_{CE} = 1.0 \text{ Vdc}$) ($I_C = 1.0 \text{ A dc}$, $V_{CE} = 1.0 \text{ Vdc}$)		h_{FE}	40 30 10	-- 150 --	--
Collector-Emitter Saturation Voltage (1) ($I_C = 1.0 \text{ A dc}$, $I_B = 0.1 \text{ A dc}$)		$V_{CE(sat)}$	--	0.6	Vdc
Base-Emitter Saturation Voltage (1) ($I_C = 1.0 \text{ A dc}$, $I_B = 0.1 \text{ A dc}$)		$V_{BE(sat)}$	--	1.3	Vdc
Base-Emitter On Voltage (1) ($I_C = 1.0 \text{ A dc}$, $V_{CE} = 1.0 \text{ Vdc}$)		$V_{BE(on)}$	--	1.3	Vdc
SMALL-SIGNAL CHARACTERISTICS					
Current Gain — Bandwidth Product ($I_C = 250 \text{ mA dc}$, $V_{CE} = 10 \text{ Vdc}$, $f = 1.0 \text{ MHz}$)		f_T	3.0	--	MHz
Output Capacitance ($V_{CB} = 10 \text{ Vdc}$, $I_E = 0$, $f = 100 \text{ kHz}$)		C_{ob}	--	100	pF
Small-Signal Current Gain ($I_C = 250 \text{ mA dc}$, $V_{CE} = 10 \text{ Vdc}$, $f = 1.0 \text{ kHz}$)		h_{fe}	25	--	--

*Indicates JEDEC Registered Data

(1) Pulse Test: PW $\approx 300 \mu\text{s}$, Duty Cycle $\approx 2.0\%$

FIGURE 2 — SWITCHING TIME EQUIVALENT CIRCUIT




FIGURE 3 — TURN-ON TIME




FIGURE 4 – THERMAL RESPONSE





FIGURE 5 – ACTIVE-REGION SAFE OPERATING AREA



There are two limitations on the power handling ability of a transistor: average junction temperature and second breakdown. Safe operating area curves indicate $I_C - V_{CE}$ operation i.e., the transistor must not be subjected to greater dissipation than the curves indicate.

The data of Figure 5 is based on $T_{J(pk)} = 150^\circ\text{C}$; T_C is variable depending on conditions. Second breakdown pulse limits are valid for duty cycles to 10% provided $T_{J(pk)} \leq 150^\circ\text{C}$. At high case temperatures, thermal limitations will reduce the power that can be handled to values less than the limitations imposed by second breakdown.

FIGURE 6 – STORAGE TIME





FIGURE 7 – FALL TIME



TYPICAL DC CHARACTERISTICS

FIGURE 8 – CURRENT GAIN




FIGURE 9 – COLLECTOR SATURATION REGION




FIGURE 10 – EFFECTS OF BASE-EMITTER RESISTANCE




FIGURE 11 – "ON" VOLTAGE




FIGURE 12 – COLLECTOR CUTOFF REGION




FIGURE 13 – TEMPERATURE COEFFICIENTS

