


SHROUDED HEADERS & STACKERS

(1.27 mm) .050" PITCH • TML/ZML SERIES



TML/ZML

Mates:

SMS, RSM

SPECIFICATIONS

TML

Insulator Material:

Black Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating:

Au or Sn over

50 μ" (1.27 μm) Ni

Operating Temp Range:

-55 °C to +105 °C with Tin;

-55 °C to +125 °C with Gold

ZML

Insulator Material:

Black Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating:

Au or Sn over

50 μ" (1.27 μm) Ni

Operating Temp Range:

-55 °C to +105 °C with Tin;

-55 °C to +125 °C with Gold

PROCESSING

TML

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0.10 mm) .004" max (05-20)

(0.15 mm) .006" max (32)*

*(.004" stencil solution

may be available; contact

ipg@samtec.com)

ZML

Same as TML except:

SMT Lead Coplanarity:

(0.15 mm) .006" max*

*(.004" stencil solution

may be available; contact

ipg@samtec.com)

TML	-	1	NO. PINS PER ROW	-	LEAD STYLE	-	PLATING OPTION	-	D	-	TAIL OPTION	-	OTHER OPTION
-----	---	---	---------------------	---	---------------	---	-------------------	---	---	---	----------------	---	-----------------

05, 08,
10, 20, 32
(Standard sizes)

Specify
LEAD
STYLE
from
chart

-F
= Gold flash
on post,
Matte Tin on tail

-L
= 10 μ" (0.25 μm)
Gold on post,
Matte Tin on tail


-G
= 10 μ" (0.25 μm)
Gold on post,
Gold flash on tail

(Leave blank for
Through-hole)


-RA
= Right-angle

-SM
= Surface Mount
(For locking clip
add -LC)

-“XXX”
= Polarized
position
(Specify position
of omitted pin)



THROUGH-HOLE



SURFACE MOUNT

RIGHT-ANGLE

LEAD STYLE	POST HEIGHT (A)
-01	(3.05) .120
-02	(5.84) .230
-03	(4.32) .170

ZML	-	1	NO. PINS PER ROW	-	LEAD STYLE	-	PLATING OPTION	-	D	-	BODY HEIGHT	-	TAIL OPTION
-----	---	---	---------------------	---	---------------	---	-------------------	---	---	---	----------------	---	----------------

05, 08,
10, 20, 32
(Standard sizes)

Specify
LEAD
STYLE
from
chart

-L
= 10 μ" (0.25 μm)
Gold on post,
Matte Tin on tail


-G
= 10 μ" (0.25 μm)
Gold on post,
Gold flash on tail

(Leave blank for
Through-hole)


-“XXX”
= -SM Body Height
(Specify board space
“B” in inches from
lead style charts.)

(Leave blank for
Through-hole)

-SM
= Surface
Mount



THROUGH-HOLE



SURFACE MOUNT

THROUGH-HOLE	
LEAD STYLE	BODY HEIGHT (C)
-01	(12.83) .505
-02	(14.22) .560
-03	(16.64) .655
-04	(19.69) .775

SURFACE MOUNT		
LEAD STYLE	POST HEIGHT (A)	BODY HEIGHT (B)
-53	(3.05) .120	(13.46) .530 to (20.19) .795
-54	(5.84) .230	(13.46) .530 to (17.40) .685

ALSO AVAILABLE
Contact Samtec

Other sizes

Other platings

Notes:

For added mechanical stability, Samtec recommends mechanical board spacers be used in applications with gold or selective gold plated connectors. Contact ipg@samtec.com for more information.

Some sizes, styles and options are non-standard, non-returnable.