



# 74HC4017; 74HCT4017

Johnson decade counter with 10 decoded outputs

Rev. 8 — 27 March 2024

Product data sheet

## 1. General description

The 74HC4017; 74HCT4017 is a 5-stage Johnson decade counter with 10 decoded outputs (Q0 to Q9), an output from the most significant flip-flop ( $\overline{Q}5-9$ ), two clock inputs (CP0 and  $\overline{CP}1$ ) and an overriding asynchronous master reset input (MR). The counter is advanced by either a LOW-to-HIGH transition at CP0 while  $\overline{CP}1$  is LOW or a HIGH-to-LOW transition at  $\overline{CP}1$  while CP0 is HIGH. When cascading counters, the  $\overline{Q}5-9$  output, which is LOW while the counter is in states 5, 6, 7, 8 and 9, can be used to drive the CP0 input of the next counter. A HIGH on MR resets the counter to zero (Q0 =  $\overline{Q}5-9$  = HIGH; Q1 to Q9 = LOW) independent of the clock inputs (CP0 and  $\overline{CP}1$ ). Automatic code correction of the counter is provided by an internal circuit: following any illegal code the counter returns to a proper counting mode within 11 clock pulses. Inputs include clamp diodes. This enables the use of current limiting resistors to interface inputs to voltages in excess of  $V_{CC}$ .

## 2. Features and benefits

- Wide supply voltage range from 2.0 V to 6.0 V
- CMOS low power dissipation
- High noise immunity
- Latch-up performance exceeds 100 mA per JESD 78 Class II Level B
- Complies with JEDEC standards:
  - JESD8C (2.7 V to 3.6 V)
  - JESD7A (2.0 V to 6.0 V)
- Input levels:
  - For 74HC4017: CMOS level
  - For 74HCT4017: TTL level
- ESD protection:
  - HBM: ANSI/ESDA/JEDEC JS-001 class 2 exceeds 2000 V
  - CDM: ANSI/ESDA/JEDEC JS-002 class C3 exceeds 1000 V
- Multiple package options
- Specified from -40 °C to +85 °C and from -40 °C to +125 °C

## 3. Ordering information

Table 1. Ordering information

| Type number                                               | Package           |          |                                                                                                                                      |                          |
|-----------------------------------------------------------|-------------------|----------|--------------------------------------------------------------------------------------------------------------------------------------|--------------------------|
|                                                           | Temperature range | Name     | Description                                                                                                                          | Version                  |
| <a href="#">74HC4017D</a><br><a href="#">74HCT4017D</a>   | -40 °C to +125 °C | SO16     | plastic small outline package; 16 leads;<br>body width 3.9 mm                                                                        | <a href="#">SOT109-1</a> |
| <a href="#">74HC4017PW</a>                                | -40 °C to +125 °C | TSSOP16  | plastic thin shrink small outline package; 16 leads;<br>body width 4.4 mm                                                            | <a href="#">SOT403-1</a> |
| <a href="#">74HC4017BQ</a><br><a href="#">74HCT4017BQ</a> | -40 °C to +125 °C | DHVQFN16 | plastic dual in-line compatible thermal enhanced<br>very thin quad flat package; no leads; 16 terminals;<br>body 2.5 × 3.5 × 0.85 mm | <a href="#">SOT763-1</a> |

4. Functional diagram




Fig. 1. Functional diagram




Fig. 2. Logic symbol




Fig. 3. IEC logic symbol




Fig. 4. Logic diagram





Fig. 5. Timing diagram

5. Pinning information

5.1. Pinning



5.2. Pin description

Table 2. Pin description

| Symbol                                 | Pin                            | Description                              |
|----------------------------------------|--------------------------------|------------------------------------------|
| Q0, Q1, Q2, Q3, Q4, Q5, Q6, Q7, Q8, Q9 | 3, 2, 4, 7, 10, 1, 5, 6, 9, 11 | decoded output                           |
| GND                                    | 8                              | ground (0 V)                             |
| Q5-9                                   | 12                             | carry output (active LOW)                |
| CP1                                    | 13                             | clock input (HIGH-to-LOW edge-triggered) |
| CP0                                    | 14                             | clock input (LOW-to-HIGH edge-triggered) |
| MR                                     | 15                             | master reset input (active HIGH)         |
| V <sub>CC</sub>                        | 16                             | supply voltage                           |

6. Functional description

Table 3. Function table

H = HIGH voltage level; L = LOW voltage level; X = don't care; ↑ = LOW-to-HIGH transition; ↓ = HIGH-to-LOW transition;

| MR | CP0 | CP1 | Operation                        |
|----|-----|-----|----------------------------------|
| H  | X   | X   | Q0 = Q5-9 = HIGH; Q1 to Q9 = LOW |
| L  | H   | ↓   | counter advances                 |
| L  | ↑   | L   | counter advances                 |
| L  | L   | X   | no change                        |
| L  | X   | H   | no change                        |
| L  | H   | ↑   | no change                        |
| L  | ↓   | L   | no change                        |

7. Limiting values

Table 4. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

| Symbol           | Parameter               | Conditions                                                              | Min  | Max  | Unit |
|------------------|-------------------------|-------------------------------------------------------------------------|------|------|------|
| V <sub>CC</sub>  | supply voltage          |                                                                         | -0.5 | +7   | V    |
| I <sub>IK</sub>  | input clamping current  | V <sub>I</sub> < -0.5 V or V <sub>I</sub> > V <sub>CC</sub> + 0.5 V [1] | -    | ±20  | mA   |
| I <sub>OK</sub>  | output clamping current | V <sub>O</sub> < -0.5 V or V <sub>O</sub> > V <sub>CC</sub> + 0.5 V [1] | -    | ±20  | mA   |
| I <sub>O</sub>   | output current          | -0.5 V < V <sub>O</sub> < V <sub>CC</sub> + 0.5 V                       | -    | ±25  | mA   |
| I <sub>CC</sub>  | supply current          |                                                                         | -    | 50   | mA   |
| I <sub>GND</sub> | ground current          |                                                                         | -50  | -    | mA   |
| T <sub>stg</sub> | storage temperature     |                                                                         | -65  | +150 | °C   |
| P <sub>tot</sub> | total power dissipation | T <sub>amb</sub> = -40 °C to +125 °C [2]                                | -    | 500  | mW   |

- [1] The input and output voltage ratings may be exceeded if the input and output current ratings are observed.  
[2] For SOT109-1 (SO16) package: P<sub>tot</sub> derates linearly with 12.4 mW/K above 110 °C.  
For SOT403-1 (TSSOP16) package: P<sub>tot</sub> derates linearly with 8.5 mW/K above 91 °C.  
For SOT763-1 (DHVQFN16) package: P<sub>tot</sub> derates linearly with 11.2 mW/K above 106 °C.

8. Recommended operating conditions

Table 5. Recommended operating conditions

| Symbol           | Parameter                           | Conditions              | 74HC4017 |      |                 | 74HCT4017 |      |                 | Unit |
|------------------|-------------------------------------|-------------------------|----------|------|-----------------|-----------|------|-----------------|------|
|                  |                                     |                         | Min      | Typ  | Max             | Min       | Typ  | Max             |      |
| V <sub>CC</sub>  | supply voltage                      |                         | 2.0      | 5.0  | 6.0             | 4.5       | 5.0  | 5.5             | V    |
| V <sub>I</sub>   | input voltage                       |                         | 0        | -    | V <sub>CC</sub> | 0         | -    | V <sub>CC</sub> | V    |
| V <sub>O</sub>   | output voltage                      |                         | 0        | -    | V <sub>CC</sub> | 0         | -    | V <sub>CC</sub> | V    |
| Δt/ΔV            | input transition rise and fall rate | V <sub>CC</sub> = 2.0 V | -        | -    | 625             | -         | -    | -               | ns/V |
|                  |                                     | V <sub>CC</sub> = 4.5 V | -        | 1.67 | 139             | -         | 1.67 | 139             | ns/V |
|                  |                                     | V <sub>CC</sub> = 6.0 V | -        | -    | 83              | -         | -    | -               | ns/V |
| T <sub>amb</sub> | ambient temperature                 |                         | -40      | +25  | +125            | -40       | +25  | +125            | °C   |

9. Static characteristics

Table 6. Static characteristics

At recommended operating conditions; voltages are referenced to GND (ground = 0 V).

| Symbol          | Parameter                 | Conditions                                                                             | 25 °C |      |      | -40 °C to +85 °C |      | -40 °C to +125 °C |      | Unit |
|-----------------|---------------------------|----------------------------------------------------------------------------------------|-------|------|------|------------------|------|-------------------|------|------|
|                 |                           |                                                                                        | Min   | Typ  | Max  | Min              | Max  | Min               | Max  |      |
| 74HC4017        |                           |                                                                                        |       |      |      |                  |      |                   |      |      |
| V <sub>IH</sub> | HIGH-level input voltage  | V <sub>CC</sub> = 2.0 V                                                                | 1.5   | 1.2  | -    | 1.5              | -    | 1.5               | -    | V    |
|                 |                           | V <sub>CC</sub> = 4.5 V                                                                | 3.15  | 2.4  | -    | 3.15             | -    | 3.15              | -    | V    |
|                 |                           | V <sub>CC</sub> = 6.0 V                                                                | 4.2   | 3.2  | -    | 4.2              | -    | 4.2               | -    | V    |
| V <sub>IL</sub> | LOW-level input voltage   | V <sub>CC</sub> = 2.0 V                                                                | -     | 0.8  | 0.5  | -                | 0.5  | -                 | 0.5  | V    |
|                 |                           | V <sub>CC</sub> = 4.5 V                                                                | -     | 2.1  | 1.35 | -                | 1.35 | -                 | 1.35 | V    |
|                 |                           | V <sub>CC</sub> = 6.0 V                                                                | -     | 2.8  | 1.8  | -                | 1.8  | -                 | 1.8  | V    |
| V <sub>OH</sub> | HIGH-level output voltage | V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub>                                    |       |      |      |                  |      |                   |      |      |
|                 |                           | I <sub>O</sub> = -20 µA; V <sub>CC</sub> = 2.0 V                                       | 1.9   | 2.0  | -    | 1.9              | -    | 1.9               | -    | V    |
|                 |                           | I <sub>O</sub> = -20 µA; V <sub>CC</sub> = 4.5 V                                       | 4.4   | 4.5  | -    | 4.4              | -    | 4.4               | -    | V    |
|                 |                           | I <sub>O</sub> = -20 µA; V <sub>CC</sub> = 6.0 V                                       | 5.9   | 6.0  | -    | 5.9              | -    | 5.9               | -    | V    |
|                 |                           | I <sub>O</sub> = -4.0 mA; V <sub>CC</sub> = 4.5 V                                      | 3.98  | 4.32 | -    | 3.84             | -    | 3.7               | -    | V    |
|                 |                           | I <sub>O</sub> = -5.2 mA; V <sub>CC</sub> = 6.0 V                                      | 5.48  | 5.81 | -    | 5.34             | -    | 5.2               | -    | V    |
| V <sub>OL</sub> | LOW-level output voltage  | V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub>                                    |       |      |      |                  |      |                   |      |      |
|                 |                           | I <sub>O</sub> = 20 µA; V <sub>CC</sub> = 2.0 V                                        | -     | 0    | 0.1  | -                | 0.1  | -                 | 0.1  | V    |
|                 |                           | I <sub>O</sub> = 20 µA; V <sub>CC</sub> = 4.5 V                                        | -     | 0    | 0.1  | -                | 0.1  | -                 | 0.1  | V    |
|                 |                           | I <sub>O</sub> = 20 µA; V <sub>CC</sub> = 6.0 V                                        | -     | 0    | 0.1  | -                | 0.1  | -                 | 0.1  | V    |
|                 |                           | I <sub>O</sub> = 4.0 mA; V <sub>CC</sub> = 4.5 V                                       | -     | 0.15 | 0.26 | -                | 0.33 | -                 | 0.4  | V    |
|                 |                           | I <sub>O</sub> = 5.2 mA; V <sub>CC</sub> = 6.0 V                                       | -     | 0.16 | 0.26 | -                | 0.33 | -                 | 0.4  | V    |
| I <sub>I</sub>  | input leakage current     | V <sub>I</sub> = V <sub>CC</sub> or GND; V <sub>CC</sub> = 6.0 V                       | -     | -    | ±0.1 | -                | ±1.0 | -                 | ±1.0 | µA   |
| I <sub>CC</sub> | supply current            | V <sub>I</sub> = V <sub>CC</sub> or GND; I <sub>O</sub> = 0 A; V <sub>CC</sub> = 6.0 V | -     | -    | 8.0  | -                | 80   | -                 | 160  | µA   |
| C <sub>I</sub>  | input capacitance         |                                                                                        | -     | 3.5  | -    | -                | -    | -                 | -    | pF   |

| Symbol           | Parameter                 | Conditions                                                                                                                                              | 25 °C |      |      | -40 °C to +85 °C |      | -40 °C to +125 °C |      | Unit |
|------------------|---------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------|-------|------|------|------------------|------|-------------------|------|------|
|                  |                           |                                                                                                                                                         | Min   | Typ  | Max  | Min              | Max  | Min               | Max  |      |
| 74HCT4017        |                           |                                                                                                                                                         |       |      |      |                  |      |                   |      |      |
| V <sub>IH</sub>  | HIGH-level input voltage  | V <sub>CC</sub> = 4.5 V to 5.5 V                                                                                                                        | 2.0   | 1.6  | -    | 2.0              | -    | 2.0               | -    | V    |
| V <sub>IL</sub>  | LOW-level input voltage   | V <sub>CC</sub> = 4.5 V to 5.5 V                                                                                                                        | -     | 1.2  | 0.8  | -                | 0.8  | -                 | 0.8  | V    |
| V <sub>OH</sub>  | HIGH-level output voltage | V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub> ; V <sub>CC</sub> = 4.5 V                                                                           |       |      |      |                  |      |                   |      |      |
|                  |                           | I <sub>O</sub> = -20 µA                                                                                                                                 | 4.4   | 4.5  | -    | 4.4              | -    | 4.4               | -    | V    |
|                  |                           | I <sub>O</sub> = -4 mA                                                                                                                                  | 3.98  | 4.32 | -    | 3.84             | -    | 3.7               | -    | V    |
| V <sub>OL</sub>  | LOW-level output voltage  | V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub> ; V <sub>CC</sub> = 4.5 V                                                                           |       |      |      |                  |      |                   |      |      |
|                  |                           | I <sub>O</sub> = 20 µA                                                                                                                                  | -     | 0    | 0.1  | -                | 0.1  | -                 | 0.1  | V    |
|                  |                           | I <sub>O</sub> = 4.0 mA                                                                                                                                 | -     | 0.15 | 0.26 | -                | 0.33 | -                 | 0.4  | V    |
| I <sub>I</sub>   | input leakage current     | V <sub>I</sub> = V <sub>CC</sub> or GND; V <sub>CC</sub> = 5.5 V                                                                                        | -     | -    | ±0.1 | -                | ±1.0 | -                 | ±1.0 | µA   |
| I <sub>CC</sub>  | supply current            | V <sub>I</sub> = V <sub>CC</sub> or GND; V <sub>CC</sub> = 5.5 V; I <sub>O</sub> = 0 A                                                                  | -     | -    | 8.0  | -                | 80   | -                 | 160  | µA   |
| ΔI <sub>CC</sub> | additional supply current | per input pin; V <sub>I</sub> = V <sub>CC</sub> - 2.1 V; other inputs at V <sub>CC</sub> or GND; V <sub>CC</sub> = 4.5 V to 5.5 V; I <sub>O</sub> = 0 A |       |      |      |                  |      |                   |      |      |
|                  |                           | CP0 input                                                                                                                                               | -     | 25   | 90   | -                | 113  | -                 | 123  | µA   |
|                  |                           | CP1 input                                                                                                                                               | -     | 40   | 144  | -                | 180  | -                 | 196  | µA   |
|                  |                           | MR input                                                                                                                                                | -     | 50   | 180  | -                | 225  | -                 | 245  | µA   |
| C <sub>I</sub>   | input capacitance         |                                                                                                                                                         | -     | 3.5  | -    | -                | -    | -                 | -    | pF   |

10. Dynamic characteristics

Table 7. Dynamic characteristics

GND = 0 V;  $t_r = t_f = 6\text{ ns}$ ;  $C_L = 50\text{ pF}$ ; see Fig. 9.

| Symbol           | Parameter                     | Conditions                                      | 25 °C |     |     | -40 °C to +85 °C |     | -40 °C to +125 °C |     | Unit |
|------------------|-------------------------------|-------------------------------------------------|-------|-----|-----|------------------|-----|-------------------|-----|------|
|                  |                               |                                                 | Min   | Typ | Max | Min              | Max | Min               | Max |      |
| 74HC4017         |                               |                                                 |       |     |     |                  |     |                   |     |      |
| t <sub>pd</sub>  | propagation delay             | CP0 to Qn; CP0 to Q̄5-9; see Fig. 6 [1]         |       |     |     |                  |     |                   |     |      |
|                  |                               | V <sub>CC</sub> = 2.0 V                         | -     | 63  | 230 | -                | 290 | -                 | 345 | ns   |
|                  |                               | V <sub>CC</sub> = 4.5 V                         | -     | 23  | 46  | -                | 58  | -                 | 69  | ns   |
|                  |                               | V <sub>CC</sub> = 5.0 V; C <sub>L</sub> = 15 pF | -     | 20  | -   | -                | -   | -                 | -   | ns   |
|                  |                               | V <sub>CC</sub> = 6.0 V                         | -     | 18  | 39  | -                | 49  | -                 | 59  | ns   |
|                  |                               | CP̄1 to Qn; CP̄1 to Q̄5-9; see Fig. 6           |       |     |     |                  |     |                   |     |      |
|                  |                               | V <sub>CC</sub> = 2.0 V                         | -     | 61  | 250 | -                | 315 | -                 | 375 | ns   |
|                  |                               | V <sub>CC</sub> = 4.5 V                         | -     | 22  | 50  | -                | 63  | -                 | 75  | ns   |
|                  |                               | V <sub>CC</sub> = 5.0 V; C <sub>L</sub> = 15 pF | -     | 20  | -   | -                | -   | -                 | -   | ns   |
|                  |                               | V <sub>CC</sub> = 6.0 V                         | -     | 18  | 43  | -                | 54  | -                 | 64  | ns   |
| t <sub>PHL</sub> | HIGH to LOW propagation delay | MR to Qn; see Fig. 7                            |       |     |     |                  |     |                   |     |      |
|                  |                               | V <sub>CC</sub> = 2.0 V                         | -     | 52  | 230 | -                | 290 | -                 | 345 | ns   |
|                  |                               | V <sub>CC</sub> = 4.5 V                         | -     | 19  | 46  | -                | 58  | -                 | 69  | ns   |
|                  |                               | V <sub>CC</sub> = 6.0 V                         | -     | 15  | 39  | -                | 49  | -                 | 59  | ns   |
| t <sub>PLH</sub> | LOW to HIGH propagation delay | MR to Q̄5-9, Q0; see Fig. 7                     |       |     |     |                  |     |                   |     |      |
|                  |                               | V <sub>CC</sub> = 2.0 V                         | -     | 55  | 230 | -                | 290 | -                 | 345 | ns   |
|                  |                               | V <sub>CC</sub> = 4.5 V                         | -     | 20  | 46  | -                | 58  | -                 | 69  | ns   |
|                  |                               | V <sub>CC</sub> = 6.0 V                         | -     | 16  | 39  | -                | 49  | -                 | 59  | ns   |
| t <sub>t</sub>   | transition time               | see Fig. 6 [2]                                  |       |     |     |                  |     |                   |     |      |
|                  |                               | V <sub>CC</sub> = 2.0 V                         | -     | 19  | 75  | -                | 95  | -                 | 110 | ns   |
|                  |                               | V <sub>CC</sub> = 4.5 V                         | -     | 7   | 15  | -                | 19  | -                 | 22  | ns   |
|                  |                               | V <sub>CC</sub> = 6.0 V                         | -     | 6   | 13  | -                | 16  | -                 | 19  | ns   |
| t <sub>w</sub>   | pulse width                   | CP0 and CP̄1 (HIGH or LOW); see Fig. 7          |       |     |     |                  |     |                   |     |      |
|                  |                               | V <sub>CC</sub> = 2.0 V                         | 80    | 17  | -   | 100              | -   | 120               | -   | ns   |
|                  |                               | V <sub>CC</sub> = 4.5 V                         | 16    | 6   | -   | 20               | -   | 24                | -   | ns   |
|                  |                               | V <sub>CC</sub> = 6.0 V                         | 14    | 5   | -   | 17               | -   | 20                | -   | ns   |
|                  |                               | MR (HIGH); see Fig. 7                           |       |     |     |                  |     |                   |     |      |
|                  |                               | V <sub>CC</sub> = 2.0 V                         | 80    | 19  | -   | 100              | -   | 120               | -   | ns   |
|                  |                               | V <sub>CC</sub> = 4.5 V                         | 16    | 7   | -   | 20               | -   | 24                | -   | ns   |
|                  |                               | V <sub>CC</sub> = 6.0 V                         | 14    | 6   | -   | 17               | -   | 20                | -   | ns   |
| t <sub>su</sub>  | set-up time                   | CP̄1 to CP0; CP0 to CP̄1; see Fig. 8            |       |     |     |                  |     |                   |     |      |
|                  |                               | V <sub>CC</sub> = 2.0 V                         | 50    | -8  | -   | 65               | -   | 75                | -   | ns   |
|                  |                               | V <sub>CC</sub> = 4.5 V                         | 10    | -3  | -   | 13               | -   | 15                | -   | ns   |
|                  |                               | V <sub>CC</sub> = 6.0 V                         | 9     | -2  | -   | 11               | -   | 13                | -   | ns   |


## Johnson decade counter with 10 decoded outputs


| Symbol           | Parameter                     | Conditions                                                                       | 25 °C |     |     | -40 °C to +85 °C |     | -40 °C to +125 °C |     | Unit |
|------------------|-------------------------------|----------------------------------------------------------------------------------|-------|-----|-----|------------------|-----|-------------------|-----|------|
|                  |                               |                                                                                  | Min   | Typ | Max | Min              | Max | Min               | Max |      |
| $t_h$            | hold time                     | $\overline{CP}1$ to $CP0$ ; $CP0$ to $\overline{CP}1$ ; see Fig. 8               |       |     |     |                  |     |                   |     |      |
|                  |                               | $V_{CC} = 2.0\text{ V}$                                                          | 50    | 17  | -   | 65               | -   | 75                | -   | ns   |
|                  |                               | $V_{CC} = 4.5\text{ V}$                                                          | 10    | 6   | -   | 13               | -   | 15                | -   | ns   |
|                  |                               | $V_{CC} = 6.0\text{ V}$                                                          | 9     | 5   | -   | 11               | -   | 13                | -   | ns   |
| $t_{rec}$        | recovery time                 | MR to $CP0$ and MR to $\overline{CP}1$ ; see Fig. 7                              |       |     |     |                  |     |                   |     |      |
|                  |                               | $V_{CC} = 2.0\text{ V}$                                                          | 5     | -17 | -   | 5                | -   | 5                 | -   | ns   |
|                  |                               | $V_{CC} = 4.5\text{ V}$                                                          | 5     | -6  | -   | 5                | -   | 5                 | -   | ns   |
|                  |                               | $V_{CC} = 6.0\text{ V}$                                                          | 5     | -5  | -   | 5                | -   | 5                 | -   | ns   |
| $f_{max}$        | maximum frequency             | $CP0$ or $\overline{CP}1$ ; see Fig. 7                                           |       |     |     |                  |     |                   |     |      |
|                  |                               | $V_{CC} = 2.0\text{ V}$                                                          | 6.0   | 23  | -   | 4.8              | -   | 4.0               | -   | MHz  |
|                  |                               | $V_{CC} = 4.5\text{ V}$                                                          | 30    | 70  | -   | 24               | -   | 20                | -   | MHz  |
|                  |                               | $V_{CC} = 5.0\text{ V}$ ; $C_L = 15\text{ pF}$                                   | -     | 77  | -   | -                | -   | -                 | -   | MHz  |
|                  |                               | $V_{CC} = 6.0\text{ V}$                                                          | 25    | 83  | -   | 28               | -   | 24                | -   | MHz  |
| $C_{PD}$         | power dissipation capacitance | $V_I = \text{GND to } V_{CC}$ ; $V_{CC} = 5\text{ V}$ ; $f_i = 1\text{ MHz}$ [3] | -     | 35  | -   | -                | -   | -                 | -   | pF   |
| <b>74HCT4017</b> |                               |                                                                                  |       |     |     |                  |     |                   |     |      |
| $t_{pd}$         | propagation delay             | $CP0$ to $Q_n$ ; $CP0$ to $\overline{Q}5-9$ ; see Fig. 6 [1]                     |       |     |     |                  |     |                   |     |      |
|                  |                               | $V_{CC} = 4.5\text{ V}$                                                          | -     | 25  | 46  | -                | 58  | -                 | 69  | ns   |
|                  |                               | $V_{CC} = 5.0\text{ V}$ ; $C_L = 15\text{ pF}$                                   | -     | 21  | -   | -                | -   | -                 | -   | ns   |
|                  |                               | $\overline{CP}1$ to $Q_n$ ; $\overline{CP}1$ to $\overline{Q}5-9$ ; see Fig. 6   |       |     |     |                  |     |                   |     |      |
|                  |                               | $V_{CC} = 4.5\text{ V}$                                                          | -     | 25  | 50  | -                | 63  | -                 | 75  | ns   |
|                  |                               | $V_{CC} = 5.0\text{ V}$ ; $C_L = 15\text{ pF}$                                   | -     | 21  | -   | -                | -   | -                 | -   | ns   |
| $t_{PHL}$        | HIGH to LOW propagation delay | MR to $Q_n$ ; see Fig. 7                                                         |       |     |     |                  |     |                   |     |      |
|                  |                               | $V_{CC} = 4.5\text{ V}$                                                          | -     | 22  | 46  | -                | 58  | -                 | 69  | ns   |
| $t_{PLH}$        | LOW to HIGH propagation delay | MR to $\overline{Q}5-9$ , $Q0$ ; see Fig. 7                                      |       |     |     |                  |     |                   |     |      |
|                  |                               | $V_{CC} = 4.5\text{ V}$                                                          | -     | 20  | 46  | -                | 58  | -                 | 69  | ns   |
| $t_t$            | transition time               | see Fig. 6 [2]                                                                   |       |     |     |                  |     |                   |     |      |
|                  |                               | $V_{CC} = 4.5\text{ V}$                                                          | -     | 7   | 15  | -                | 19  | -                 | 22  | ns   |
| $t_W$            | pulse width                   | $CP0$ and $\overline{CP}1$ (HIGH or LOW); see Fig. 7                             |       |     |     |                  |     |                   |     |      |
|                  |                               | $V_{CC} = 4.5\text{ V}$                                                          | 16    | 7   | -   | 20               | -   | 24                | -   | ns   |
|                  |                               | MR (HIGH); see Fig. 7                                                            |       |     |     |                  |     |                   |     |      |
|                  |                               | $V_{CC} = 4.5\text{ V}$                                                          | 16    | 4   | -   | 20               | -   | 24                | -   | ns   |
| $t_{su}$         | set-up time                   | $\overline{CP}1$ to $CP0$ ; $CP0$ to $\overline{CP}1$ ; see Fig. 8               |       |     |     |                  |     |                   |     |      |
|                  |                               | $V_{CC} = 4.5\text{ V}$                                                          | 10    | -3  | -   | 13               | -   | 15                | -   | ns   |
| $t_h$            | hold time                     | $\overline{CP}1$ to $CP0$ ; $CP0$ to $\overline{CP}1$ ; see Fig. 8               |       |     |     |                  |     |                   |     |      |
|                  |                               | $V_{CC} = 4.5\text{ V}$                                                          | 10    | 6   | -   | 13               | -   | 15                | -   | ns   |

| Symbol           | Parameter                     | Conditions                                                                                         | 25 °C |     |     | -40 °C to +85 °C |     | -40 °C to +125 °C |     | Unit |
|------------------|-------------------------------|----------------------------------------------------------------------------------------------------|-------|-----|-----|------------------|-----|-------------------|-----|------|
|                  |                               |                                                                                                    | Min   | Typ | Max | Min              | Max | Min               | Max |      |
| t <sub>rec</sub> | recovery time                 | MR to CP0 and MR to $\overline{\text{CP1}}$ ; see Fig. 7                                           |       |     |     |                  |     |                   |     |      |
|                  |                               | V <sub>CC</sub> = 4.5 V                                                                            | 5     | -5  | -   | 5                | -   | 5                 | -   | ns   |
| f <sub>max</sub> | maximum frequency             | CP0 or $\overline{\text{CP1}}$ ; see Fig. 7                                                        |       |     |     |                  |     |                   |     |      |
|                  |                               | V <sub>CC</sub> = 4.5 V                                                                            | 30    | 61  | -   | 24               | -   | 20                | -   | MHz  |
|                  |                               | V <sub>CC</sub> = 5.0 V; C <sub>L</sub> = 15 pF                                                    | -     | 67  | -   | -                | -   | -                 | -   | MHz  |
| C <sub>PD</sub>  | power dissipation capacitance | V <sub>I</sub> = GND to V <sub>CC</sub> - 1.5 V; V <sub>CC</sub> = 5 V; f <sub>i</sub> = 1 MHz [3] | -     | 36  | -   | -                | -   | -                 | -   | pF   |

- [1] t<sub>pd</sub> is the same as t<sub>PHL</sub> and t<sub>PLH</sub>.
- [2] t<sub>i</sub> is the same as t<sub>THL</sub> and t<sub>TLH</sub>.
- [3] C<sub>PD</sub> is used to determine the dynamic power dissipation (P<sub>D</sub> in μW):  
 $P_D = C_{PD} \times V_{CC}^2 \times f_i \times N + \sum (C_L \times V_{CC}^2 \times f_o)$  where:  
f<sub>i</sub> = input frequency in MHz;  
f<sub>o</sub> = output frequency in MHz;  
C<sub>L</sub> = output load capacitance in pF;  
V<sub>CC</sub> = supply voltage in V;  
N = number of inputs switching;  
 $\sum (C_L \times V_{CC}^2 \times f_o)$  = sum of outputs.


10.1. Waveforms and test circuit





Measurement points are given in [Table 8](#).  
 $V_{OL}$  and  $V_{OH}$  are typical voltage output levels that occur with the output load.

**Fig. 7.** Waveforms showing the minimum pulse width for CP0, CP1 and MR input; the maximum frequency for CP0 and CP1 input; the recovery time for MR and the MR input to Qn and Q5-9 output propagation delays



Measurement points are given in [Table 8](#).  
 $V_{OL}$  and  $V_{OH}$  are typical voltage output levels that occur with the output load.

**Fig. 8.** Waveforms showing the set-up and hold times for CP0 to CP1 and CP1 to CP0

**Table 8. Measurement points**

| Type      | Input               | Output              |
|-----------|---------------------|---------------------|
|           | $V_M$               | $V_M$               |
| 74HC4017  | $0.5 \times V_{CC}$ | $0.5 \times V_{CC}$ |
| 74HCT4017 | 1.3 V               | 1.3 V               |




Table 9. Test data


| Type      | Input    |            | Load         |              | S1 position        |                    |                    |
|-----------|----------|------------|--------------|--------------|--------------------|--------------------|--------------------|
|           | $V_I$    | $t_r, t_f$ | $C_L$        | $R_L$        | $t_{PHL}, t_{PLH}$ | $t_{PZH}, t_{PHZ}$ | $t_{PZL}, t_{PLZ}$ |
| 74HC4017  | $V_{CC}$ | 6 ns       | 15 pF, 50 pF | 1 k $\Omega$ | open               | GND                | $V_{CC}$           |
| 74HCT4017 | 3 V      | 6 ns       | 15 pF, 50 pF | 1 k $\Omega$ | open               | GND                | $V_{CC}$           |

## 11. Application information

Some examples of applications for the 74HC4017; 74HCT4017 are:


- Decade counter with decimal decoding
- 1 out of n decoding counter (when cascaded)
- Sequential controller
- Timer

**Fig. 10** shows a technique for extending the number of decoded output states for the 74HC4017; 74HCT4017. Decoded outputs are sequential within each stage and from stage to stage, with no dead time (except propagation delay).



**Remark:** It is essential not to enable the counter on  $\overline{CP1}$  when CP0 is HIGH, or on CP0 when  $\overline{CP1}$  is LOW, as this would cause an extra count.

Fig. 11 shows an example of a divide-by 2 through divide-by 10 circuit using one 74HC4017; 74HCT4017. Since the 74HC4017; 74HCT4017 has an asynchronous reset, the output pulse widths are narrow (minimum expected pulse width is 6 ns). The output pulse widths can be enlarged by inserting an RC network at the MR input.



12. Package outline

SO16: plastic small outline package; 16 leads; body width 3.9 mm

SOT109-1




Fig. 12. Package outline SOT109-1 (SO16)

TSSOP16: plastic thin shrink small outline package; 16 leads; body width 4.4 mm

SOT403-1




Fig. 13. Package outline SOT403-1 (TSSOP16)

DHVQFN16: plastic dual in-line compatible thermal enhanced very thin quad flat package; no leads;  
16 terminals; body 2.5 x 3.5 x 0.85 mm

SOT763-1




Fig. 14. Package outline SOT763-1 (DHVQFN16)

13. Abbreviations

Table 10. Abbreviations

| Acronym | Description                             |
|---------|-----------------------------------------|
| CDM     | Charged Device Model                    |
| CMOS    | Complementary Metal Oxide Semiconductor |
| DUT     | Device Under Test                       |
| ESD     | ElectroStatic Discharge                 |
| HBM     | Human Body Model                        |
| TTL     | Transistor-Transistor Logic             |

14. Revision history

Table 11. Revision history

| Document ID          | Release date                                                                                                                                                                                                                                                                                                                                                                                                                   | Data sheet status     | Change notice | Supersedes           |
|----------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|---------------|----------------------|
| 74HC_HCT4017 v.8     | 20240327                                                                                                                                                                                                                                                                                                                                                                                                                       | Product data sheet    | -             | 74HC_HCT4017 v.7     |
| Modifications:       | <ul style="list-style-type: none"><li>Section 2: ESD specification updated according to the latest JEDEC standard.</li><li>Fig. 12, Fig. 13: Aligned SO and TSSOP package outline drawings to JEDEC MS-012 and MO-153</li></ul>                                                                                                                                                                                                |                       |               |                      |
| 74HC_HCT4017 v.7     | 20210510                                                                                                                                                                                                                                                                                                                                                                                                                       | Product data sheet    | -             | 74HC_HCT4017 v.6     |
| Modifications:       | <ul style="list-style-type: none"><li>Type number 74HC4017DB (SOT338-1 / SSOP16) removed.</li></ul>                                                                                                                                                                                                                                                                                                                            |                       |               |                      |
| 74HC_HCT4017 v.6     | 20200701                                                                                                                                                                                                                                                                                                                                                                                                                       | Product data sheet    | -             | 74HC_HCT4017 v.5     |
| Modifications:       | <ul style="list-style-type: none"><li>The format of this data sheet has been redesigned to comply with the identity guidelines of Nexperia.</li><li>Legal texts have been adapted to the new company name where appropriate.</li><li>Section 1 and Section 2 updated.</li><li>Table 4: Derating values for P<sub>tot</sub> total power dissipation have been updated.</li></ul>                                                |                       |               |                      |
| 74HC_HCT4017 v.5     | 20160203                                                                                                                                                                                                                                                                                                                                                                                                                       | Product data sheet    | -             | 74HC_HCT4017 v.4     |
| Modifications:       | <ul style="list-style-type: none"><li>Type numbers 74HC4017N and 74HCT4017N (SOT38-4) removed.</li></ul>                                                                                                                                                                                                                                                                                                                       |                       |               |                      |
| 74HC_HCT4017 v.4     | 20131210                                                                                                                                                                                                                                                                                                                                                                                                                       | Product data sheet    | -             | 74HC_HCT4017 v.3     |
| Modifications:       | <ul style="list-style-type: none"><li>General description updated.</li></ul>                                                                                                                                                                                                                                                                                                                                                   |                       |               |                      |
| 74HC_HCT4017 v.3     | 20080108                                                                                                                                                                                                                                                                                                                                                                                                                       | Product data sheet    | -             | 74HC_HCT4017_CNV v.2 |
| Modifications:       | <ul style="list-style-type: none"><li>The format of this data sheet has been redesigned to comply with the new identity guidelines of NXP Semiconductors.</li><li>Legal texts have been adapted to the new company name where appropriate.</li><li>Section 3: DHVQFN16 package added.</li><li>Section 7: derating values added for DHVQFN16 package.</li><li>Section 12: outline drawing added for DHVQFN16 package.</li></ul> |                       |               |                      |
| 74HC_HCT4017_CNV v.2 | 19970829                                                                                                                                                                                                                                                                                                                                                                                                                       | Product specification | -             | -                    |

15. Legal information

Data sheet status

| Document status [1][2]         | Product status [3] | Definition                                                                            |
|--------------------------------|--------------------|---------------------------------------------------------------------------------------|
| Objective [short] data sheet   | Development        | This document contains data from the objective specification for product development. |
| Preliminary [short] data sheet | Qualification      | This document contains data from the preliminary specification.                       |
| Product [short] data sheet     | Production         | This document contains the product specification.                                     |

- [1] Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions".
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <https://www.nexperia.com>.

Definitions

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

**Short data sheet** — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

**Product specification** — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

Disclaimers

**Limited warranty and liability** — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

**Right to make changes** — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

**Suitability for use** — Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal

injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

**Limiting values** — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

**Terms and conditions of commercial sale** — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <http://www.nexperia.com/profile/terms>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

**No offer to sell or license** — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

**Non-automotive qualified products** — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

**Trademarks**

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

Contents

1. General description..... 1

2. Features and benefits..... 1

3. Ordering information..... 1

4. Functional diagram..... 2

5. Pinning information..... 4

5.1. Pinning..... 4

5.2. Pin description..... 4

6. Functional description..... 5

7. Limiting values..... 5

8. Recommended operating conditions..... 5

9. Static characteristics..... 6

10. Dynamic characteristics..... 8

10.1. Waveforms and test circuit..... 10

11. Application information..... 13

12. Package outline..... 14

13. Abbreviations..... 17

14. Revision history..... 17

15. Legal information..... 18

© Nexperia B.V. 2024. All rights reserved

For more information, please visit: <http://www.nexperia.com>

For sales office addresses, please send an email to: [salesaddresses@nexperia.com](mailto:salesaddresses@nexperia.com)

Date of release: 27 March 2024