


SHEET 1 OF 2
NUMBER 61320



1. TERMINAL SUPPLIED IN INDIVIDUAL FORM, NOT AS CONTINUOUS STRIP.
2. PARTS COMPLY WITH AMP SOLDERABILITY SPEC. NO. 109-11-3
3. .000030 GOLD OVER .000050 NICKEL.

4. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

BRIGHT TIN		61320-4
GOLD Δ	.012 PH. BRZ	61320-2 Δ
PRE-TIN		61320-1
FINISH	MATERIAL	PART NO

U2	REV PER ECO-10-000445	KK	HMR	JAN 2010
U1	RESTORED	BD	RS	1/15/85
U	REV PER AG-118			1/15/85
T	REV PER AG-25			1/15/85
S	ECN M-7426			1/15/85
R	SMT1 REV. & REDOWN	N-7310		1/15/85
-TR	REVIS. C. RECORD	DA	CHK	DATE
DR	4-15-83	DS		
CH	D. A. SATZ			
33	W. E. TRAVIS			

© 1987 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

MATERIAL AND FINISH
SEE TABLE

WIRE — RANGE — INSULATION
— * — — * —

TYPE
— * —

CLASS
— * —

LOC
CM, A


NO SHEET OF 2
61320

REV
U2

NAME
MATE-N-LOK SOCKET WITH P.C. BOARD TAB

1/6
DIMENSIONS IN INCHES. DO NOT SCALE PRINT.

SHEET 2 OF 2

NUMBER
61320

1. FOR 3, 4, 6, 9, 12, AND 15 CIRCUIT
 PANEL MOUNT HOUSINGS ONLY.

PRINT DIM
 DIMENSIONS IN INCHES. DO NOT SCALE PRINT.

SEE SHEET 1			
LTR	REVISION RECORD	ECN	DATE
DR	6-2-70	IDE	
JIM KUNKLE			
CHKD	6-4-70	APD	
Thun. 6-4-70	Thun. 6-4-70		

©1968 BY AMP INCORPORATED. ALL RIGHTS
 RESERVED. AMP PRODUCTS COVERED BY
 PATENTS AND/OR PATENTS PENDING

MATERIAL AND FINISH

—H—

WIRE — RANGE — INSULATION
 —H— —H—

TOLERANCE EXCEPT
 AS NOTED
 $\pm$.015 $\pm$ 1" 6"

SCALE
 2-1

CLASS

TYPE

LOC
 CM A

CUSTOMER COPY
 REFERENCE ONLY

AMP

AMP INCORPORATED
 HARTFORD, PENNA.

NO SHEET 2 OF 2
 61320

REV
 U2

NAME RECOMMENDED HOLE LOCATIONS
 FOR MOUNTING MATE-N-LOK HOUSINGS