



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		A1	REVISED PER ECO-11-004917	11MAR11	RK	HMR

D


C

B


A




- 1 WIRE RANGE: 0.13–0.32mm² (26–22 AWG).
- 2 INSULATION RANGE: 1.20–1.75 DIA.
- 3 FINISH: 0.76μm MINIMUM GOLD IN LOCALIZED GOLD PLATE AREA OVER 1.27μm MINIMUM NICKEL
- 4 FINISH: 2.54μm MINIMUM TIN IN LOCALIZED TIN PLATE AREA.



SECTION A-A



SECTION B-B



SECTION C-C

	PHOS. BRZ.	1586316-4
PRE-TIN	PHOS. BRZ.	1586316-3
	BRASS	1586316-2
PRE-TIN	BRASS	1586316-1
FINISH:	MATERIAL:	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HOOVER 14-OCT-2003	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK D. COLEY 14-OCT-2003				
		APVD D. COLEY 14-OCT-2003	NAME			
		PRODUCT SPEC	TERMINAL LOOSE PIECE, PIN VAL-U-LOK(TM)			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
0 PLC ±			A2	00779	C=1586316	—
1 PLC ± 0.3[.01]			SCALE 10:1			
2 PLC ± 0.15 [.006]			SHEET 1 OF 1			
3 PLC ± 0.050 [.0020]			REV A1			
4 PLC ±						
ANGLES ±						
FINISH		WEIGHT				
		CUSTOMER DRAWING				