


GSD



NOTES:

1. FOR USE WITH RG-8, 8A, 11, 11A & 213/U CABLE.
2. FOR CABLING INSTRUCTION SEE CP-402.
3. FOR CABLE CRIMPING USE DIE KTH-2003.
4. INTERFACE PER MIL-STD-348 FIG. 304-1.
5. MATERIALS:
 - INSULATOR: TEFLON, ASTM-D-4894
 - GASKET: SIL. RUBBER, ZZ-R-765
 - OUTER CONTACT AND C-RING: PHOS. BRONZE, ASTM-B-103
 - ALL OTHER METAL PARTS: BRASS, ASTM-B16
6. FINISHES:
 - CENTER CONTACT: SILVER PLATE PER QQ-S-365
 - ALL OTHER METAL PARTS: KINGS TARNISH RESISTANT NICKEL FINISH (TR-5)
7. ELECTRICAL CHARACTERISTICS:
 - NOMINAL IMPEDANCE: 50 OHM
 - FREQUENCY RANGE: DC TO 11 GHz
 - VOLTAGE RATING: 1000 VOLTS RMS

REVISIONS

ISSUE	CHANGES	
	DATE	BY
7	CN 31160 C	KH 09/20/89

KN-59-132

KN25132S

SCALE 4:1

APPROX SURFACE AREA

USED ON

REF:

PL, N

DRAWN	KH	DATE	05/20/97
DESIGN	VLS	DATE	05/21/97
APPR.		DATE	

KINGS
ELECTRONICS CO., INC.
TUCKAHOE, NEW YORK 10707

KN-59-132

GSD