

Key Parameters

V_{RRM}	=	3200 V
I_{FAVM}	=	1870 A
I_{FSM}	=	23.5 kA
V_{F0}	=	0.95 V
r_F	=	0.23 mΩ

Avalanche Rectifier Diode

5SDA 19F3205

Doc. No. 5SYA 1129 - 01 Apr-98

Features


- Optimized for line frequency rectifiers
- Low on-state voltage, narrow V_F -bands for parallel operation
- Self protected against transient overvoltages
- Guaranteed maximum avalanche power dissipation
- Industry standard housing

Blocking

Part number	5SDA 19F3205	5SDA 19F2905	Condition
V_{RRM}	3200	2900	$f = 50 \text{ Hz}$ $t_p = 10 \text{ ms}$
V_{RSM}	3520	3190	$t_p = 10 \text{ ms}$ $T_j = 160^\circ\text{C}$
I_{RRM}	$\leq 50 \text{ mA}$		V_{RRM} $T_j = 160^\circ\text{C}$
P_{RSM}	$\leq 100 \text{ kW}$		$t_p = 20 \mu\text{s}$ $T_j = 45^\circ\text{C}$
	$\leq 75 \text{ kW}$		$t_p = 20 \mu\text{s}$ $T_j = 160^\circ\text{C}$

Mechanical data

F_M	Mounting force	min.	20 kN
		max.	24 kN
a	Acceleration		
	Device unclamped		50 m/s ²
	Device clamped		200 m/s ²
m	Weight		0.5 kg
D_s	Surface creepage distance		30 mm
D_a	Air strike distance		20 mm



On-state

I _{FAVM}	Max. average on-state current	1870 A	Half sine wave, T _C = 85°C			
I _{FRMS}	Max. RMS on-state current	2940 A				
I _{FSM}	Max. peak non-repetitive surge current	23.5 kA	tp	=	10 ms	T _j = 160°C
		25.0 kA	tp	=	8.3 ms	After surge:
I ² t	Limiting load integral	2760·10 ³ A ² s	tp	=	10 ms	V _D = V _R = 0V
		2600·10 ³ A ² s	tp	=	8.3 ms	
V _{F0}	Threshold voltage	0.95 V	I _F	=	1500 - 4500 A	T _j = 160°C
r _F	Slope resistance	0.23 mΩ				
V _{F min}	On-state voltage	1.50 V	I _F	=	4000 A	T _j = 25°C
V _{F max}	On-state voltage	1.70 V				


Thermal

T_j	Storage and operating junction temperature range	-40...160°C	
R_{thJC}	Thermal resistance junction to case	40 K/kW	Anode side cooled
		40 K/kW	Cathode side cooled
		20 K/kW	Double side cooled
R_{thCH}	Thermal resistance case to heat sink	10 K/kW	Single side cooled
		5 K/kW	Double side cooled

Analytical function for transient thermal impedance:

$$Z_{thJC}(t) = \sum_{i=1}^4 R_i(1 - e^{-t/\tau_i})$$

i	1	2	3	4
$R_{(K/kW)}$	11.83	4.26	1.63	2.28
τ_i (s)	0.432	0.071	0.01	0.0054



For a given case temperature T_c at ambient temperature T_a the maximum on-state current can be calculated as follows:

$$I_{FAVM} = \frac{-V_{F0} + \sqrt{(V_{F0})^2 + 4 \cdot f^2 \cdot r_f \cdot P}}{2 \cdot f^2 \cdot r_f}$$

$$\text{where } P = \frac{T_{J \max} - T_C}{R_{thjc}} \text{ or } P = \frac{T_{J \max} - T_A}{R_{thja}}$$

I_{FAVM} (A)
 $T_{\max}$ (°C)
 R_{thja} (K/kW)

P (W)
 T_c (°C)
 R_{thjc} (K/kW)

V_{F0} (V)
 T_a (°C)
 r_f (Ω)

$f^2 =$ 1 for DC current
2.5 for half-sine wave
3.1 for 120° el., sine
6 for 60° el., sine