

SR-5H

300 V Subminiature time-delay fuses



Product features

- Radial leaded time-delay thru-hole fuse
- Designed to IEC 60127-3, Sheet 4
- Ideal for electronic lighting ballasts
- cURus Recognized at 300V/100A
- Internationally accepted for primary and secondary overcurrent protection
- Place directly into PCB or plug into BK/PCS holder
- High inrush withstand capability
- Compatible with leaded and lead-free reflow and wave solder
- Plastic base/cap, UL 94V0

Regulatory compliance

- cURus: File E19180 JDYX2, JDYX8
- KC: SU05011-9005 1A~2.5A, SU05011-9006A 3.15A~5A
- PSE+JET: JET1641-31007-1006 1~5A, JET1641-31007-1007 6.3A
- CCC: 2009010207369246 1~4A
- CQC: CQC09012036744 5A
- SEMKO: 1023114 1A~5A
- VDE: File 40020842
- VDE Acceptance: File 40020843
- VDE: File122052, 40020046

Environmental data

- Solderability: EIA-186-9E Method 9
- High Frequency Vibration: MIL-STD-202F, Method 201A
- Operating Temperature: -40°C to +125°C
- Soldering Heat Resistance: 260°C, 10S (IEC 60068-2-20)

Ordering information

- Specify product and packaging code (i.e., SR-5H-1A-BK2)

Electrical Characteristics

Rated Current	1.5 I _n	2.1 I _n	2.75 I _n		4 I _n		10 I _n	
	min	max	min	max	min	max	min	max
400mA-5A	60 min	2 min	400 ms	10 sec	150 ms	3 sec	20 ms	150 ms

Specifications

Part Number	Voltage Rating (Vac)*	Interrupting Rating (amps)@ Rated Voltage	Typical DC Cold Resistance (Ω)	Typical Melting I _t	Voltage Drop (mV) @ 20°C Rated Current	Agency Information					
						VDE	SEMKO	cURus*	CCC	KC-Mark	PSE*
SR-5H-400mA	300	100	0.285	0.771618	127			X			
SR-5H-500mA	300	100	0.24	2	143			X			
SR-5H-630mA	300	100	0.162	3.5	120			X			
SR-5H-800mA	300	100	0.113	6.5	107			X			
SR-5H-1A	300	100	0.081	7.5	93	X	X	X	X	X	X
SR-5H-1.25A	300	100	0.06	13	88	X	X	X	X	X	X
SR-5H-1.6A	300	100	0.043	24	85	X	X	X	X	X	X
SR-5H-2A	300	100	0.031	30	74	X	X	X	X	X	X
SR-5H-2.5A	300	100	0.025	45	75	X	X	X	X	X	X
SR-5H-3.15A	300	100	0.018	57	73	X	X	X	X	X	X
SR-5H-4A	300	100	0.013	80	65	X	X	X	X	X	X
SR-5H-5A	300	100	0.007	115	45	X**	X	X	X***	X	X


* cURus: 400mA - 5A @ 300Vac/100A; PSE: 1 - 5A @ 300Vac/100A

† Voltage rating 250Vac


** Acceptance

*** CQC

Dimensions / Packaging Information – mm [in]




Dimensions / Packaging Information – mm [in]



Packaging Suffix	
Packaging Code	Description
-BK	200 fuses in polybag, Lead L= 4.3 ± 0.3
-BK2	200 fuses in polybag, Lead L= 21 ± 3.0
-AP	1000 fuses, ammo-pack, pitch= 12.7



Time-Current Curves



PCS Mounting Socket (RoHS compliant)

- Available as option. Specify catalog number BK/PCS (in bulk 100 per bag)

(PC)



Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
www.eaton.com/electronics

© 2017 Eaton
All Rights Reserved
Printed in USA
Publication No. 4360 BU-SB11805
June 2017

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eaton:

[SR-5H-1A-APH](#) [SR-5H-2A-APH](#) [SR-5H-400MA-APH](#) [SR-5H-4A-APH](#) [SR-5H-500MA-APH](#) [SR-5H-5A-APH](#) [SR-5H-630MA-APH](#) [SR-5H-800MA-APH](#) [SR-5H-1-25A-AP](#) [SR-5H-1-25A-APH](#) [SR-5H-1-25A-BK](#) [SR-5H-1-6A-AP](#) [SR-5H-1-6A-APH](#) [SR-5H-1-6A-BK](#) [SR-5H-2-5A-AP](#) [SR-5H-2-5A-APH](#) [SR-5H-2-5A-BK](#) [SR-5H-3-15A-AP](#) [SR-5H-3-15A-APH](#) [SR-5H-3-15A-BK](#) [SR-5H-6-3A-AP](#) [SR-5H-6-3A-APH](#) [SR-5H-6-3A-BK](#) [SR-5H-1A-AP](#) [SR-5H-1A-BK](#) [SR-5H-2A-AP](#) [SR-5H-2A-BK](#) [SR-5H-4A-AP](#) [SR-5H-4A-BK](#) [SR-5H-5A-AP](#) [SR-5H-5A-BK](#) [SR-5H-1.25A-AP](#) [SR-5H-1.25A-BK](#) [SR-5H-1.6A-AP](#) [SR-5H-1.6A-BK](#) [SR-5H-2.5A-AP](#) [SR-5H-2.5A-BK](#) [SR-5H-3.15A-AP](#) [SR-5H-3.15A-BK](#) [SR-5H-6.3A-AP](#) [SR-5H-6.3A-BK](#) [SR-5H-1.25A-APH](#) [SR-5H-1.6A-APH](#) [SR-5H-2.5A-APH](#) [SR-5H-3.15A-APH](#) [SR-5H-6.3A-APH](#)