






This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for the manufacture or sale by anyone other than Amphenol Corporation without its prior consent, and that no right is granted to disclose or to use any information in this document.



Specifications:

Current Rating: 1.0A AC/DC
Voltage Rating: 230V AC/DC
Contact Resistance: 20m ohm. Max.
Insulation Resistance: 1000M ohm. Min.
Withstanding Voltage: 500V AC For One Minute
Operating Temperature Range: -40°C ~ +105°C
Material and Finish
Insulator: High Temp. Plastic (UL94V-0)
Contact: Phosphor Bronze
Finish: Tin Plated


How to Order

TMM-X-X-XX-X

Type	Packaging
1-IDC Male	1 - Tape & Reel
2-IDC Plug	2 - Tube
3-DIP Male Straight	3 - Bag
4-DIP Female Straight	
5-DIP Female R/A	
6-SMT Female Straight	

Number of Positions
04, 06, 08, 10, 12, 14,
16, 18, 20, 22, 24 or 26

Locking System
0-without lock
L-with lock



PCB Layout



TOLERANCE (mm)	APPROVALS	DATE	TITLE
X: ±0.3	Stephane	28/OCT/08	TMM Series
X.X: ±0.1	Rob	28/OCT/08	SMT Female
X.XX: ±0.05	Rob	28/OCT/08	
UNLESS OTHERWISE SPECIFIED			
UNIT	MM	SIZE	SCALE
		A4	N.A.
			Sheet 1 of 1
			REV
			C

AMPHENOL
Amphenol European
Design Center

TMM-6-0-XX-X