






FCIconnect.com


Copyright FCI

PRODUCT NUMBER
SEE TABLE




mat'l. code SEE NOTE 3				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HPC							
ltr		ecm no		dr		date		tolerances unless otherwise specified				title					
E		V40227		PDP		1/11/94		angles		linear		.XX ±.01/.3		INCH/MM		3 ROW R/A HEADER	
F		V90522		HTB		2/26/99						.XXX ±.005/.13				SOLDER TO BOARD, 0 G.P.	
G		V00262		JWS		1/25/00		0°±2°				.XXXX ±.0020/.051		scale 1:1			
H		V02768		LSS		11/21/00		enr		D. SHEAFFER		6/05/91		FCI		dwg no	
J		V05-0756		DAI		10/07/05		dgr		S. CLARK		6/05/91				sheet 1 of 3 size	
K		V05-1040		HTB		11/14/05		chr		S. CLARK		6/05/91				50119	
L		M06-0255		MNR		7/06/06		appd		S. CLARK		6/05/91				A3	
sheet		revision		L		L		L								type	
index		sheet		1		2		3								Product Customer Drawing	

form: A3



SECTION X-X



form: A3	1	2	3	4	5	6
----------	---	---	---	---	---	---

PRODUCT NUMBER	NUMBER OF POSITIONS SEE NOTE 2	TAIL LENGTH REF.	TERMINAL PLATING
50119 - 1YYYH	YYY	.180/4.57	30μ"/.76μ GOLD
50119 - 1YYYJ	YYY	.120/3.05	30μ"/.76μ GOLD
50119 - 3YYYH	YYY	.180/4.57	50μ"/1.27μ GOLD
50119 - 3YYYJ	YYY	.120/3.05	50μ"/1.27μ GOLD
50119 - 5YYYH	YYY	.180/4.57	30μ"/.76μ GXT
50119 - 5YYYHLF	YYY	.180/4.57	30μ"/.76μ GXT
50119 - 5YYYJ	YYY	.120/3.05	30μ"/.76μ GXT
50119 - 5YYYJLF	YYY	.120/3.05	30μ"/.76μ GXT

NOTES:

1. PRODUCT NUMBERING CODE:

50119 - X YYY Z LF

LEAD FREE (OPTIONAL)
TAIL LENGTH SEE TABLE
NO. OF POSITIONS SEE NOTE 2
PLATING SEE TABLE
BASE NUMBER

PRODUCT NUMBERING CODE FOR
SELECT LOAD PART NUMBERS:

50119 - XXYYY LF

LEAD FREE (OPTIONAL)
SEQUENCE NUMBER
ALWAYS 'XX'
BASE NUMBER

2. THIS PRODUCT IS CONFIGURED IN SIZES OF 6 THRU 80 COLUMNS IN INCREMENTS OF ONE.
i.e.: 6,7,8,9,.....78,79,80.

3. HOUSING MATERIAL: GLASS AND MINERAL FILLED
HIGH TEMP. THERMOPLASTIC. FLAME RETARDANT PER
UL94V-0. COLOR: BLACK.
PIN MATERIAL: PHOS. BRONZE

4. MANUFACTURE'S NAME, P/N, AND LOT CODE TO APPEAR ON
THIS SURFACE PER BUS-12-108.

5. LENGTH FORMULAS:

DIM "A" = .100/2.54 x NO. OF COLUMNS + .75/19.1

DIM "B" = .100/2.54 x NO. OF COLUMNS + .450/11.43

DIM "C" = .100/2.54 x NO. OF COLUMNS - .100/2.54

6. THIS PRODUCT (WITH "LF" SUFFIX) MEETS EUROPEAN UNION DIRECTIVES
AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
7. THIS HOUSING WILL WITHSTAND EXPOSURE TO 260° C PEAK TEMPERATURE
FOR 10-30 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE
REFLOW OVEN.

mat'l. code SEE NOTE 3			surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HPC
ltr	ecn	no	dr	date	tolerances unless otherwise specified	title
L					linear .XX ±.01/.3	3 ROW R/A HEADER
					linear .XXX ±.005/.13	SOLDER TO BOARD, 0 G.P.
					linear .XXXX ±.0020/.051	
			dr	D. SHEAFFER	6/05/91	dwg no
			enr	S. CLARK	6/05/91	sheet 3 of 3 size
			chr	S. CLARK	6/05/91	50119 A3
			appd	S. CLARK	6/05/91	type Product Customer Drawing
sheet index	revision sheet					