




Home: Crimp Housings &gt;

**Part Number: 49389-0392**

5.50mm Pitch Wire-to-Board Female Housing, 3 Circuits, UL94V-0, Red



Series image - Reference only

Status:	<b>OBSOLETE</b>
Replacement:	Contact Molex
Series:	49389
Category:	Crimp Housings

Go to [Part Detail](#) ▾[CHECK DISTRIBUTOR INVENTORY](#)[Add to My Parts](#)[Email this page](#)**Mates With Part(s):**  
[49388-0310](#) Wire-to-Board Header**Use With Part(s):**  
[35725-3401](#) Slip-in Wire-to-Wire Terminal**Product Environmental Compliance**[EU ELV](#):Product not active[EU RoHS](#):Product not active[EU RoHS Phthalates](#):Product not active[China RoHS](#):[REACH SVHC](#):Product not active[Low-Halogen Status](#):Product not active[EU RoHS Certificate of Compliance \(PDF\)](#)[Multiple Part Product Compliance Statements](#)

EU RoHS, REACH SVHC, &amp; Low-Halogen

[Multiple Part Industry Compliance Documents](#)

\*IPC 1752A Class C

\*IPC 1752A Class D

\*Molex Product Compliance Declaration

**Application Tooling****FAQ**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Previously Available Application Tooling**[Check our list of old tooling that used to be available for this part](#)Questions on Product Environmental Compliance? Email [ProductCompliance@molex.com](mailto:ProductCompliance@molex.com)Request Molex's CMRT from [conflictminerals@molex.com](mailto:conflictminerals@molex.com)**Part Detail**[COLLAPSE ALL](#)**▼ General**

Status	Obsolete
Category	Crimp Housings
Series	<a href="#">49389</a>
Application	Power
Comments	Polarized to Mating Part
Product Name	N/A
UPC	800756755526

**▼ Physical**

Circuits (maximum)	3
Color - Resin	Natural
Gender	Receptacle
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Net Weight	3.658/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.50mm
Pitch - Termination Interface	5.50mm
Polarized to Mating Part	Yes
Temperature Range - Operating	N/A

**▼ Electrical**

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	12.0A, 15.0A, 7.0A
-------------------------------	--------------------

**PRODUCTS****QUICK LINKS**[Antennas](#)  
[Application Tooling](#)  
[Cable Assemblies](#)  
[Connected Lighting](#)  
[Connectors](#)  
[Copper Flex](#)  
[Electrical Products](#)  
[Industrial Automation](#)  
[Membrane Switches](#)  
[Optical Solutions](#)  
[Printed Electronic Solutions](#)[Company Information](#)  
[Contact Molex](#)  
[Cross-Reference](#)  
[Koch Industries](#)  
[Industries](#)  
[Investor Relations](#)  
[Literature](#)  
[Molex Racing](#)  
[Press Room / Press Releases](#)  
[Product Index](#)  
[Sitemap](#)  
[Terms & Conditions](#)**RESOURCES**[Supply Chain Transparency](#)  
[Business Continuity](#)  
[Compliance](#)  
[ecocare](#)  
[Feedback | Help](#)  
[Jobs](#)  
[Legal | Trademarks](#)  
[Mobile Site](#)  
[Supplier Portal](#)  
[Privacy Policy](#)  
[Tradeshows](#)**STAY CONNECTED**