



PARTS LIST

| ITEM | QTY. | PART NO. | PART DESCRIPTION                |
|------|------|----------|---------------------------------|
| 1    | 1    | F040013  | P16 EE T11                      |
| 2    | 1    | F050402  | 50-004-02 (INCANDESCENT BULB)   |
| 3    | 1    | F050205  | 50-002-05(WHT LENS TRANSPARENT) |






RECOMMEND PANEL MOUNTING



1 0 1 0 2  
3 0 0 4  
a-(L)-b (+)

SPST  
CONTACT  
CONFIGURATION



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 5A@250V AC / 8A@125V AC
5. MECHANICAL LIFETIME: >2 MILLION OPERATIONS
6. TRAVEL: 3.0MM
7. CONTACT MATERIAL: COPPER ALLOY W/SILVER PLATING
8. LAMP VOLTAGE: 6V AC/ 200mA DC
9. ▲ DENOTES CRITICAL PARAMETER.

**E-SWITCH®**

| TITLE                                                                                                        |         |                         |         |
|--------------------------------------------------------------------------------------------------------------|---------|-------------------------|---------|
| P16EET11A/WHIT                                                                                               |         |                         |         |
| A                                                                                                            | 13363   | RELEASED FOR PRODUCTION | 8/11/03 |
| REV.                                                                                                         | ECN No. | DESCRIPTION             | DATE    |
| THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED |         |                         |         |
| SCALE 1.5:1                                                                                                  |         |                         |         |
| DATE 8/11/03                                                                                                 |         |                         |         |
| DR AR                                                                                                        |         |                         |         |
| DWG XF0564P                                                                                                  |         |                         |         |
| REV A                                                                                                        |         |                         |         |