


T-UP Series multi terminal snap-in

- **NEW** 50mm diameter sizes with five P. C. mount terminals
- **NEW** lengths up to 105mm
- Endurance rating of 3000 hours at 85°C
- 4 or 5 terminal mounting provides stability and keyed polarity
- Can vent construction



Rated Working Voltage:	16 ~ 250 VDC	350 ~ 500 VDC
Operating Temperature:	-40 ~ +85°C	-25 ~ +85°C
Nominal Capacitance:	1200 ~ 270000μF (±20% tolerance)	220 ~ 2700μF (±20% tolerance)
Endurance:	3000 hours at +85°C with maximum specified ripple current (see page 4)	

Part Number System



T-UP Standard Ratings

Cap. (μF)	Size (mm) D x L	Max 85°C R.C. (A _{rms})		Max 20°C E.S.R. (Ω)		Panasonic Part Number	Cap. (μF)	Size (mm) D x L	Max 85°C R.C. (A _{rms})		Max 20°C E.S.R. (Ω)		Panasonic Part Number
		120 Hz	10k~100kHz	120Hz	20kHz				120Hz	10k~100kHz	120Hz	20kHz	
16 VDC Working, 20 VDC Surge							25 VDC Working, 32 VDC Surge						
47000	35 x 40	7.47	8.59	0.021	0.019	ECET1CP473EA	33000	35 x 40	6.84	7.87	0.019	0.015	ECET1EP333EA
68000	35 x 50	9.05	10.41	0.018	0.017	ECET1CP683EA	47000	35 x 50	8.00	9.20	0.014	0.012	ECET1EP473EA
82000	35 x 63	10.02	11.52	0.016	0.015	ECET1CP823EA	56000	35 x 63	8.85	10.18	0.015	0.013	ECET1EP563EA
100000	35 x 80	11.00	12.65	0.015	0.014	ECET1CP104EA	68000	35 x 80	10.43	11.99	0.013	0.011	ECET1EP683EA
120000	35 x 105	12.81	14.73	0.014	0.013	ECET1CP124EA	100000	35 x 105	11.97	13.77	0.010	0.008	ECET1EP104EA
56000	40 x 40	9.05	10.41	0.022	0.021	ECET1CP563FA	39000	40 x 40	8.00	9.20	0.020	0.018	ECET1EP393FA
82000	40 x 50	10.29	11.83	0.016	0.015	ECET1CP823FA	56000	40 x 50	8.96	10.30	0.016	0.015	ECET1EP563FA
100000	40 x 63	11.36	13.06	0.018	0.017	ECET1CP104FA	68000	40 x 63	10.25	11.79	0.017	0.015	ECET1EP683FA
120000	40 x 80	12.42	14.28	0.017	0.016	ECET1CP124FA	100000	40 x 80	12.08	13.89	0.012	0.011	ECET1EP104FA
180000	40 x 105	14.85	17.08	0.013	0.012	ECET1CP184FA	150000	40 x 105	14.07	16.18	0.011	0.010	ECET1EP154FA
120000	50 x 50	13.17	15.15	0.014	0.013	ECEP1CP124HA	82000	50 x 50	12.29	14.13	0.016	0.015	ECEP1EP823HA
150000	50 x 63	14.40	16.56	0.012	0.011	ECEP1CP154HA	100000	50 x 63	13.45	15.47	0.014	0.013	ECEP1EP104HA
180000	50 x 80	15.69	18.04	0.011	0.010	ECEP1CP184HA	120000	50 x 80	15.29	17.58	0.012	0.011	ECEP1EP124HA
220000	50 x 92	16.73	19.24	0.010	0.009	ECEP1CP224HA	150000	50 x 92	16.01	18.41	0.011	0.010	ECEP1EP154HA
270000	50 x 105	17.79	20.46	0.009	0.008	ECEP1CP274HA	180000	50 x 105	16.89	19.42	0.010	0.009	ECEP1EP184HA
35 VDC Working, 44 VDC Surge							50 VDC Working, 63 VDC Surge						
22000	35 x 40	6.10	7.02	0.026	0.020	ECET1VP223EA	15000	35 x 40	6.44	7.41	0.028	0.021	ECET1HP153EA
33000	35 x 50	7.15	8.22	0.018	0.014	ECET1VP333EA	22000	35 x 50	7.57	8.71	0.021	0.017	ECET1HP223EA
39000	35 x 63	7.94	9.13	0.015	0.012	ECET1VP393EA	27000	35 x 63	8.31	9.56	0.018	0.015	ECET1HP273EA
47000	35 x 80	9.53	10.96	0.014	0.011	ECET1VP473EA	33000	35 x 80	9.23	10.61	0.015	0.012	ECET1HP333EA
68000	35 x 105	10.62	12.21	0.010	0.008	ECET1VP683EA	47000	35 x 105	10.27	11.81	0.014	0.011	ECET1HP473EA
27000	40 x 40	6.84	7.87	0.021	0.017	ECET1VP273FA	18000	40 x 40	6.94	7.98	0.023	0.017	ECET1HP183FA
39000	40 x 50	7.98	9.18	0.017	0.014	ECET1VP393FA	27000	40 x 50	8.12	9.34	0.018	0.015	ECET1HP273FA
47000	40 x 63	9.58	11.02	0.016	0.013	ECET1VP473FA	33000	40 x 63	9.10	10.47	0.018	0.014	ECET1HP333FA
56000	40 x 80	10.30	11.85	0.015	0.012	ECET1VP563FA	39000	40 x 80	10.12	11.64	0.015	0.012	ECET1HP393FA
82000	40 x 105	12.02	13.82	0.012	0.009	ECET1VP823FA	56000	40 x 105	11.47	13.19	0.012	0.009	ECET1HP563FA
56000	50 x 50	10.94	12.58	0.015	0.012	ECEP1VP563HA	33000	50 x 50	10.48	12.05	0.018	0.014	ECEP1HP333HA
68000	50 x 63	11.93	13.72	0.013	0.011	ECEP1VP683HA	47000	50 x 63	11.54	13.27	0.013	0.010	ECEP1HP473HA
82000	50 x 80	13.06	15.02	0.012	0.010	ECEP1VP823HA	56000	50 x 80	12.46	14.33	0.012	0.009	ECEP1HP563HA
100000	50 x 92	13.97	16.07	0.011	0.009	ECEP1VP104HA	68000	50 x 92	13.17	15.15	0.011	0.009	ECEP1HP683HA
120000	50 x 105	14.86	17.09	0.010	0.008	ECEP1VP124HA	82000	50 x 105	13.87	15.95	0.011	0.008	ECEP1HP823HA

T-UP Standard Ratings (continued)

Cap. (μ F)	Size (mm) D x L	Max. 85°C R.C. (A_{rms})		Max. 20°C E.S.R. (Ω)		Panasonic Part Number
		120 Hz	10k~100kHz	120Hz	20kHz	
63 VDC Working, 79 VDC Surge						
10000	35 x 40	6.52	7.50	0.041	0.033	ECET1JP103EA
12000	35 x 50	7.15	8.22	0.035	0.028	ECET1JP123EA
15000	35 x 63	7.71	8.87	0.028	0.022	ECET1JP153EA
18000	35 x 80	9.41	10.82	0.023	0.018	ECET1JP183EA
27000	35 x 105	10.38	11.94	0.015	0.012	ECET1JP273EA
12000	40 x 40	7.15	8.22	0.035	0.028	ECET1JP123FA
15000	40 x 50	7.53	8.66	0.033	0.027	ECET1JP153FA
18000	40 x 63	9.25	10.64	0.028	0.022	ECET1JP183FA
27000	40 x 80	9.97	11.47	0.018	0.015	ECET1JP273FA
33000	40 x 105	11.76	13.52	0.015	0.012	ECET1JP333FA
27000	50 x 50	10.86	12.49	0.018	0.015	ECEP1JP273HA
33000	50 x 63	11.67	13.42	0.017	0.013	ECEP1JP333HA
47000	50 x 80	12.78	14.70	0.013	0.010	ECEP1JP473HA
51000	50 x 92	13.34	15.34	0.012	0.010	ECEP1JP513HA
56000	50 x 105	13.93	16.02	0.012	0.009	ECEP1JP563HA
80 VDC Working, 100 VDC Surge						
6800	35 x 40	5.16	5.93	0.046	0.035	ECET1KP682EA
8200	35 x 50	5.83	6.70	0.038	0.029	ECET1KP822EA
10000	35 x 63	6.38	7.34	0.033	0.025	ECET1KP103EA
12000	35 x 80	6.92	7.96	0.028	0.021	ECET1KP123EA
22000	35 x 105	9.86	11.34	0.015	0.011	ECET1KP223EA
8200	40 x 40	5.83	6.70	0.038	0.029	ECET1KP822FA
10000	40 x 50	6.56	7.54	0.033	0.025	ECET1KP103FA
12000	40 x 63	7.29	8.38	0.028	0.021	ECET1KP123FA
15000	40 x 80	8.93	10.27	0.024	0.018	ECET1KP153FA
27000	40 x 105	11.35	13.05	0.015	0.012	ECET1KP273FA
18000	50 x 50	10.00	11.50	0.023	0.017	ECEP1KP183HA
22000	50 x 63	11.08	12.74	0.019	0.014	ECEP1KP223HA
27000	50 x 80	12.33	14.18	0.015	0.012	ECEP1KP273HA
33000	50 x 92	13.37	15.38	0.014	0.010	ECEP1KP333HA
39000	50 x 105	14.34	16.49	0.013	0.010	ECEP1KP393HA
100 VDC Working, 125 VDC Surge						
4700	35 x 40	5.13	5.90	0.071	0.049	ECET2AP472EA
6800	35 x 50	6.60	7.59	0.049	0.037	ECET2AP682EA
8200	35 x 63	7.05	8.11	0.040	0.030	ECET2AP822EA
10000	35 x 80	7.74	8.90	0.033	0.025	ECET2AP103EA
12000	35 x 105	8.57	9.86	0.028	0.021	ECET2AP123EA
5600	40 x 40	5.75	6.61	0.059	0.044	ECET2AP562FA
8200	40 x 50	7.28	8.37	0.040	0.030	ECET2AP822FA
10000	40 x 63	7.97	9.17	0.033	0.025	ECET2AP103FA
12000	40 x 80	8.65	9.95	0.028	0.021	ECET2AP123FA
15000	40 x 105	10.12	11.64	0.022	0.017	ECET2AP153FA
10000	50 x 50	8.82	10.14	0.033	0.025	ECEP2AP103HA
15000	50 x 63	10.07	11.58	0.022	0.017	ECEP2AP153HA
18000	50 x 80	11.00	12.65	0.018	0.014	ECEP2AP183HA
22000	50 x 92	11.76	13.52	0.015	0.011	ECEP2AP223HA
27000	50 x 105	12.53	14.41	0.014	0.010	ECEP2AP273HA
200 VDC Working, 250 VDC Surge						
1800	35 x 40	4.32	6.05	0.120	0.060	ECET2DP182EA
2200	35 x 50	4.92	6.89	0.098	0.054	ECET2DP222EA
2700	35 x 63	5.50	7.70	0.080	0.044	ECET2DP272EA
3300	35 x 80	6.44	9.02	0.065	0.036	ECET2DP332EA
5600	35 x 105	8.90	12.46	0.038	0.021	ECET2DP562EA
2200	40 x 40	4.92	6.89	0.098	0.054	ECET2DP222FA
2700	40 x 50	5.41	7.57	0.080	0.044	ECET2DP272FA
3300	40 x 63	6.32	8.85	0.065	0.036	ECET2DP332FA
4700	40 x 80	8.38	11.73	0.046	0.025	ECET2DP472FA
6800	40 x 105	8.65	12.11	0.032	0.017	ECET2DP682FA
3900	50 x 50	8.22	9.45	0.055	0.030	ECEP2DP392HA
4700	50 x 63	9.32	13.05	0.046	0.025	ECEP2DP472HA
6800	50 x 80	11.41	15.97	0.032	0.017	ECEP2DP682HA
7500	50 x 92	12.28	17.19	0.029	0.016	ECEP2DP752HA
8200	50 x 105	13.16	18.42	0.026	0.014	ECEP2DP822HA
250 VDC Working, 300 VDC Surge						
1200	35 x 40	3.32	4.65	0.166	0.083	ECET2EP122EA
1500	35 x 50	4.04	5.66	0.133	0.066	ECET2EP152EA
1800	35 x 63	4.49	6.29	0.111	0.055	ECET2EP182EA
2200	35 x 80	4.94	6.92	0.090	0.045	ECET2EP222EA
3900	35 x 105	7.47	10.46	0.051	0.026	ECET2EP392EA
1500	40 x 40	4.04	5.66	0.133	0.066	ECET2EP152FA
1800	40 x 50	4.49	6.29	0.111	0.055	ECET2EP182FA
2200	40 x 63	4.94	6.92	0.090	0.045	ECET2EP222FA
3300	40 x 80	7.00	9.80	0.060	0.030	ECET2EP332FA
4700	40 x 105	8.88	12.43	0.042	0.021	ECET2EP472FA
2700	50 x 50	6.77	7.79	0.074	0.037	ECEP2EP272HA
3300	50 x 63	7.79	10.91	0.060	0.030	ECEP2EP332HA
4700	50 x 80	9.65	13.51	0.042	0.021	ECEP2EP472HA
5600	50 x 92	10.80	15.12	0.036	0.018	ECEP2EP562HA
6800	50 x 105	12.16	17.02	0.029	0.015	ECEP2EP682HA
350 VDC Working, 400 VDC Surge						
470	35 x 40	2.40	3.36	0.388	0.175	ECET2VP471EA
680	35 x 50	2.96	4.14	0.366	0.165	ECET2VP681EA
1000	35 x 63	3.80	5.32	0.249	0.112	ECET2VP102EA
1200	35 x 80	4.42	6.19	0.207	0.093	ECET2VP122EA
1800	35 x 105	5.79	8.11	0.138	0.062	ECET2VP182EA
680	40 x 40	2.96	4.14	0.366	0.165	ECET2VP681FA
1000	40 x 50	3.80	5.32	0.249	0.112	ECET2VP102FA
1200	40 x 63	4.42	6.19	0.207	0.093	ECET2VP122FA
1800	40 x 80	5.85	8.19	0.138	0.062	ECET2VP182FA
2200	40 x 105	6.91	9.67	0.113	0.051	ECET2VP222FA
1200	50 x 50	5.18	5.96	0.207	0.093	ECEP2VP122HA
1500	50 x 63	6.01	8.41	0.166	0.075	ECEP2VP152HA
1800	50 x 80	6.89	9.65	0.138	0.062	ECEP2VP182HA
2200	50 x 92	7.79	10.91	0.113	0.051	ECEP2VP222HA
2700	50 x 105	8.80	12.32	0.092	0.041	ECEP2VP272HA
400 VDC Working, 450 VDC Surge						
470	35 x 40	2.39	3.35	0.388	0.136	ECET2GP471EA
560	35 x 50	2.72	3.81	0.326	0.114	ECET2GP561EA
820	35 x 63	3.55	4.97	0.222	0.078	ECET2GP821EA
1200	35 x 80	4.52	6.33	0.152	0.053	ECET2GP122EA
1500	35 x 105	5.44	7.62	0.122	0.043	ECET2GP152EA
560	40 x 40	2.69	3.77	0.326	0.114	ECET2GP561FA
820	40 x 50	3.38	4.73	0.222	0.078	ECET2GP821FA
1200	40 x 63	4.52	6.33	0.152	0.053	ECET2GP122FA
1500	40 x 80	5.50	7.70	0.122	0.043	ECET2GP152FA
1800	40 x 105	6.53	9.14	0.101	0.035	ECET2GP182FA
1000	50 x 50	4.76	5.47	0.199	0.080	ECEP2GP102HA
1200	50 x 63	5.47	7.66	0.166	0.066	ECEP2GP122HA
1500	50 x 80	6.47	9.06	0.133	0.053	ECEP2GP152HA
1800	50 x 92	7.35	10.29	0.111	0.044	ECEP2GP182HA
2200	50 x 105	8.43	11.80	0.090	0.036	ECEP2GP222HA
450 VDC Working, 500 VDC Surge						
330	35 x 40	2.01	2.81	0.553	0.249	ECET2WP331EA
470	35 x 50	2.53	3.54	0.423	0.233	ECET2WP471EA
560	35 x 63	2.90	4.06	0.355	0.195	ECET2WP561EA
820	35 x 80	3.78	5.29	0.243	0.133	ECET2WP821EA
1200	35 x 105	4.80	6.72	0.166	0.091	ECET2WP122EA
470	40 x 40	2.53	3.54	0.423	0.233	ECET2WP471FA
680	40 x 50	3.15	4.41	0.293	0.161	ECET2WP681FA
820	40 x 63	3.70	5.18	0.243	0.133	ECET2WP821FA
1200	40 x 80	4.84	6.78	0.166	0.091	ECET2WP122FA
1500	40 x 105	5.81	8.13	0.133	0.073	ECET2WP152FA
820	50 x 50	4.31	4.96	0.263	0.145	ECEP2WP821HA
1000	50 x 63	4.96	6.94	0.216	0.119	ECEP2WP102HA
1200	50 x 80	5.71	7.99	0.180	0.099	ECEP2WP122HA
1500	50 x 92	6.55	9.17	0.144	0.079	ECEP2WP152HA
1800	50 x 105	7.36	10.30	0.120	0.066	ECEP2WP182HA

T-UP Standard Ratings (continued)

Cap. (μ F)	Size (mm) D x L	Max. 85°C R.C. (A_{rms})		Max. 20°C E.S.R. (Ω)		Panasonic
		120 Hz	10k~100kHz	120Hz	20kHz	Part Number
500 VDC Working, 550 VDC Surge						
270	35 x 40	1.76	2.46	0.614	0.276	ECET2HP271EA
390	35 x 50	2.22	3.11	0.425	0.234	ECET2HP391EA
470	35 x 63	2.58	3.61	0.353	0.194	ECET2HP471EA
680	35 x 80	3.21	4.49	0.244	0.134	ECET2HP681EA
820	35 x 105	3.97	5.56	0.202	0.111	ECET2HP821EA
330	40 x 40	2.16	3.02	0.502	0.276	ECET2HP331FA
470	40 x 50	2.70	3.78	0.353	0.194	ECET2HP471FA
560	40 x 63	3.11	4.35	0.326	0.179	ECET2HP561FA
820	40 x 80	3.88	5.43	0.222	0.122	ECET2HP821FA
1200	40 x 105	5.90	8.26	0.152	0.084	ECET2HP122FA
560	50 x 50	3.52	4.05	0.355	0.195	ECEP2HP561HA
680	50 x 63	4.07	5.70	0.293	0.161	ECEP2HP681HA
1000	50 x 80	5.05	7.07	0.199	0.109	ECEP2HP102HA
1200	50 x 92	5.74	8.04	0.166	0.091	ECEP2HP122HA
1500	50 x 105	6.65	9.31	0.144	0.079	ECEP2HP152HA