






Transfer or duplication of this document as well as the utilisation or communication of its content are not permitted unless express consent is granted. Violations give rise to claims for damages. All rights reserved in case of patent, utility model or design patent registrations.



Technical Data:
Electrical
Pitch: 5.0mm
Voltage rating: 300V
Current rating: 16 Amps
Contact resistance: 5mΩ(max)
Withstanding Voltage: 2000VAC(1min) Test time=60sec/1pcs
Wire range: 14-24AWG
Wire strip length: 4.5-5mm
Mechanical:
Torque: 0.4n-m
Operating temperature: -40°C to +105°C
Soldering temperature:
Temperature= 250°C±10°C /5 seconds max
Safety approval:
RoHS Compliance

Part No.:
OSTTDXX0161

No. of Poles	COLOR
02 2 Poles	0: Black
03 3 Poles	2: Red
...	3: Orange
24 24 Poles	4: Yellow
	5: Green
	6: Blue (Standard)
	8: Grey

Nonstandard colors
Mins could apply

4	Screw	Steel / M2.5	M2.5/Zn plated	1xN
3	Solder pin	Copper Alloy	Tin plated	1xN
2	Spring	Stainless steel		1xN
1	Body	PA66 UL94V-0		1
ITEM	NAME OF PART	MATERIAL	NOTES	Q'TY
DWG.	DATE	UNITS:	MM	SHEET: 1 OF 1
CHK.	DATE	SCALE:	NONE 5:1 (:)	REV: A
APP.	DATE	TITLE:	OSTTD SERIES 5.0MM	X. ±0.50
		PART NO.	OSTTDXX0161	X.X ±0.30
		DWG NO.	OSTTDXX0161.DWG	X* ±1°

ON-SHORE TECHNOLOGY, INC.

REV	SIGN	DESCRIPTION	CHK.	DATE