


LEDs & INDICATORS


515 MPA Series

- Threaded body for panel thicknesses 0.5-3.5mm, panel cut-out 6.4mm diameter
- Stripped wire termination 164mm long, PVC
- LED, Filament 6-28V 30-40mA and Neons 125-240V 0.8-1mA, as standard
- Polycarbonate lens/body, chrome bezel, supplied with nut and shakeproof washer
- Red, green, amber, clear, blue and opal lens colour options as standard
- Maximum working temperature 105°C
- Custom wire lengths and specification to order



TYPE NO.	515	1	05 - XXXX	- T /	XXX
515 Series Indicator	515				
Lens Type	1				
Stripped wire 164mm long	05				
LED, black cathode & white anode wires	LED				
Filament 6V 40mA, white wire	640				
Filament 12V 35mA, yellow wire	1235				
Filament 14V 40mA, yellow wire	1440				
Filament 24V 35mA, green wire	24				
Filament 28V 30mA, green wire	28				
Neon 125V 1mA, blue wire	125				
Neon 240V 0.8mA, red wire	240				
Transparent lens	T				
Lens colour Red	RED				
Lens colour Green	GRN				
Lens colour Amber	AMB				
Lens colour Clear	CLR				
Lens colour Blue	BLU				
Lens colour Opal	OPL				

Body Dimensions



PCB
TERMINAL
BLOCKS

INTER-
CONNECTION

FUSES &
FUSE-
HOLDERS

LEDs &
INDICATORS

MINIATURE
SWITCHES

LIMIT &
SAFETY
SWITCHES

CONTROL
PRODUCTS

INTERFACE
MODULES &
SUPPORTS

RELAY
BASES

ENCLOSURES

BATTERIES

TRANS-
FORMERS