

# Customer Information Sheet

DRAWING No.: M83-LMTIM2NXX-0000-000

SHEET 2 OF 2

IF IN DOUBT - ASK






(C)

NOT TO SCALE



THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm

SPECIFICATIONS:  
MATERIAL:  
MOULDING = GLASS-FILLED PPS,  
UL94V-0, BLACK  
JACKSCREW = STAINLESS STEEL  
CONTACT = PHOSPHOR BRONZE  
FINISH:  
CONTACT = 0.75µ GOLD  
ELECTRICAL:  
CURRENT RATING AT 25°C = 3.0A MAX  
CURRENT RATING AT 85°C = 2.2A MAX  
CONTACT RESISTANCE = 25 mΩ MAX  
WORKING VOLTAGE = 120V AC/DC  
VOLTAGE PROOF = 360V AC/DC  
INSULATION RESISTANCE = 100 MΩ MIN  
MECHANICAL:  
DURABILITY = 500 OPERATIONS  
ENVIRONMENTAL:  
TEMPERATURE RANGE = -55°C TO +125°C  
PACKING:  
TRAY.  
BOARD MOUNT NUTS PACKED SEPERATELY  
IN BAG  
FOR COMPLETE SPECIFICATION, SEE  
COMPONENT SPECIFICATION C005XX  
(LATEST ISSUE)



SECTION X-X



ORDER CODE:  
**M83-LMTIM2NXX-0000-000**  
TOTAL No. OF CONTACTS  
18, 27, 36, 54, 60, 63, 72, 96

| DIMENSION                                                                                                           | CALCULATION                         |
|---------------------------------------------------------------------------------------------------------------------|-------------------------------------|
| DIM 'A'                                                                                                             | ((TOTAL No. OF CONTACTS /3) x2) +13 |
| DIM 'B'                                                                                                             | ((TOTAL No. OF CONTACTS /3) x2) +7  |
| DIM 'C'                                                                                                             | ((TOTAL No. OF CONTACTS /3) x2) -2  |
| EXAMPLE: CONNECTOR WITH 27 CONTACTS,<br>M83-LMTIM2N27-0000-000<br>DIM 'A' = 31.00, DIM 'B' = 25.00, DIM 'C' = 16.00 |                                     |

|                     |      |          |        |
|---------------------|------|----------|--------|
| SB                  | 2    | 01.02.12 | 11638  |
| NAME                | ISS. | DATE     | C/NOTE |
| APPROVED: S.BENNETT |      |          |        |
| CHECKED: S.FLOWER   |      |          |        |
| DRAWN: S. MCCULLAGH |      |          |        |
| CUSTOMER REF.:      |      |          |        |
| ASSEMBLY DRG:       |      |          |        |

**HARWIN**  
www.harwin.com  
technical@harwin.com

THIS DRAWING AND ANY  
INFORMATION OR DESCRIPTIVE  
MATTER SET OUT HEREON ARE  
CONFIDENTIAL AND COPYRIGHT  
PROPERTY OF THE HARWIN  
GROUP AND MUST NOT BE  
DISCLOSED, LOANED, COPIED  
OR USED FOR MANUFACTURING,  
TENDERING OR FOR ANY  
OTHER PURPOSE WITHOUT  
THEIR WRITTEN PERMISSION.

TOLERANCES  
X. = ±1mm  
X.X = ±0.25mm  
X.XX = ±0.10mm  
X.XXX = ±0.01mm  
ANGLES = ±5°  
UNLESS STATED

MATERIAL:  
SEE ABOVE  
FINISH: SEE ABOVE  
S/AREA: mm<sup>2</sup>

TITLE: JACKSCREW DATAMATE  
3-ROW MALE VERTICAL PC TAIL  
ASSEMBLY  
DRAWING NUMBER:  
**M83-LMTIM2NXX-0000-000**  
SHT 2 OF 2