





Last Time Buy Date: 31 Mar 2018

Date of discontinuation: 30 Sep 2018

< List of part numbers with package codes >

LQH3NPN330MG0L, LQH3NPN330MG0K

Shape

 <p>(in mm)</p>	
L size	3.0 ±0.2mm
W size	3.0 ±0.2mm
T size	0.9 ±0.1mm
Size code in inch (mm)	1212 (3030)

Notes

When applied Rated current to the Products, Inductance will be within ±30% of nominal Inductance value.

When applied Rated current to the Products, temperature rise caused by self-generated heat shall be limited to 40°C max.

Keep the temperature (ambient temperature plus self-generation of heat) under 125°C.

References

Packaging code	Specifications	Minimum quantity
L	φ180mm Embossed taping	1500
K	φ330mm Embossed taping	6000
Mass (Typ.)		
1 piece		0.034g

Specifications

Inductance	33μH ±20%
Inductance test frequency	1MHz
Rated current (Isat) (Based on Inductance change)	250mA
Rated current (Itemp) (Based on Temperature rise)	345mA
Max. of DC resistance	2.52Ω
Avg. of DC resistance	2.1Ω±20%
Self resonance frequency (min.)	24MHz
Operating temperature range (Self-temperature rise is not included)	-40~85°C
Class of magnetic shield	Magnetic Resin
Series	LQH3NPN_G0

1 of 2

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

 **Attention**

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
2. This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

