

MemoryPrime 2MEGA MEMORY BUILT-IN

GDS-1000A-U is a general purpose 2-channel oscilloscope designed to meet diversified educational demands and basic industrial requirements. This series provides bandwidths ranging from 70MHz to 150MHz. Together with intuitive human machine interface design and 5.7 inch color TFT LCD, GDS-1000A-U allows users to enjoy better measurement experiences.

GDS-1000A-U series offers dual sampling modes, 1GSa/s Real-Time and 25GSa/s Equivalent sampling rates, giving users a more flexible option to process incoming signals. With fast waveform process capability, more advanced triggering functions, and 2.5Kg light-weight design, GDS-1000A-U is a very capable oscilloscope to enhance users' returns on their investments in terms of price versus performance. GDS-1000A-U is also viewed as a replacement of analog oscilloscope. With its good functionality and capability, GDS-1000A-U can satisfy diversified educational demands as well as fulfill industrial basic requirements in servicing, maintenance, or production.

GDS-1000A-U also provides great accessibility through its USB Host and Device ports. Via USB Device port, user can easily build a remote control program to manipulate the machine. Via USB Host port, user is capable of not only storing data directly into flash disk for further analysis but also activating data logging function to monitor waveform data in designated time sequence.

Easy to use

Several acquisition mode and 27 auto measurement functions help user to measure the accurate property of waveforms. The advanced auto-set function makes GDS-1000A-U Series catch waveform automatically and display waveform quickly. With arithmetic functions, FFT function keeps user being aware of the results by updating value immediately. Without almost extra-calculation GDS-1000A-U Series can provide sufficient information of testing.

USB Host & USB Device supported

A total of 15 waveforms could be saved into the internal memory for later recall and display, and 2 saved reference waveforms plus 2 live waveforms could be shown on the screen at the same time for comparison. USB Host mass storage and USB device port are supported, providing storage/transfer of measurement data and remote control for diversified solutions.

Guaranteed Protection


By providing the Global Lifetime Warranty Program for the GDS-1000A-U digital storage oscilloscope series, we believe you can have the same confidence we do in the quality of each GDS-1000A-U DSO. By purchasing a GDS-1000A-U you can be assured of a highly economical, low maintenance, quality DSO backed with the protection of the LifeTime Warranty program. For more details and applicable conditions regarding the LifeTime Service program, please visit the GW Instek or consult your nearest distributor.

GDS-1000A-U Series

FEATURES

- 150/100/70 MHz Bandwidth, 2 Input Channels
- 1GSa/s Real-Time and 25GSa/s Equivalent-Time Sampling Rate
- 2Mega Point Record Length
- 2mV~10V Vertical Scale
- 1ns~50s Horizontal Range
- Up to 27 Auto Measurements
- Versatile Math Function: +, -, ×, ÷, FFT, FFTrms, Zoom FFT
- 5.7" Color TFT LCD Display
- USB Host & Device Ports
- Go/NoGo Function
- Data Logger
- Limited Lifetime Warranty

GDB-02 Oscilloscope Education and Training Kit



APPLICATIONS

- Laboratories and Educational Facilities
- Product Testing and Quality Assurance
- Service Operation and Post-Sales Support
- Product Development and Debugging

SPECIFICATIONS

		GDS-1072A-U	GDS-1102A-U	GDS-1152A-U
VERTICAL	Channels Bandwidth Rise Time Sensitivity Accuracy Input Coupling Input Impedance Polarity Maximum Input Waveform Signal Process Offset Range Bandwidth Limit	2 DC~70MHz(-3dB) <5ns Approx.	2 DC~100MHz(-3dB) <3.5ns Approx.	2 DC~150MHz(-3dB) <2.3ns Approx.
TRIGGER	Source Mode Coupling Sensitivity	2mV/div ~ 10V/div (1-2-5 increments) ± (3% x Readout + 0.1 div + 1mV) AC, DC & Ground 1MΩ ± 2%, ~15pF Normal & Invert 300V (DC+AC peak), CATII +, -, x, FFT, FFTrms, Zoom FFT 2mV/div ~ 50mV/div : ±0.4V ; 100mV/div ~ 500mV/div : ±4V ; 1V/div ~ 5V/div : ±40V ; 10V/div : ±300V 20MHz (-3dB)		
EXT TRIGGER	Range Sensitivity Input Impedance Maximum Input	±15V DC ~ 25MHz : ~ 50mV ; 25MHz ~ 70/100/150MHz : ~15mV 1MΩ ±2%, ~ 15pF 300V (DC+AC peak) , CATII		
HORIZONTAL	Range Modes Accuracy Pre-Trigger Post-Trigger	1ns/div ~ 50s/div (1-2.5-5 increments); ROLL : 50ms/div ~ 50s/div MAIN, WINDOW, WINDOW ZOOM, ROLL, X-Y ±0.01% 10 div maximum 1000 div		
X-Y MODE	X-Axis Input Y-Axis Input Phase Shift	Channel 1 Channel 2 ±3° at 100kHz		
SIGNAL ACQUISITION	Real-Time Sample Rate Equivalent Sample Rate Vertical Resolution Record Length Acquisition Mode Peak Detection Average	1GSa/s maximum 25GSa/s maximum 8 Bits 2Mega Points maximum Normal, Peak Detect, Average 10ns(500ns/div ~ 50s/div) 2, 4, 8, 16, 32, 64, 128, 256		
CURSORS AND MEASUREMENT	Voltage Measurement Time Measurement Delay Measurement Cursors Measurement Auto Counter	V _{pp} , V _{amp} , V _{avg} , V _{rms} , V _{hi} , V _{lo} , V _{max} , V _{min} , Rise Preshoot/Overshoot, Fall Preshoot/Overshoot Freq, Period, Rise Time, Fall Time, Positive Width, Negative Width, Duty Cycle Eight different delay measurement Voltage difference between cursors (ΔV) Time difference between cursors (ΔT), frequency measurement (1/ΔT) Resolution : 6 digits Accuracy : ±2% Signal Source: All available trigger source except the Video trigger mode		
ADJUSTABLE PROBE COMPENSATION SIGNAL	Frequency Range Duty Cycle Range	1kHz ~ 100kHz, 1kHz/STEP 5% ~ 95%, 5%/STEP		
CONTROL PANEL FUNCTION	Autoset Save Setup Save Waveform	Adjust Vertical VOLT/DIV, Horizontal TIME/DIV, and Trigger level automatically Up to 15 sets of measurement conditions 15 sets of waveform		
DISPLAY	TFT LCD Type Display Resolution Display Graticule Display Brightness	5.7 inch 234(Vertically)x 320 (Horizontally) Dots 8 x 10 divisions Adjustable		
INTERFACE	USB Device USB Host	USB1.1 & 2.0 full speed compatible Image (BMP) waveform data (CSV) and setup (SET)		
POWER SOURCE	Line Voltage Range	AC 100V ~ 240V, 48Hz ~ 63Hz, Auto selection		
MISCELLANEOUS	Go/NoGo Function Data Logger Multi-Language Menu Online Help	Available Available Available Available		
DIMENSIONS & WEIGHT		310(W) x 142 (H) x 140(D)mm, Approx. 2.5kg		

The specifications apply when the oscilloscope is powered on for at least 30 minutes under +20°C~+30°C.

Specifications subject to change without notice. DS-1000A-UGD1DH

ORDERING INFORMATION

GDS-1072A-U	70MHz, 2 channel, 1GSa/s & 2Mega Memory DSO
GDS-1102A-U	100MHz, 2 channel, 1GSa/s & 2Mega Memory DSO
GDS-1152A-U	150MHz, 2 channel, 1GSa/s & 2Mega Memory DSO

ACCESSORIES

User manual x1, Power cord x1
Probe GTP-070A-4 or equivalent:70MHz(10:1/1:1)Switchable passive probe for GDS-1072A-U(one per channel)
Probe GTP-100A-4 or equivalent:100MHz(10:1/1:1)Switchable passive probe for GDS-1102A-U(one per channel)
Probe GTP-150A-2 or equivalent:150MHz(10:1/1:1)Switchable passive probe for GDS-1152A-U(one per channel)

OPTIONAL ASSESSORIES

GTL-242 USB Cable, USB 2.0 Type A - Type B, 4P **GTL-110** Test Lead, BNC-BNC Heads
GSC-006 Soft Carrying Case

FREE DOWNLOAD

PC Software FreeWave software **Driver** USB driver; LabView Driver

Global Headquarters

GOOD WILL INSTRUMENT CO., LTD.

No.7-1, Jhongsing Road, Tucheng Dist., New Taipei City 236, Taiwan
T +886-2-2268-0389 F +886-2-2268-0639
E-mail: marketing@goodwill.com.tw

China Subsidiary

GOOD WILL INSTRUMENT (SUZHOU) CO., LTD.

NO. 69, Lushan Road, Snd, Suzhou Jiangsu 215011 China
T +86-512-6661-7177 F +86-512-6661-7277
E-mail: marketing@instek.com.cn

Malaysia Subsidiary

GOOD WILL INSTRUMENT (M) SDN. BHD.

27, Persiaran Mahsuri 1/1, Sunway Tunas,
11900 Bayan Lepas, Penang, Malaysia
T +604-6309988 F +604-6309989
E-mail: sales@goodwill.com.my

U.S.A. Subsidiary

INSTEK AMERICA CORP.

3661 Walnut Avenue Chino, CA 91710, U.S.A.
T +1-909-5918358 F +1-909-5912280
E-mail: sales@instekamerica.com

Japan Subsidiary

INSTEK JAPAN CORPORATION

4F, Prosper Bldg, 1-3-3 Iwamoto-Cho Chiyoda-Ku,
Tokyo 101-0032 Japan
T +81-3-5823-5656 F +81-3-5823-5655
E-mail: info@instek.co.jp

Korea Subsidiary

GOOD WILL INSTRUMENT KOREA CO., LTD.

Room No.805, Ace Hightech-City B/D 1 Dong,
Mullae-Dong 3Ga 55-20, Yeongduengpo-Gu, Seoul, Korea
T +82-2-3439-2205 F +82-2-3439-2207
E-mail: gwinstek@gwinstek.co.kr

GW INSTEK
Simply Reliable

www.gwinstek.com