





Copyright FCI.

Product number
SEE TABLE, SHEET 5



rev	ecn no	dr	date
A	S06-0112	CH	2006-03-31
B	S06-0374	DG	2006-12-21
C	S09-0279	YK	2009-09-07
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface 3.2 ASME Y14.5		tolerance std ASME Y14.5		projection 		MM 				
			TOLERANCES UNLESS OTHERWISE SPECIFIED										
Dr	G. HULL	2004-01-15	ANGULAR		LINEAR		0.X		±		size A4	Scale 2:1	
Eng	Y. K. LIM	2009-09-07					0.XX		±				
Chr	Y. K. LIM	2009-09-07	0°		±°		0.XXX		±		ECN	S09-0279	
Appr	JOEY NG	2009-09-07	Product family AirMax VS						Spec ref				
			title AirMax VS R/A HEADER ASSY PRESS-FIT, 150 POS, 32MM				dwg no 10037324				Rev. C		
			catalog no				-				CUSTOMER		sheet 1 of 5

REV F - 2006-04-17

PDM: Rev:C


STATUS: Released

Printed: Dec 01, 2010



Copyright FCI.

DESCRIPTION	DIM A	DIM B	DIM C
2-32MM MODULES PLACED END-TO-END	5.00	31.90 2X	32.00
1-30MM MODULE & 1-32MM MODULE PLACED END-TO-END	4.00	29.90 1X & 31.90 1X	31.00



DETAIL A


RECOMMENDED PCB LAYOUT
FOR DIFFERENTIAL APPLICATIONS
COMPONENT SIDE
(TWO ADJACENT FOOTPRINTS SHOWN)
NOTES 6 & 7

	title	AirMax VS R/A HEADER ASSY		dwg no	10037324		Rev. C
		PRESS-FIT, 150 POS, 32MM					
	catalog no	-		CUSTOMER		sheet 2 of 5	



Copyright FCI.

DESCRIPTION	DIM D	DIM E	DIM F
2-32MM MODULES PLACED END-TO-END	5.00	31.90 2X	32.00
1-30MM MODULE & 1-32MM MODULE PLACED END-TO-END	4.00	29.90 1X & 31.90 1X	31.00



DETAIL B

RECOMMENDED PCB LAYOUT
FOR SINGLE ENDED APPLICATIONS
COMPONENT SIDE
(TWO ADJACENT FOOTPRINTS SHOWN)
NOTES 6 & 7

	title	AirMax VS R/A HEADER ASSY		dwg no	10037324		Rev. C
		PRESS-FIT, 150 POS, 32MM					
	catalog no	-		CUSTOMER		sheet 3 of 5	



Copyright FCI.

A

B

C



D

A

B

C

D




title	AirMax VS R/A HEADER ASSY PRESS-FIT, 150 POS, 32MM	dwg no	10037324	Rev.	C
catalog no	-	CUSTOMER	sheet 4 of 5		

PART NUMBER	PRESS-FIT TAIL PLATING TYPE	SHORT DETECT CONTACT
10037324-101	TIN/LEAD ALLOY OVER NICKEL	NO
10037324-101LF	TIN OVER NICKEL (LEAD FREE)	
10037324-111	TIN/LEAD ALLOY OVER NICKEL	YES (SEE NOTE 13)
10037324-111LF	TIN OVER NICKEL (LEAD FREE)	

NOTES:

1. CONNECTOR MATERIALS:
HOUSING & RETAINER: HIGH TEMP THERMOPLASTIC, NATURAL, UL94V-0
IMLA PLASTIC: HIGH TEMP THERMOPLASTIC, BLACK, UL94V-0
CONTACT: COPPER ALLOY
2. CONTACT PLATING:
SEPARABLE INTERFACE:
PERFORMANCE-BASED PLATING, QUALIFIED TO MEET THE
REQUIREMENTS OF FCI PRODUCT SPECIFICATION GS-12-239
INCLUDING TELCORDIA GR-1217-CORE (NOVEMBER 1995)
CENTRAL OFFICE TEST SEQUENCE

PRESS-FIT TAILS: SEE TABLE
3. PRODUCT SPECIFICATION: GS-12-239
4. APPLICATION SPECIFICATION: GS-20-035
5. PRODUCT MARKING, (PART NUMBER & LOT CODE), ON THIS SURFACE
6. REFER TO CUSTOMER DRAWING 10035911 FOR INFORMATION REGARDING
PCB LAYOUT OF POWER AND GUIDE MODULES RELATIVE TO SIGNAL MODULES
7. POSITIONS F AND L OF ODD NUMBERED COLUMNS AND POSITIONS G AND M
OF EVEN NUMBERED COLUMNS CORRESPOND TO EARLY MATE HEADER PINS
8. THERE IS NO GROUND BUSSING WITHIN THE CONNECTOR SYSTEM
9. REFER TO CUSTOMER DRAWING 10045979 FOR INFORMATION
ON PCB HOLE DIAMETERS AND PLATING OPTIONS.
10. LEAD FREE PRODUCT MEETS EUROPEAN UNION DIRECTIVES &
OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
11. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C
PEAK TEMPERATURE FOR 40 SECONDS IN A CONVECTION,
INFRA-RED OR VAPOR PHASE REFLOW OVEN.
12. PACKAGING MEETS GS-14-920 LEAD FREE LABELING
SPECIFICATION.
13. MATING PIN H6 HAS 0.5mm LESS WIPE THAN THE
SHORTEST SIGNAL PIN.
14. A  SYMBOL WILL BE NEXT TO ANY DIMENSION,
VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH
THE CURRENT DRAWING REVISION.



title	AirMax VS R/A HEADER ASSY PRESS-FIT, 150 POS, 32MM	dwg no	10037324	Rev.	C
catalog no	-	CUSTOMER	sheet 5 of 5		