


HIGH VOLTAGE APPLICATION.
TELEPHONE APPLICATION.


MAXIMUM RATINGS (Ta=25℃)

CHARACTERISTIC		SYMBOL	RATING	UNIT
Collector-Base Voltage	MMBTA42	V_{CBO}	300	V
	MMBTA43		200	
Collector-Emitter Voltage	MMBTA42	V_{CEO}	300	V
	MMBTA43		200	
Emitter-Base Voltage		V_{EBO}	5.0	V
Collector Current		I_C	500	mA
Emitter Current		I_E	-500	mA
Collector Power Dissipation		P_C *	350	mW
Junction Temperature		T_j	150	℃
Storage Temperature		T_{stg}	-55~150	℃

P_C * : Package mounted on 99.5% alumina 10×8×0.6mm.



Marking



ELECTRICAL CHARACTERISTICS (Ta=25℃)

CHARACTERISTIC		SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Collector-Base Breakdown Voltage	MMBTA42	$V_{(BR)CBO}$	$I_C=100\mu A, I_E=0$	300	-	-	V
	MMBTA43			200	-	-	
Collector-Emitter Breakdown Voltage	MMBTA42	$V_{(BE)CEO}$	$I_C=1.0mA, I_B=0$	300	-	-	V
	MMBTA43			200	-	-	
DC Current Gain		* h_{FE}	$I_C=1.0mA, V_{CE}=10V$	40	-	-	
			$I_C=10mA, V_{CE}=10V$	40	-	-	
			$I_C=30mA, V_{CE}=10V$	40	-	-	
Collector-Emitter Saturation Voltage		$V_{CE(sat)}$	$I_C=20mA, I_B=2.0mA$	-	-	0.5	V
Base-Emitter Saturation Voltage		$V_{BE(sat)}$	$I_C=20mA, I_B=2.0mA$	-	-	0.9	V
Transition Frequency		f_T	$V_{CE}=20V, I_C=10mA, f=100MHz$	50	-	-	MHz
Collector Output Capacitance	MMBTA42	C_{ob}	$V_{CB}=20V, I_E=0, f=1MHz$	-	-	3.0	pF
	MMBTA43			-	-	4.0	

*Pulse Test : Pulse Width≤300μS, Duty Cycle≤2.0%

MMBTA42/43

