



[Home](#) [Applications](#) **[Products](#)** [Where To Buy](#) [What's New](#) [Support](#) [Service](#) [About Us](#)

[Accessories](#) > [Cases and Holsters](#) >

CXT170 Extreme Case



- Unbreakable, watertight, airtight, dustproof, chemical resistant and corrosion proof
- Buoyancy allows case to float in salt water with 3.6 kg (7.94 lb) load
- Includes an automatic purge valve for quick equalization after changes in atmospheric pressure
- Features an exclusive 6.4 mm (0.25 in) neoprene O-ring and ABS latches for excellent seal
- For use with the following test tools:
 - Air Quality: 922
 - Insulation Testers: 1503, 1507, 1577, 1587
 - Multimeters: 77 III, 77 IV, 114, 115, 116, 117, 177, 179
 - Process Tools: 712, 714, 715, 717, 718, 787
 - Temperature: 51, 51-2, 52, 52-2, 53, 53-2, 54, 54-2

Model Name	Description
CXT170	CXT170 Extreme Case

© 1995 - 2008 Fluke Corporation
[Privacy Statement](#)
[Disclaimer](#)