



REV.	C/N	DESCRIPTION	APPROVAL
A	2066	ISSUE NEW DWG.	
B	2079	ADDED NOTE B AND REVISED DIMS	
C		ADDED P600L-125-7.5/10/15	



NOTES:

- ALL DIMENSIONS ARE IN INCHES.
- LEADS TO BE COATED WITH SN60/PB40 SOLDER.
- PRIOR TO SK-406 LEAD FORMING, ALL FUSES SHALL BE SCREENED PER THE GROUP A SCREENING REQUIREMENTS OF THE P600L SPECIFICATION.
- GROUP B SCREENING TO BE CONDUCTED ON FUSES AFTER LEAD FORMING TO SK-406 REQUIREMENTS.
- PARTS TO BE MARKED PER THE P600L SPECIFICATION WITH P600L PART NUMBER.
- FUSE PACKAGING TO BE LABELED WITH SK-406 DESIGNATION.
- PART ORDERING INFORMATION:
EXAMPLE: P600L-72-7.5 ORDERED AS SK406-72-7.5.
- GROUP B, SOLDERABILITY TESTING, TO BE CONDUCTED PRIOR TO TERMINAL STRENGTH AND OVERLOAD CURRENT TESTING.

	A		B		C		D		E		F		G	
P600L FIG.	MIN.	MAX.	MIN.	MAX.	MIN.	MAX.	MIN.	MAX.	MIN.	MAX.	MIN.	MAX.	MIN.	MAX.
FIGURE 1	.145	.175	.024	.028	.120	.135	.480	.540	.260	.280	.260	.275	.130	.145
FIGURE 2	.190	.210	.049	.054	.120	.135	.610	.685	.360	.380	.400	.410	.190	.210
FIGURE 3	.190	.210	.063	.067	.120	.135	.610	.685	.360	.380	.400	.410	.190	.210
P600L-125-7.5 P600L-125-10.0 P600L-125-15.0	.335	.365	.049	.054	.120	.135	.640	.710	.590	.610	.415	.435	.290	.310



DRAWING TITLE : SK406 LEAD OPTION
FOR P600L STYLE FUSES

TOLERANCES UNLESS OTHERWISE SPECIFIED , .XX = N/A .XXX = N/A ANGLE = N/A °	DWG. NO 887108	REV. C
--	-------------------	-----------

DESIGNED :	SHEET 1 OF 1
DRAWN : J M 6-26-97	SCALE NONE
CHECKED : M. VL. 6-27-97	DRAWING SIZE A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AEM:](#)

[SK406-72-1.0\(EM\)](#) [SK406-72-4.0\(EM\)](#) [SK406-125-3.0](#)