


Class II power supply for DIN - rail mounting. Ref:

ESC-1.24.100S

24 W




1. Scatola 8 moduli in plastica ABS termoresistente.
Housing 8 module in heat resisting ABS plastic.
8M Gehäuse aus hitzebeständigem ABS-Plastik.
Boîtier 8 modules en plastique ABS thermorésistant.

2. Etichetta
Label
Typenschild
Etiquette

3. Morsetto primario
Input clamp
Eingangsklemme
Bornier primaire
4. Base per aggancio su binario DIN
Guide for DIN-rail mounting
Führung für Hutschiene
Embase pour fixation sur rail-IN

5. Inserto per fissaggio su binario DIN
Clip for DIN-rail mounting
Klemmriegel zur Hutschienenmontage
Ressort pour fixation sur rail-DIN

6. Morsetto secondario
Output clamp
Ausgangsklemme
Bornier secondaire



Norme di riferimento Standards Normen Normes	EN61558
Tensione d'ingresso Input voltage Eingangsspannung Tension d'entrée	230 Vac
Frequenza Frequency Frequenz Fréquence	50 - 60 Hz
Tensione d'uscita Output voltage Ausgangsspannung Tension de sortie	24 Vdc
Corrente nominale d'uscita Output current Nominaler Ausgangsstrom Courant nominal de sortie	1 A
Tensione a vuoto No-load voltage Leerlaufspannung Tension à vide	33,57 Vdc
Ondulazione residua Ripple Restwelligkeit Ondulation résiduelle	2,53 Vpp

Rigidità dielettrica Pri/Sec Dielectric strength Dielektrischer Widerstand Rigidité diélectrique Pri/Sec	3'750 Vac / 1 min.
Protezione Protection Schutz Protection	Sovraccarico / corto circuito Overload / short circuit Überlast / Kurzschluss Surcharge / court-circuit
Tipo protezione Protection type Schutzart Type de protection	Fuse 5 x 20
Temperatura d'utilizzo Temperature range Betriebstemperatur Température d'utilisation	- 20 °C / + 40 °C
Umidità relativa Relative humidity Relative Feuchtigkeit Humidité relative	5 % / 90 %
MTBF	100'000h