




TYPICAL PERFORMANCE



Horizontal: 2 MHz/div

Vertical (from top): Magnitude

10 dB/div

SPECIFICATION


Parameter	Min	Typ	Max	Units
Center Frequency (F_c) ¹	69.9	70	70.1	MHz
1 dB Bandwidth	6.5			MHz
3 dB Bandwidth	7.0			
40 dB Bandwidth			9.7	MHz
Ultimate Rejection ($0.5 * F_c$ to 62 MHz)	50			dB
Ultimate Rejection (78 to $1.5 * F_c$ MHz)	50			dB
Insertion Loss			22	dB
Source and Load Impedance		50		Ω
Passband Amplitude Ripple ²			0.8	dB p-p
Passband Phase Ripple ²			4.0	deg p-p
Passband Group Delay Ripple ^{2,3}			100	ns p-p
Measurement Temperature		23		° C
Operating Temperature Range ⁴	-30		+70	° C

Notes:

1. Floating reference. All specified bandwidths track with this frequency.
2. Defined over the interval bound by the first local maxima inward from the 3 dB frequencies.
3. A 1% smoothing aperture and an averaging factor of 16 may be used for this measurement.
4. Temperature coefficient of Frequency = -94ppm/°C nominal



PACKAGE OUTLINE



Units: mm

Pin Configuration:

Input: 1
Input Return: 14
Output: 8
Output Return: 7
Ground: 2,9

MATCHING CIRCUIT

None

ISO 9001
Registered

Micro Networks

Worldwide Headquarters: 324 Clark Street Worcester, MA 01606. tel: 508-852-5400 fax: 508-852-8456
European Sales Headquarters: Hertosingel 20 6214 AD Maastricht, Netherlands. tel: +31-43-32-70912 fax: +31-43-32-70715
www.micronetworks.com