


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	P1	REVISED PER ECO-16-001847	19JUL2016	NK	MZ



- 1

0.76µm [.000030] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH 1.27µm [.000050] MATTE TIN PLATE IN WIRE CRIMP AREA, BOTH OVER 0.76µm [.000030] MIN NICKEL PER QQ-N-290.
- 2


0.76µm [.000030] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH A UNIFORM GRADIENT TO 0.25µm [.000010] MIN GOLD PER MIL-G-45204 ON THE REMAINDER OVER 0.76µm [.000030] MIN NICKEL PER QQ-N-290.
- 3

GOLD PLATING NEED NOT APPEAR IN THIS AREA.
- 4

WIRE RANGE 26-30 AWG.
INSULATION RANGE 0.36[.014]-0.76[.030].
- 5

0.38µm [.000015] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN, 1.27µm [.000050] MIN TIN-LEAD PER MIL-T-10727 FOR A LENGTH OF 5.69 [.224] MIN ON OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL PER QQ-N-290 ON ENTIRE CONTACT.

OBSOLETE	5	1-66394-4	66405-8
	1	66394-4	66405-4
OBSOLETE	2	66394-1	66405-1
	BODY FINISH	STRIP P/N REF	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 7-30-91 R.SHIREY		 TE Connectivity						
		CHK 9-19-91 R.STONE								
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME SOCKET ASSEMBLY, LOOSE PIECE, TYPE III+						
	0 PLC ± -		APVD -							
	1 PLC ± -		PRODUCT SPEC -							
	2 PLC ± 0.13[.005]		-							
	3 PLC ± -		APPLICATION SPEC							
4 PLC ± -		ANGLES ± -	-		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
MATERIAL		FINISH		WEIGHT -		A2 00779 C-66405		-		
SEE CALLOUTS		SEE CALLOUTS		CUSTOMER DRAWING				SCALE 8:1	SHEET 1 of 1	REV P1