

MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

39HM1

CATALOG LISTING

PAGE 1 OF 1

RELEASE NO. PR-16849

REPLACES

39HM1

ISSUE 6

CHECK

REVISIONS

A 200109

WJC 13 MAR 00

B 0044639

MBH 16 OCT 08

RS

CHECK

SAV



13 MAR 00

CHECK

WJC 13 MAR 00

DRAWN

PTC/CAD 2D



NOTES

- 1 - FOR USE IN TEMPERATURE RANGE -85°F TO +400°F CONTINUOUS, -85°F TO +500°F INTERMITTENTLY
- 2 - SWITCH IS HERMETICALLY SEALED PER ENCLOSURE DESIGN SYMBOL 5 MIL-PRF-8805/8
- 3 - SWITCH CHARACTERISTICS TO BE MEASURED AT THIS POINT

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

CHARACTERISTICS	3	ELECTRICAL DATA			SCALE	2 : 1	DO NOT SCALE PRINT
OPERATING FORCE -----	6 OZ MAX	CONTACT ARRANGEMENT S P N C			UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ± WEIGHT		
RELEASE FORCE -----	1 OZ MIN	LINE VOLTAGE	INDUCTIVE LOAD	RESISTIVE LOAD			
DIFFERENTIAL TRAVEL -----	.025 MAX	28 VDC	1 AMP	3 AMP			
OVERTRAVEL -----	.050 MAX	115 VAC (400 CYCLE)	1 AMP	1 AMP			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[39HM1](#)