

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5018762444

Status:


Active

Overview:

iGrid Wire-to-Board Dual-Row System

Description:

2.00mm Pitch, iGrid PCB Header, Dual Row, Right-Angle, Through Hole, Tin (Sn) Plating, Positive Lock, 24 Circuits, Tray, 3.20mm PC Tail Length, Blue



Series image - Reference only

Documents:	
3D Model	Application Specification 5016460000-A00 (PDF)
Drawing (PDF)	Application Specification 5016460000-A01 (PDF)
3D Model (PDF)	Packaging Specification SPK-501876-001-001 (PDF)
Product Specification 5016461001-PS-001 (PDF)	Datasheet (PDF)
Product Specification PS-501646-001-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Headers
Series	501876
Application	Signal, Wire-to-Board
Overview	iGrid Wire-to-Board Dual-Row System
Product Name	iGrid
UPC	822350171526
Physical	
Breakaway	No
Circuits (Loaded)	24
Circuits (maximum)	24
Color - Resin	Blue
Durability (mating cycles max)	30
Flammability	94V-0
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Number of Rows	2
Orientation	Right Angle
PC Tail Length	3.20mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.20mm, 1.60mm
Packaging Type	Tray
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	No
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	2.0A
Voltage - Maximum	250V AC (RMS)/DC

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
501876 Series

Mates With
iGrid Receptacle Housing 501646

Material Info

Cross-Plant Material Status

LT

Reference - Drawing Numbers

Application Specification

5016460000-A00, 5016460000-A01

Packaging Specification

SPK-501876-001-001

Product Specification

5016461001-PS-001, PS-501646-001-001

Sales Drawing

5018760000-SD-000

This document was generated on 08/03/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION