







SECTION A-A

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.

| SIGN | DATE | DESCRIPTION | APPROVER |
|------|------|-------------|----------|
|      |      |             |          |

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

#### Material

- Terminal body
- (metal housing): Brass(CuZn)
- Terminal screw: Steel Zinc plating "-" slot type
- Contacts: Brass
- Surface of solder tail: Tin plated
- Insulator (housing): Thermoplastic (UL94V-0)

#### Electrical

- Voltage rating: 300VAC
- Current rating: 30A
- Wire range:
  - Solid wire(AWG): 10-24
  - Stranded wire(AWG): 10-24
- Torque(Lb-In): 8.9
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -30°C to +105°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: 

RoHS Compliant

PART NUMBER:

OSTT7XX0151

No. of Poles  
02 2 Poles  
03 3 Poles  
...  
24 24 Poles

COLOR  
0: Black  
5: Green (Standard)  
6: Blue  
8: Grey



|                       |                      |                              |                      |                                                                                       |                                         |                                                            |
|-----------------------|----------------------|------------------------------|----------------------|---------------------------------------------------------------------------------------|-----------------------------------------|------------------------------------------------------------|
| TITLE                 |                      | OSTT7 6.35mm Series - 45 Deg |                      |                                                                                       |                                         |                                                            |
| PART NO.              | OSTT7XX0151          |                              |                      | DWG NO.                                                                               | OSTT7XX0151.DWG                         |                                                            |
| APPROVED              | CHECKED              | DESIGNED                     | DRAWN                | CUST NO.                                                                              |                                         |                                                            |
| Shi Jun<br>2006.10.21 | Marvin<br>2006.10.21 | Marvin<br>2006.10.21         | Marvin<br>2006.10.21 |  | UNIT: mm<br>SCALE: NONE<br>SHEET: 01/01 | Tolerance<br>X. ±0.50<br>X.X ±0.30<br>X.XX ±0.10<br>X° ±1° |
|                       |                      |                              |                      | REV: F                                                                                |                                         |                                                            |