




| REV. | DESCRIPTION                      | DATE     | APPROVED |
|------|----------------------------------|----------|----------|
| D    | Engineering Update w/o Changes   | 02/27/04 | M. C.    |
| E    | Add [ -2 ] version to the series | 04/13/06 | M. C.    |
| F    | -1 version Obsolete              | 10/04/07 | M. C.    |
| G    | Updated (0.50") Height Dimension | 03/04/08 | M. C.    |
| H    | Removed Material Code            | 05/28/16 | J. C.    |



| PART NO.      |               |               |               | DIA           |
|---------------|---------------|---------------|---------------|---------------|
| H-275C SERIES | H-276C SERIES | H-277C SERIES | H-278C SERIES |               |
| H-275C-2      | H-276C-2      | H-277C-2      | H-278C-2      | .206 [5.23mm] |

|                                                      |                |                                                                                                                                                                 |  |
|------------------------------------------------------|----------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|--|
| STANDARD TOLERANCE<br>( UNLESS OTHERWISE SPECIFIED ) |                | <br>4 THOMAS, IRVINE, CA. 92618<br>TEL: (949) 951-8808 FAX: (949) 951-3974 |  |
| <u>DECIMALS</u>                                      | <u>ANGULAR</u> |                                                                                                                                                                 |  |
| .X ± .1                                              | X° ± 1°        |                                                                            |  |
| .XX ± .01                                            |                |                                                                                                                                                                 |  |
| .XXX ± .005                                          |                |                                                                                                                                                                 |  |
| DESIGNED: M. Chen                                    |                | DATE: 03/31/03                                                                                                                                                  |  |
| CHECKED: D. Green                                    |                | DATE: 03/31/03                                                                                                                                                  |  |
|                                                      |                | TITLE: BI-LEVEL T-1¾ (5mm) LED HOLDER<br>INTERLOCKING VARIABLE INSIDE DIAMETER                                                                                  |  |
|                                                      |                | PART NO: H-27XC-X                                                                                                                                               |  |
|                                                      |                | REVISION H                                                                                                                                                      |  |
|                                                      |                | CAGE CODE : 32559                                                                                                                                               |  |
|                                                      |                | SHEET # 1 OF 1                                                                                                                                                  |  |
| CAD GENERATED DOCUMENT. DO NOT MEASURE DRAWING.      |                |                                                                                                                                                                 |  |

2. MATERIAL: NYLON 6/6, 94V-0, BLACK.

1. GENERAL SPECIFICATIONS: BIVAR MOLDED COMPONENT SPECIFICATION BV00-E101.