



250mA LDO Linear Regulators with Current-Limiting Switch

General Description

The MAX4834/MAX4835 family of low-dropout (LDO) linear regulators feature an accurate current-limiting switch with an integrated FLAG or RESET function. These devices operate from 2.5V to 5.5V and deliver up to 250mA of load current at a preset output voltage. Preset output voltage levels are 1.8V/2.5V/2.8V/3.0V/3.3V.

The MAX4834/MAX4835 offer a programmable soft-start control function to eliminate false reset during startup. The MAX4834 provides a FLAG function to notify the system when the load current exceeds the limit. The MAX4835 provides a RESET function to notify the system when the output drops below the threshold. Additionally, reverse-current protection prevents current flowing from the output to the input. Other features include a low 90µA quiescent current, a 0.1µA shutdown current.

The MAX4834/MAX4835 are available in space-saving 6-pin SOT23 and TDFN packages. Each device is specified over the -40°C to +85°C extended temperature range. Contact factory for other programmed output voltage versions from 1.5V to 3.3V in 100mV increments.


For pin-compatible 100mA versions of this device, refer to the MAX4832/MAX4833. For pin-compatible 500mA versions of this device, refer to the MAX4836/MAX4837.

Applications

SDIO Ports and Devices	Notebook Computers
USB Ports and Devices	Cell Phones
PDAs and Palmtop Devices	GPS Systems

Pin Configurations

TOP VIEW



TDFN

() MAX4834ETTxyc ONLY.

Pin Configurations continued at end of data sheet.

Features

- ◆ Guaranteed Minimum 250mA Load Current
- ◆ Accurate Current Limit
- ◆ Preset Output Voltages: 1.8V/2.5V/2.8V/3.0V/3.3V
- ◆ 2.5V to 5.5V Supply Voltage Range
- ◆ Adjustable Soft-Start
- ◆ Low Dropout Voltage
- ◆ Thermal Shutdown
- ◆ Reverse-Current Protection
- ◆ Shutdown Output Discharge (MAX4835)
- ◆ Low 90µA Supply Current
- ◆ Ultra-Low 0.1µA Shutdown Current
- ◆ FLAG and Latch Off (MAX4834) or RESET (MAX4835)
- ◆ Tiny SOT23 and TDFN (3mm x 3mm) Packages

Ordering Information

PART	TEMP RANGE	PIN-PACKAGE
MAX4834EUTxy_-T*	-40°C to +85°C	6 SOT23-6
MAX4834ETTxyc_-T	-40°C to +85°C	6 TDFN-6
MAX4835EUTxy_dd-T*	-40°C to +85°C	6 SOT23-6
MAX4835ETTxyc_dd-T	-40°C to +85°C	6 TDFN-6

Note: "xy" are placeholders for the output voltage levels of the devices. Insert the values found in Table 1 at the end of this document in the place of "xy". The "_" is a placeholder for either the RESET or the FLAG feature. Insert "B" in the place of "_" for RESET and "C" for FLAG. "dd" is a placeholder for the reset timeout period. Insert the values found in Table 2 in the place of "dd." For example, MAX4835EUT18BD2 has a 1.8V output voltage, RESET feature, and a 30ms reset timeout period. Note that "dd" applies only to the devices with RESET option and does not apply to the devices with FLAG option. For devices with the FLAG option, leave dd blank. Standard versions require a minimum order increment of 2.5k units. Nonstandard versions must be ordered in 10k unit increments. Contact factory for availability.

*Future product—contact factory for availability.

Tables 1 and 2 and Selector Guide appear at end of data sheet.

MAX4834/MAX4835



Maxim Integrated Products 1

For pricing, delivery, and ordering information, please contact Maxim/Dallas Direct! at 1-888-629-4642, or visit Maxim's website at www.maxim-ic.com.

250mA LDO Linear Regulators with Current-Limiting Switch

ABSOLUTE MAXIMUM RATINGS

IN, $\overline{\text{SHDN}}$, FLAG, OUT to GND	-0.3V to +6V
RESET to GND	-0.3V to ($\text{VOUT} + 0.3\text{V}$)
SS to GND	-0.3V to ($\text{VIN} + 0.3\text{V}$)
IN to OUT	$\pm 6\text{V}$
OUT Short Circuit to GND	Continuous
All Pins ESD Handling (Human Body Model)	2kV

Continuous Power Dissipation ($T_A = +70^\circ\text{C}$)	
6-Pin SOT23 (derate 9.1mW/ $^\circ\text{C}$ above $+70^\circ\text{C}$)	727mW
6-Pin TDFN (derate 24.4mW/ $^\circ\text{C}$ above $+70^\circ\text{C}$)	1951.2mW
Operating Temperature Range	-40 $^\circ\text{C}$ to +85 $^\circ\text{C}$
Operating Junction Temperature Range	-40 $^\circ\text{C}$ to +125 $^\circ\text{C}$
Storage Temperature Range	-65 $^\circ\text{C}$ to +150 $^\circ\text{C}$
Lead Temperature (soldering, 10s)	+300 $^\circ\text{C}$

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

ELECTRICAL CHARACTERISTICS

($\text{VIN} = \text{VOUT} + 1\text{V}$, $\overline{\text{SHDN}} = \text{IN}$, $\text{COUT} = 3.3\mu\text{F}$, $T_A = -40^\circ\text{C}$ to +85 $^\circ\text{C}$, unless otherwise noted. Typical values are at $T_A = +25^\circ\text{C}$.) (Note 1)

PARAMETER	SYMBOL	CONDITIONS		MIN	TYP	MAX	UNITS
Operating Voltage	VIN			2.5	5.5		V
Input Undervoltage Lockout Threshold	VUVLO	VIN rising		2.00	2.25		V
Input Undervoltage Lockout Threshold Hysteresis				50			mV
Quiescent Current	IQ	$\overline{\text{SHDN}} = \text{IN}$, $\text{IOUT} = 0$		90	150		μA
		$\overline{\text{SHDN}} = \text{IN}$, $\text{IOUT} = 0$, $\text{VUVLO} < \text{VIN} < \text{VOUT}$ (nominal)		150			
		$\overline{\text{SHDN}} = \text{GND}$, $\text{IOUT} = 0$		0.1	2		
Dropout Voltage (Note 2)		$\text{IOUT} = 250\text{mA}$	$\text{TA} = +25^\circ\text{C}$	103	140		mV
			$\text{TA} = -40^\circ\text{C}$ to +85 $^\circ\text{C}$	165			
Output Voltage Accuracy		$\text{IOUT} = 1\text{mA}$ to 250mA, $\text{TA} = +25^\circ\text{C}$		-1.3	+1.3		$\%V_{\text{NOM}}$
		$\text{IOUT} = 1\text{mA}$ to 250mA, $\text{TA} = -40^\circ\text{C}$ to +85 $^\circ\text{C}$		-2	+2		
Output Current	IOUT			250			mA
Output Current Limit		$\text{VOUT} = 0\text{V}$		270	330		mA
Reverse Current at VIN		$\text{VOUT} = 5.5\text{V}$, $\text{VIN} = 0\text{V}$ to VOUT		0.1	2		μA
Soft-Start Time (Note 3)	tss	$\text{CSS} = \text{not connected}$		0.5	1	2.0	ms
		$\text{CSS} = 0.01\mu\text{F}$		4	10	15	
		$\text{CSS} = 0.1\mu\text{F}$		40	100	150	
Line Regulation (Note 4)		$\text{VOUT} + 0.5\text{V} < \text{VIN} < 5.5\text{V}$, $\text{ILOAD} = 100\mu\text{A}$	$\text{TA} = +25^\circ\text{C}$	-0.04	+0.02	+0.065	$\%V_{\text{NOM}}/V$
			$\text{TA} = -40^\circ\text{C}$ to +85 $^\circ\text{C}$	-0.05	+0.03	+0.08	
Load Regulation		$100\mu\text{A} < \text{ILOAD} < 250\text{mA}$, $\text{VIN} = \text{VOUT} + 1\text{V}$		1.3			$\%V_{\text{NOM}}$
Output Noise		10Hz to 100kHz, $\text{CSS} = 0.01\mu\text{F}$		70			μVRMS
SHUTDOWN INPUT ($\overline{\text{SHDN}}$)							
OUT Discharge Resistance in Shutdown (MAX4835)		$\overline{\text{SHDN}} = \text{GND}$		900			Ω
$\overline{\text{SHDN}}$ Input-Voltage High	V_{IH}			1.4			V
$\overline{\text{SHDN}}$ Input-Voltage Low	V_{IL}			0.5			V
$\overline{\text{SHDN}}$ Input Hysteresis				30			mV
$\overline{\text{SHDN}}$ Input Leakage Current		$\overline{\text{SHDN}} = \text{IN}$ or GND		-100	+100		nA

250mA LDO Linear Regulators with Current-Limiting Switch

ELECTRICAL CHARACTERISTICS (continued)

($V_{IN} = V_{OUT} + 1V$, $\overline{SHDN} = IN$, $C_{OUT} = 3.3\mu F$, $T_A = -40^\circ C$ to $+85^\circ C$, unless otherwise noted. Typical values are at $T_A = +25^\circ C$.) (Note 1)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
RESET OUTPUT (MAX4835)						
RESET Threshold	V_{RESET}		$0.85 \times V_{OUT}$	$0.875 \times V_{OUT}$	$0.90 \times V_{OUT}$	V
OUT Drop to RESET Delay (Note 5)	t_{OR}			35		μs
RESET Timeout Period	t_{RESET}	D1 timing option	2.5	3.75	5.0	ms
		D2 timing option	20	30	40	
		D3 timing option	150	225	300	
		D4 timing option	1200	1800	2400	
RESET Output-Voltage Low		$V_{OUT} \geq 1.0V$, $I_{SINK} = 50\mu A$, \overline{RESET} asserted		0.3		V
		$V_{OUT} \geq 1.5V$, $I_{SINK} = 3.2mA$, \overline{RESET} asserted			0.4	
RESET Output-Voltage High		$V_{OUT} \geq 2.0V$, $I_{SOURCE} \leq 500\mu A$, \overline{RESET} deasserted	$0.8 \times V_{OUT}$			V
FLAG OUTPUT (MAX4834)						
Blanking Time (Note 6)	t_{BLANK}	$V_{OUT} + 1V \leq V_{IN} \leq 5.5V$, $OUT = GND$	5	10	17	ms
Open-Drain \overline{FLAG} Output-Voltage Low		$I_{SINK} = 3.2mA$, \overline{FLAG} asserted, $V_{OUT} \geq 1.5V$			0.4	V
Open-Drain \overline{FLAG} Leakage Current		$V_{FLAG} = 5.5V$		0.01	1	μA
THERMAL PROTECTION						
Thermal-Shutdown Temperature		Junction temperature rising		+165		$^\circ C$
Thermal-Shutdown Hysteresis				15		$^\circ C$

Note 1: Parts are 100% tested at $+25^\circ C$. Limits across the full temperature range are guaranteed by design and correlation over the specified temperature range.

Note 2: The dropout voltage is measured from V_{IN} to V_{OUT} when V_{OUT} is 2% below its nominal value. The nominal output voltage is measured from V_{OUT} to GND when V_{IN} is 1V greater than V_{OUT} . Defined only for $V_{OUT} \geq 2.5V$.

Note 3: Soft-start time is defined as the time required for the output to rise from 10% of its nominal value to 90% of its nominal value.

Note 4: For $V_{OUT} < 2V$, V_{IN} must be above 2.5V.









Note 5: This is the maximum time OUT can be out of tolerance before a reset is issued. It is implemented to ensure that momentary output glitches do not trigger a reset condition.

Note 6: In startup mode, the blanking time counter is not started until the soft-start time has elapsed. The total time from startup to \overline{FLAG} issued is $t_{SS} + t_{BLANK}$.

250mA LDO Linear Regulators with Current-Limiting Switch

Typical Operating Characteristics









($V_{IN} = V_{OUT} + 1V$, $\overline{SHDN} = \text{IN}$, $C_{OUT} = 3.3\mu\text{F}$, $T_A = +25^\circ\text{C}$, unless otherwise noted.)



250mA LDO Linear Regulators with Current-Limiting Switch

Typical Operating Characteristics (continued)







($V_{IN} = V_{OUT} + 1V$, $\overline{SHDN} = IN$, $C_{OUT} = 3.3\mu F$, $T_A = +25^\circ C$, unless otherwise noted.)



250mA LDO Linear Regulators with Current-Limiting Switch

Typical Operating Characteristics (continued)

($V_{IN} = V_{OUT} + 1V$, $\overline{SHDN} = \text{IN}$, $C_{OUT} = 3.3\mu\text{F}$, $T_A = +25^\circ\text{C}$, unless otherwise noted.)



250mA LDO Linear Regulators with Current-Limiting Switch

Pin Description

PIN		NAME	FUNCTION
SOT23	TDFN		
1	1	IN	Regulator Power Input. Bypass IN to GND with a 0.1 μ F ceramic capacitor. Install the bypass capacitor as close to the device as possible.
2	2	GND	Ground
3	3	SHDN	Active-Low Shutdown Input. Drive SHDN low to shutdown the regulator. Drive SHDN high or connect to IN for normal operation.
4	4	FLAG (MAX4834)	Overcurrent Flag. Open-drain FLAG goes low when the device senses sustained current exceeding the current-limit threshold for a duration longer than the blanking time. FLAG is high when SHDN is low or the device is in thermal shutdown.
		RESET (MAX4835)	Active-Low Reset Output. Push-pull RESET goes low when the voltage at OUT is below the reset threshold or when the voltage at OUT is greater than IN. RESET is low when SHDN is low or the device is in thermal shutdown. After the reset condition terminates, RESET remains low for the duration of the reset timeout period.
5	5	SS	Soft-Start Control. Connect a capacitor, C_{SS} , from SS to GND to program the output rise time at startup. No capacitor from SS to GND gives 1ms output rise time at startup. See the soft-start response time plots in the <i>Typical Operating Characteristics</i> .
6	6	OUT	Regulator Output. Bypass OUT to GND with a 3.3 μ F or larger ceramic capacitor. The capacitor's ESR should be less than 0.2 Ω for stable operation.
—	EP	EP	Exposed Pad. EP is internally connected to GND. Externally connect EP to GND to provide a low thermal resistance path from the IC junction to the PC board.

Detailed Description

The MAX4834/MAX4835 are ultra-low quiescent current, low-dropout linear regulators with an integrated current limiter. These devices guarantee up to 250mA drive capabilities and regulate the preset output voltage.

The MAX4834 has a flag output that asserts low when the load current exceeds the current limit for more than the blanking time (t_{BLANK}). The MAX4835 has a reset output that asserts low when the regulator output voltage is below the reset threshold voltage (V_{RESET}). V_{RESET} is 87.5% of the nominal output voltage. Figure 1 shows the simplified functional diagram and Figure 2 shows the typical application circuits.

FLAG Output (MAX4834)

The open-drain FLAG output goes low and the LDO's pass transistor is latched off when the current in the pass transistor is at its output current limit for more than the blanking time (t_{BLANK}). Cycling IN or SHDN (high to low to high) brings the device out of its latched-off state and back into normal operation.

RESET Output (MAX4835)

The RESET output asserts when one of the following conditions occurs:

- The input voltage (V_{IN}) is below the input undervoltage lockout threshold (V_{UVLO}).
- The output voltage (V_{OUT}) is below the reset threshold (V_{RESET}).
- SHDN is pulled low.
- The device is in thermal shutdown.
- When $V_{OUT} > V_{IN}$.

RESET remains low for the reset timeout period (t_{RESET}) after reset conditions are terminated. There are four RESET timeout periods available as shown in the *Electrical Characteristics* table. RESET is available in a push-pull configuration as shown in the *Selector Guide*.

Shutdown

Pull SHDN low to shut down the LDO and reduce the quiescent current consumption of the device from 90 μ A to 0.1 μ A. In shutdown mode, the pass transistor, control circuit, and reference circuit are turned off. Connect SHDN to a supply voltage greater than V_{IH} to turn on the LDO.

MAX4834/MAX4835

250mA LDO Linear Regulators with Current-Limiting Switch




Figure 1. Functional Diagram




Figure 2. Typical Application Circuits

250mA LDO Linear Regulators with Current-Limiting Switch

Shutdown Discharge (MAX4835)

OUT discharges through a 900Ω internal resistor during shutdown mode.

Reverse OUT to IN Current

When the output voltage is greater than the input voltage, the internal pass transistor turns off. To avoid reverse-charging the input source, the current at IN is guaranteed to be below $3\mu A$ when $V_{OUT} \geq V_{IN}$.

Current Limit

The MAX4834/MAX4835 include an accurate internal current-limiting circuit. OUT can be shorted to ground indefinitely without damaging the part.

The MAX4834 latches off if the load current exceeds the current limit for more than the blanking time (see the *FLAG Output* section). During soft-start, the device does not latch off to an overload condition. During an overload condition, the MAX4835 holds the current at current limit until the thermal limit is reached. Once the junction temperature reaches $+165^\circ C$, thermal shutdown occurs.

Thermal Shutdown

When the junction temperature (T_J) exceeds $+165^\circ C$, the LDO's pass transistor turns off allowing the junction to cool. The LDO's pass transistor turns on again after the IC's junction temperature cools by $15^\circ C$, resulting in a pulsed output during continuous thermal overload conditions.

Soft-Start

During power-up, the soft-start ensures that the output ramps up slowly reducing inrush current peaks. See the soft-start response time plots in the *Typical Operating Characteristics*. The soft-start time (t_{SS}) is given by the following equation:

$$t_{SS} = C_{SS} \text{ (ms)}$$

where C_{SS} is in nF.

A soft-start capacitor (C_{SS}) of 10nF gives a 10ms t_{SS} . A 1ms minimum soft-start time is fixed internally to ensure that the output rises slowly even without any external capacitor at SS pin to ground. The device is in soft-start mode when either the voltage at IN or \overline{SHDN} is cycled high to low to high.

Applications Information

Capacitor Selection and Regulator Stability

For stable operation over the full temperature range and with load currents up to 250mA , use a $3.3\mu F$ (min) ceramic output capacitor with an $ESR < 0.2\Omega$. To reduce noise and improve load transient response, stability, and power-supply rejection, use larger output capacitor values such as $10\mu F$ (note that some ceramic capacitors exhibit large capacitance and ESR variation with temperature). X7R capacitors provide good performance over the $-40^\circ C$ to $+85^\circ C$ operating temperature range.

To improve power-supply rejection and transient response, use a $0.1\mu F$ capacitor between IN and GND. The MAX4834/MAX4835 remain stable with purely resistive loads or current loads up to 250mA .

15kV Operational ESD Protection

A $3.3\mu F$ or higher value ceramic capacitor from OUT to GND provides a 15kV (Human Body Model) protection at OUT. The ESR value of the capacitor should be less than 0.2Ω .

Reset Transient Immunity

The reset circuit is relatively immune to short duration, falling V_{OUT} transients. The *Typical Operating Characteristics* show a graph of the Maximum Transient Duration vs. Reset Threshold Overdrive for which reset is not asserted. The graph was produced using falling V_{OUT} transients starting at V_{OUT} and ending below the reset threshold by the magnitude indicated (reset threshold overdrive). The graph shows the maximum pulse width that a falling V_{OUT} transient can typically have without triggering the reset pulse. As the amplitude of the transient increases (i.e., goes further below the reset threshold), the maximum allowable pulse width decreases. Typically, a V_{OUT} transient that goes only 10mV below the reset threshold and lasts up to $54\mu s$ does not trigger a reset pulse.

Layout

When using the TDFN package, connect its exposed paddle to GND to provide a low thermal resistance path for heat transfer from the IC junction to the printed circuit board.

250mA LDO Linear Regulators with Current-Limiting Switch

Selector Guide

PART	PIN-PACKAGE	OUTPUT CURRENT (mA)	RESET OUTPUT CONFIGURATION	RESET (FLAG)	SHUTDOWN DISCHARGE	LATCH OFF
MAX4834EUTxyC-T	6 SOT23-6	250	Open-Drain	$\overline{\text{FLAG}}$	No	Yes
MAX4834ETTxyc-T	6 TDFN-6	250	Open-Drain	$\overline{\text{FLAG}}$	No	Yes
MAX4835EUTxyBdd-T	6 SOT23-6	250	Push-Pull	$\overline{\text{RESET}}$	Yes	No
MAX4835ETTxycBdd-T	6 TDFN-6	250	Push-Pull	$\overline{\text{RESET}}$	Yes	No

Suffix 'xy' in the part number stands for nominal output voltage. 1.8V, 2.5V, 2.8V, 3.0V, 3.3V are the standard options. For other voltages between 1.5V to 3.3V, contact factory.

Table 1. Standard Output Voltage Suffix Guide


xy	OUTPUT VOLTAGE (V)
18	1.8
25	2.5
28	2.8
30	3.0
33	3.3

Nonstandard output voltages from 1.5V to 3.3V are available in 100mV increments. Contact factory for availability.

Table 2. RESET Timeout Period Suffix Guide

dd	RESET TIMEOUT (ms)
D1	3.75
D2	30
D3	225
D4	1800

Pin Configurations (continued)



Chip Information

TRANSISTOR COUNT: 1575


PROCESS: BiCMOS

TDFN Exposed Pad: Connected to GND

250mA LDO Linear Regulators with Current-Limiting Switch

Package Information

(The package drawing(s) in this data sheet may not reflect the most current specifications. For the latest package outline information go to www.maxim-ic.com/packages.)



COMMON DIMENSIONS		
SYMBOL	MIN.	MAX.
A	0.70	0.80
D	2.90	3.10
E	2.90	3.10
A1	0.00	0.05
L	0.20	0.40
k	0.25 MIN.	
A2	0.20	REF.

PACKAGE VARIATIONS							
PKG. CODE	N	D2	E2	e	JEDEC SPEC	b	[(N/2)-1] x e
T633-1	6	1.50±0.10	2.30±0.10	0.95 BSC	MO229 / WEEA	0.40±0.05	1.90 REF
T833-1	8	1.50±0.10	2.30±0.10	0.65 BSC	MO229 / WEEC	0.30±0.05	1.95 REF
T1033-1	10	1.50±0.10	2.30±0.10	0.50 BSC	MO229 / WEED-3	0.25±0.05	2.00 REF
T1433-1	14	1.70±0.10	2.30±0.10	0.40 BSC	-----	0.20±0.03	2.40 REF
T1433-2	14	1.70±0.10	2.30±0.10	0.40 BSC	-----	0.20±0.03	2.40 REF

NOTES:

1. ALL DIMENSIONS ARE IN mm. ANGLES IN DEGREES.
2. COPLANARITY SHALL NOT EXCEED 0.08 mm.
3. WARPAGE SHALL NOT EXCEED 0.10 mm.
4. PACKAGE LENGTH/PACKAGE WIDTH ARE CONSIDERED AS SPECIAL CHARACTERISTIC(S).
5. DRAWING CONFORMS TO JEDEC MO229, EXCEPT DIMENSIONS "D2" AND "E2", AND T1433-1 & T1433-2.
6. "N" IS THE TOTAL NUMBER OF LEADS.

DALLAS SEMICONDUCTOR MAXIM


TITLE: PACKAGE OUTLINE, 6, 8, 10 & 14L, TDFN, EXPOSED PAD, 3x3x0.80 mm

APPROVAL: 21-0137 DOCUMENT CONTROL NO: REV: F 2/2

250mA LDO Linear Regulators with Current-Limiting Switch

Package Information (continued)

(The package drawing(s) in this data sheet may not reflect the most current specifications. For the latest package outline information go to www.maxim-ic.com/packages.)



SOT-23

Maxim cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim product. No circuit patent licenses are implied. Maxim reserves the right to change the circuitry and specifications without notice at any time.

12 **Maxim Integrated Products, 120 San Gabriel Drive, Sunnyvale, CA 94086 408-737-7600**