



# Through Hole Lamp Product Data Sheet LTL-1BEHJ-SS

Spec No.: DS20-2007-0119

Effective Date: 06/09/2012

Revision: A

**LITE-ON DCC**


**RELEASE**

BNS-OD-FC001/A4

## Features

- \* Lead (Pb) free product and RoHS compliant.
- \* Red and green chips are matched for uniform light output.
- \* Long life-solid state reliability.
- \* Low power consumption.
- \* I.C. compatible.

## Package Dimensions



| Part No.     | Lens           | Source Color       |
|--------------|----------------|--------------------|
| LTL-1BEHJ-SS | White Diffused | Red Orange / Green |

### Notes:

1. All dimensions are in millimeters (inches).
2. Tolerance is  $\pm 0.25\text{mm}(.010")$  unless otherwise noted.
3. Protruded resin under flange is 1.0mm(.04") max.
4. Lead spacing is measured where the leads emerge from the package.
5. Specification are subject to change without notice.
6. Pb Free on electrode pins coated by the soldering material 99.9% Sn.



# LITE-ON TECHNOLOGY CORPORATION

Property of Lite-On Only

## Absolute Maximum Ratings at $T_A=25^{\circ}\text{C}$

| Parameter                                                    | Red                                             | Green | Unit                   |
|--------------------------------------------------------------|-------------------------------------------------|-------|------------------------|
| Power Dissipation                                            | 100                                             | 100   | mW                     |
| Peak Forward Current<br>(1/10 Duty Cycle, 0.1ms Pulse Width) | 120                                             | 120   | mA                     |
| Continuous Forward Current                                   | 30                                              | 30    | mA                     |
| Derating Linear From $50^{\circ}\text{C}$                    | 0.4                                             | 0.4   | mA/ $^{\circ}\text{C}$ |
| Operating Temperature Range                                  | $-55^{\circ}\text{C}$ to $+100^{\circ}\text{C}$ |       |                        |
| Storage Temperature Range                                    | $-55^{\circ}\text{C}$ to $+100^{\circ}\text{C}$ |       |                        |
| Lead Soldering Temperature<br>[2.0mm(.078") From Body]       | $260^{\circ}\text{C}$ for 5 Seconds             |       |                        |

## Electrical Optical Characteristics at TA=25°C

| Parameter                | Symbol            | Color        | Min.       | Typ.       | Max.       | Unit | Test Condition                    |
|--------------------------|-------------------|--------------|------------|------------|------------|------|-----------------------------------|
| Luminous Intensity       | I <sub>v</sub>    | Red<br>Green | 5.6<br>5.6 | 19<br>19   | 60<br>60   | mcd  | I <sub>F</sub> = 20mA<br>Note 1,4 |
| Viewing Angle            | 2θ <sub>1/2</sub> | Red<br>Green |            | 75<br>75   |            | deg  | Note 2 (Fig.6)                    |
| Peak Emission Wavelength | λ <sub>p</sub>    | Red<br>Green |            | 630<br>565 |            | nm   | Measurement<br>@Peak (Fig.1)      |
| Dominant Wavelength      | λ <sub>d</sub>    | Red<br>Green | 615<br>568 | 625<br>573 | 632<br>578 | nm   | Note 3                            |
| Spectral Line Half-Width | Δλ                | Red<br>Green |            | 40<br>30   |            | nm   |                                   |
| Forward Voltage          | V <sub>F</sub>    | Red<br>Green |            | 2.0<br>2.1 | 2.6<br>2.6 | V    | I <sub>F</sub> = 20mA             |
| Reverse Current          | I <sub>R</sub>    | Red<br>Green |            |            | 100        | μA   | V <sub>R</sub> = 5V               |

Note: 1. Luminous intensity is measured with a light sensor and filter combination that approximates the CIE (Commission International De L'Eclairage) eye-response curve.

2. θ<sub>1/2</sub> is the off-axis angle at which the luminous intensity is half the axial luminous intensity.


3. The dominant wavelength, λ<sub>d</sub> is derived from the CIE chromaticity diagram and represents the single wavelength which defines the color of the device.

4. The I<sub>v</sub> guarantee should be added ±15% .


5. Reverse Voltage (V<sub>R</sub>) condition is applied for I<sub>R</sub> test only. The device is not designed for reverse operation.

**Typical Electrical / Optical Characteristics Curves**


(25°C Ambient Temperature Unless Otherwise Noted)




**Fig.1 Relative Intensity vs. Wavelength**




**Fig.2 FORWARD CURRENT VS. FORWARD VOLTAGE**




**Fig.3 FORWARD CURRENT DERATING CURVE**



**Fig.4 RELATIVE LUMINOUS INTENSITY VS. FORWARD CURRENT**



**Fig.5 LUMINOUS INTENSITY VS. AMBIENT TEMPERATURE**



**Fig.6 SPATIAL DISTRIBUTION**

## Bin Table Specifications

| Luminous Intensity (Red) |      | Unit : mcd @20mA |
|--------------------------|------|------------------|
| Bin code                 | Min. | Max.             |
| A                        | 5.6  | 12.6             |
| B                        | 12.6 | 29               |
| C                        | 29   | 60               |

Note: Tolerance of each bin limit is  $\pm 15\%$

| Luminous Intensity (Green) |      | Unit : mcd @20mA |
|----------------------------|------|------------------|
| Bin code                   | Min. | Max.             |
| A                          | 5.6  | 12.6             |
| B                          | 12.6 | 29               |
| C                          | 29   | 60               |

Note: Tolerance of each bin limit is  $\pm 15\%$

| Dominant Wavelength (Red - Green) |       | Unit : nm @20mA |
|-----------------------------------|-------|-----------------|
| Color                             | Min.  | Max.            |
| Red                               | 615.0 | 632.0           |
| Green                             | 568.0 | 578.0           |

Note: Tolerance of each bin limit is  $\pm 1$  nm

## CAUTIONS

### 1. Application

The LEDs described here are intended to be used for ordinary electronic equipment (such as office equipment, communication equipment and household applications). Consult Liteon's Sales in advance for information on applications in which exceptional reliability is required, particularly when the failure or malfunction of the LEDs may directly jeopardize life or health (such as in aviation, transportation, traffic control equipment, medical and life support systems and safety devices).

### 2. Storage

The storage ambient for the LEDs should not exceed 30°C temperature or 70% relative humidity.

It is recommended that LEDs out of their original packaging are used within three months.

For extended storage out of their original packaging, it is recommended that the LEDs be stored in a sealed container with appropriate desiccant or in desiccators with nitrogen ambient.

### 3. Cleaning

Use alcohol-based cleaning solvents such as isopropyl alcohol to clean the LEDs if necessary.

### 4. Lead Forming & Assembly

During lead forming, the leads should be bent at a point at least 3mm from the base of LED lens.

Do not use the base of the lead frame as a fulcrum during forming.

Lead forming must be done before soldering, at normal temperature.

During assembly on PCB, use minimum clinch force possible to avoid excessive mechanical stress.

### 5. Soldering

When soldering, leave a minimum of 2mm clearance from the base of the lens to the soldering point.

Dipping the lens into the solder must be avoided.

Do not apply any external stress to the lead frame during soldering while the LED is at high temperature.



Recommended soldering conditions :

| Soldering iron |                                | Wave soldering |              |
|----------------|--------------------------------|----------------|--------------|
| Temperature    | 350°C Max.                     | Pre-heat       | 100°C Max.   |
| Soldering time | 3 sec. Max.<br>(one time only) | Pre-heat time  | 60 sec. Max. |
|                |                                | Solder wave    | 260°C Max.   |
|                |                                | Soldering time | 5 sec. Max.  |

Note: Excessive soldering temperature and/or time might result in deformation of the LED lens or catastrophic failure of the LED. IR reflow is not suitable process for through hole type LED lamp product.

## 6. Drive Method

An LED is a current-operated device. In order to ensure intensity uniformity on multiple LEDs connected in parallel in an application, it is recommended that a current limiting resistor be incorporated in the drive circuit, in series with each LED as shown in Circuit A below.



(A) Recommended circuit

(B) The brightness of each LED might appear different due to the differences in the I-V characteristics of those LEDs

## 7. ESD (Electrostatic Discharge)

Static Electricity or power surge will damage the LED.

Suggestions to prevent ESD damage:

- Use a conductive wrist band or anti- electrostatic glove when handling these LEDs
- All devices, equipment, and machinery must be properly grounded
- Work tables, storage racks, etc. should be properly grounded
- Use ion blower to neutralize the static charge which might have built up on surface of the LEDs plastic lens as a result of friction between LEDs during storage and handing





# LITE-ON TECHNOLOGY CORPORATION

Property of Lite-On Only

## Suggested checking list :

### Training and Certification

1. Everyone working in a static-safe area is ESD-certified?
2. Training records kept and re-certification dates monitored?

### Static-Safe Workstation & Work Areas

1. Static-safe workstation or work-areas have ESD signs?
2. All surfaces and objects at all static-safe workstation and within 1 ft measure less than 100V?
3. All ionizer activated, positioned towards the units?
4. Each work surface mats grounding is good?

### Personnel Grounding

1. Every person (including visitors) handling ESD sensitive (ESDS) items wear wrist strap, heel strap or conductive shoes with conductive flooring?
2. If conductive footwear used, conductive flooring also present where operator stand or walk?
3. Garments, hairs or anything closer than 1 ft to ESD items measure less than 100V\*?
4. Every wrist strap or heel strap/conductive shoes checked daily and result recorded for all DSL?
5. All wrist strap or heel strap checkers calibration up to date?

Note: \*50V for Blue LED.

### Device Handling

1. Every ESDS items identified by EIA-471 labels on item or packaging?
2. All ESDS items completely inside properly closed static-shielding containers when not at static-safe workstation?
3. No static charge generators (e.g. plastics) inside shielding containers with ESDS items?
4. All flexible conductive and dissipative package materials inspected before reuse or recycle?

### Others

1. Audit result reported to entity ESD control coordinator?
2. Corrective action from previous audits completed?
3. Are audit records complete and on file?

## 8. Others

The appearance and specifications of the product may be modified for improvement, without prior notice.