

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200670065

Status:

Active

Overview:

Brad Micro-Change (M12) Connectors

Description:

Micro-Change (M12) Double-Ended Cordset, 3 Poles, Female (90°) to Male (Straight) with PNP LED Sensors, 22 AWG, TPE Cable, 1.0m (3.28') Length

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR6837
UL	E152210
General	
Product Family	Industrial Cordsets
Series	120067
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Micro-Change (M12) Connectors
Product Name	Micro-Change (M12)
Protocol	N/A
Region	America
Type	Double Ended
UPC	78678848483
Physical	
Cable Diameter	N/A
Cable Length	1.0m (3.28')
Color - Cable Jacket	Yellow
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	PNP Sensors
Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Orientation	90° to Straight
Poles	3
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	22
Wire/Cable Type	PLTC-ER
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	30V AC/DC
Material Info	
Engineering Number	8830P7K05M010
Reference - Drawing Numbers	
Sales Drawing	SD-120067-024



EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

120067 Series

This document was generated on 01/20/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION