





| LOC | DIST | REVISIONS |     |                           |           |     |      |
|-----|------|-----------|-----|---------------------------|-----------|-----|------|
|     |      | P         | LTR | DESCRIPTION               | DATE      | DWN | APVD |
| FT  | 0    |           | CI  | REVISED PER ECO-12-007964 | 02MAY2012 | KH  | MS   |
|     |      |           |     |                           |           |     |      |
|     |      |           |     |                           |           |     |      |
|     |      |           |     |                           |           |     |      |



- 1 MATERIALS AND FINISH  
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.  
TERMINAL: COPPER ALLOY, TIN PLATED.
- 2 SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.
- 3 RECOGNIZED UNDER THE COMPONENT PROGRAM OF  
UNDERWRITERS LABORATORIES INC. FILE N° E60677.
- 4 IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY  
WITH IEC 998-1/998-2-1.
- 5 NOT CUMULATIVE TOLERANCE.




282826-2 AS SHOWN



|        |    |                        |
|--------|----|------------------------|
| 125    | 13 | 1-282826-3             |
| 115    | 12 | 1-282826-2             |
| 105    | 11 | 1-282826-1             |
| 95     | 10 | 1-282826-0             |
| 85     | 9  | 282826-9               |
| 75     | 8  | 282826-8               |
| 65     | 7  | 282826-7               |
| 55     | 6  | 282826-6               |
| 45     | 5  | 282826-5               |
| 35     | 4  | 282826-4               |
| 25     | 3  | 282826-3               |
| 15     | 2  | 282826-2               |
| DIM. A |    | N° OF POS. PART NUMBER |

RECOMMENDED PC BOARD LAYOUT



|                                                                            |  |                                     |                                                                                                       |              |  |       |
|----------------------------------------------------------------------------|--|-------------------------------------|-------------------------------------------------------------------------------------------------------|--------------|--|-------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                     |  | DWN<br>E. ZANOLINI<br>31 JUL 2001   |  TE Connectivity |              |  |       |
| DIMENSIONS:<br>mm                                                          |  | CHK<br>D. BIEVENOUR<br>31 JUL 2001  |                                                                                                       |              |  |       |
| TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:                                  |  | APVD<br>D. BIEVENOUR<br>31 JUL 2001 | NAME<br>TERMINAL BLOCK HEADER ASSEMBLY<br>180 DEGREE CLOSED ENDS<br>10mm PITCH                        |              |  |       |
| 0 PLC ±.3<br>1 PLC ±.25<br>2 PLC ±.25<br>3 PLC ±.<br>4 PLC ±.<br>ANGLES ±2 |  | PRODUCT SPEC<br>108-20166           | SIZE<br>A3                                                                                            |              |  |       |
| MATERIAL                                                                   |  | APPLICATION SPEC<br>114-20079       | CAGE CODE<br>00779                                                                                    |              |  |       |
| FINISH                                                                     |  | WEIGHT<br>-                         | DRAWING NO<br>C-282826                                                                                |              |  |       |
| CUSTOMER DRAWING                                                           |  | SCALE 3:1                           |                                                                                                       | SHEET 1 OF 1 |  | REV C |