


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



| PANDUIT<br>PART NO.* | BUNDLE DIA.      |                  | A             | B             | C              | D              | E              | F              | G             | H             | MIN. LOOP<br>TENSILE lbs.<br>(N) | CROSS-<br>SECTION | RECM.<br>FAST.    | WEIGHT<br>lbs./100pcs.<br>(g) |
|----------------------|------------------|------------------|---------------|---------------|----------------|----------------|----------------|----------------|---------------|---------------|----------------------------------|-------------------|-------------------|-------------------------------|
|                      | MIN. in.<br>(mm) | MAX. in.<br>(mm) | in.<br>(mm)   | in.<br>(mm)   | in.<br>(mm)    | in.<br>(mm)    | in.<br>(mm)    | in.<br>(mm)    | in.<br>(mm)   |               |                                  |                   |                   |                               |
| SSC2S-S10            | .06<br>(1.5)     | 1.75<br>(44)     | .045<br>(1.1) | .180<br>(4.6) | .310<br>(7.9)  | .772<br>(19.6) | .430<br>(10.9) | 7.35<br>(187)  | .200<br>(5.1) | .075<br>(1.9) | 50 (222)                         | STANDARD          | #10 (M5)<br>SCREW | .3 (136)                      |
| SSC2S-S6             | .06<br>(1.5)     | 1.75<br>(44)     | .045<br>(1.1) | .180<br>(4.6) | .310<br>(7.9)  | .772<br>(19.6) | .430<br>(10.9) | 7.35<br>(187)  | .148<br>(3.8) | .075<br>(1.9) | 50 (222)                         | STANDARD          | #6 (M3)<br>SCREW  | .3 (136)                      |
| SSC4S-S10            | .06<br>(1.5)     | 4.00<br>(102)    | .045<br>(1.1) | .180<br>(4.6) | .310<br>(7.9)  | .772<br>(19.6) | .400<br>(10.2) | 15.67<br>(398) | .200<br>(5.1) | .075<br>(1.9) | 50 (222)                         | STANDARD          | #10 (M5)<br>SCREW | .5 (227)                      |
| SSC4H-S25            | .06<br>(1.5)     | 4.00<br>(102)    | .065<br>(1.7) | .300<br>(7.6) | .460<br>(11.7) | .930<br>(23.6) | .530<br>(13.5) | 15.55<br>(395) | .260<br>(6.6) | .110<br>(2.8) | 120 (534)                        | HEAVY             | 1/4 (M6)<br>SCREW | 1.3 (590)                     |

NOTES:

\*1) SEE [www.panduit.com](http://www.panduit.com) FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL AND PART COLOR.  
2) RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.

W10001EB/21-SS-600

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS.

PANDUIT CORP. TINLEY PARK, ILLINOIS

STA-STRAP CLAMP CABLE TIES  
SSC SERIES

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:  
(.X) ± .0005 (XXX) ± .020(.51)  
(.XX) ± .02(.5) ANGLES ± .0005

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

|                  |                    |
|------------------|--------------------|
| DRAWN BY<br>JABO | DATE<br>11/11/2011 |
|------------------|--------------------|

MAT'L;

|      |        |
|------|--------|
| DATE | 1/8/02 |
|------|--------|

NYLON 6.6

DRAWING NO.

SS - 600

DWG  
A  
SIZE

CHG NOTE 1, "SEE CURRENT PRICE..." TO "SEE [www.panduit.com](http://www.panduit.com)..."

REMOVED PART, SEE ECN FOR DETAILS

SS - 600

21

TGS

|  |  |
|--|--|
|  |  |
|--|--|

1

DATE 1

194

03

1

141

Only

c

c

DRAW

ING NO

1

**DWG**

1