

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

14-60-0133

Status:

Active

Overview:

SL™ Modular Connectors

Description:

2.54mm Pitch SL™ Insulation Displacement Connector Assembly, Female, Single Row, Version A, Non-polarized, Wire Size 26 AWG, 3.81µm Tin/Lead (SnPb), 13 Circuits

Documents:

3D Model

Drawing (PDF)

Product Specification PS-70400 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

UL

LR19980

E29179

General

Product Family

Series

Comments

Component Type

Glow-Wire Compliant

Overview

Product Name

UPC

Ribbon Cable / Wire Trap Connectors

70400

Terminals Preloaded

Housing

No

SL™ Modular Connectors

SL™

800753605282

Physical

Circuits (Loaded)

Color - Resin

Durability (mating cycles max)

Entry Angle

Flammability

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Number of Rows

PCB Retention

Packaging Type

Pitch - Mating Interface

Plating min - Mating

Plating min - Termination

Polarized to Mating Part

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Wire/Cable Type

13

Black

25

Vertical

94V-0

None

Phosphor Bronze

Tin

Tin

Polyester Alloy

1

None

Tube

2.54mm

3.810µm

1.905µm

No

Yes

N/A

-40°C to +105°C

IDT or Pierce

1.35mm max.

26

Discrete Wire, Ribbon Cable

Electrical

Current - Maximum per Contact

Voltage - Maximum

1.8A

250V

Material Info

Old Part Number

A-70400-0187



image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
70400Series

Mates With
Single Row Headers and Housings, [8624](#) ,
[70203](#) , [42375](#) , [42377](#)

Use With
[7307](#) Tinned 28AWG, [7767](#) Topcoat 28AWG, [24241](#) Tinned 26AWG, [8996](#) Topcoat 26AWG, [24226](#) Tinned 24AWG, [8997](#) Topcoat 24AWG, [24369](#) High Flex 26AWG, [24389](#) High Flex 24AWG

Application Tooling | [FAQ](#)
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Hawk™ Ribbon Cable Terminator without Break-off

[0623003000](#)

Reference - Drawing Numbers

Product Specification
Sales Drawing

PS-70400
SDA-70400-0176-0199

Hawk™ Semi-Automatic Discrete Wire Terminator for Rebuilt CE Approved*	0623004900
Hawk™ Flat Flex Cable Terminator with Break-off	0623005200
Hawk™ Ribbon Cable Terminator with Break-off	0623005300
Ribbon Cable Tool Kit, Press Not Included	0622016600
Hawk™ Semi-Automatic Discrete Wire Terminator	0623003100
IDT - Semi-automatic - Bench-Top Terminator	0011200949

This document was generated on 06/27/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[14-60-0133](#)