

SOT23 NPN SILICON PLANAR SMALL SIGNAL TRANSISTORS

ISSUE 2 - JULY 1995




FMMT5209 FMMT5210

PARTMARKING DETAILS:

FMMT5209 - 2Q

FMMT5210 - 2R



SOT23

ABSOLUTE MAXIMUM RATINGS.

PARAMETER	SYMBOL	FMMT5209	FMMT5210	UNIT
Collector-Base Voltage	V_{CBO}	50		V
Collector-Emitter Voltage	V_{CEO}	50		V
Emitter-Base Voltage	V_{EBO}	4.5		V
Continuous Collector Current	I_C	50		mA
Power Dissipation	P_{tot}	330		mW
Operating and Storage Temperature Range	$T_j; T_{stg}$	-55 TO +150		°C

ELECTRICAL CHARACTERISTICS (at $T_{amb} = 25^{\circ}\text{C}$ unless otherwise stated).

PARAMETER	SYMBOL	FMMT5209		FMMT5210		UNIT	CONDITIONS.
		MIN.	MAX.	MIN.	MAX.		
Collector-Base Cut-Off Current	I_{CBO}		50		50	nA	$V_{CB}=35\text{V}, I_E=0$
Emitter-Base Cut-Off Current	I_{EBO}		50		50	nA	$V_{EB}=3\text{V}, I_C=0$
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$		700		700	mV	$I_C=10\text{mA}, I_B=1\text{mA}$
Base-Emitter ON Voltage	$V_{BE(on)}$		850		850	mV	$I_C=1\text{mA}, V_{CE}=5\text{V}$
Static Forward Current Transfer Ratio	h_{FE}	100	300	200	600		$I_C=100\mu\text{A}, V_{CE}=5\text{V}$
		150		250			$I_C=1\text{mA}, V_{CE}=5\text{V}$
		150		250			$I_C=10\text{mA}, V_{CE}=5\text{V}^*$
Transition Frequency	f_T	30		30		MHz	$I_C=0.5\text{mA}, V_{CE}=5\text{V}, f=20\text{MHz}$
Small Signal Current Transfer Ratio	h_{fe}	150	600	250	900	MHz	$I_C=1\text{mA}, V_{CE}=5\text{V}, f=1\text{KHz}$
Noise Figure	N		3		2	dB	$I_C=200\mu\text{A}, V_{CE}=5\text{V}, R_g=2\text{K}\Omega, f=30\text{Hz}$ to 15KHz at -3dB points
			4		3	dB	$I_C=200\mu\text{A}, V_{CE}=5\text{V}, R_g=2\text{K}\Omega, f=1\text{KHz}$ to $\Delta f=200\text{Hz}$
Output Capacitance	C_{obo}		4		4	pF	$V_{CB}=5\text{V}, I_E=0, f=140\text{KHz}$

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Diodes Incorporated:](#)

[FMMT5209TA](#) [FMMT5209TC](#) [FMMT5210TA](#) [FMMT5210TC](#)