






NOTES:

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.

MATERIAL:

- 6 HOUSING: POLYCARBONATE (REF: LEXAN 500)
BUSHING & MTG. HARDWARE: NICKEL PLATED BRASS
SLEEVE & SHUNT TERMINALS: SILVER PLATED COPPER ALLOY
TIP TERMINAL: SILVER PLATED BERYLCO 25

CUSTOMER DRAWING

CAD/CAM DWG. NO.

s.mdpc2ara_cd

SHEET 1 OF 1

☆ STAR SYMBOL DENOTES CRITICAL DIMENSION. SEE S/C ENGINEERING STANDARD ES-0001.					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSE ONLY.				
UNLESS OTHERWISE SPECIFIED					SIZE	WIDTH	MULT	LBS./M	TEMPER
G	ECO #21788	6-24-97	RC	JF	1. ALL DIMENSIONS IN INCHES TWO PLACE DECIMAL ±.01 THREE PLACE DECIMAL ±.005 FRACTIONAL DIMENSIONS ±1/64 ANGLES ±1/2° ALL DIA'S CONCENTRIC WITHIN .005 T.I.R. 2. REMOVE ALL BURRS 3. MAKE NO DIMENSIONAL ALLOWANCES FOR APPLIED FINISHES, I.E., PLATING, PAINTING, ETC. 4. HOLES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±.002				
F	ECO #20627	1-25-96	DEA	TAO	FINISH SPEC. NO. . MATERIAL SPEC. NO. .				
E	ECO #20522	4-4-96	DEA	JF	FIRST USED ON SCALE I = 0.100				
D	ECO #20358	2-11-95	DEA	TAO	DATE DRAWN 6-4-76 BY FGD CHK'D JRH 1-28-77 APP'D LG 1-28-77				
C	ECO #20212	2-11-95	DEA	TAO	NAME MICRO-JACK				
B	REDRAWN ON CAD ECO #20206	2-11-95	DEA	TAO	PART NO. MDPC2ARA				
ISSUE	CHANGE NO.	DATE	BY	APP'D	ISSUE G				
REVISIONS					DO NOT SCALE DRAWING				