







P.C.B. LAYOUT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.

SIGN	DATE	DESCRIPTION	APPROVER
		THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!	

Technical Data:

Material:

- Contacts Pin: Brass with Tin plating
- Wire guard: Stainless steel
- Insulator (housing): Thermoplastic(UL94V-0)

Electrical

- Voltage rating: 250VAC
- Current rating: 12A
- Wire range:
 - Solid wire(AWG): 16-22
 - Stranded wire(AWG): 16-22
- Withstanding Voltage: 1.5KV

Mechanical:

- Temperature Range: -30°C to +105°C
- Soldering temperature: 250°±10° 5 SEC MAX.
- Safety Approval: 

RoHS Compliant

PART NUMBER:

OSTHDX0080

No. of Poles	COLOR
02 2 Poles	0: Black
03 3 Poles	5: Green
:	6: Blue
24 24 Poles	8: Grey (Standard)



TITLE		OSTHD-5.08mm series			
PART NO.	OSTHDX0080	DWG NO.	OSTHDX0080.DWG		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance
Shi Jun 2006.11.01	Marvin 2006.11.01	Marvin 2006.06.22	Marvin 2006.06.22		UNIT: mm SCALE: NONE REV: D
				SHEET: 01/01	X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°