



## 1200 Protector

Sensitive equipment needs protection, and since 1976 the answer has been the Pelican™ Protector Case. These cases are designed rugged, and travel the harshest environments on earth. Against the extreme cold of the arctic or the heat of battle, Pelican cases have survived. Made in the USA, these tough cases are designed with an automatic purge valve, that equalizes air pressure, a watertight silicone O-ring lid, over-molded rubber handles and stainless steel hardware.

- **Watertight, crushproof, and dustproof**
- Automatic Pressure Equalization Valve - balances interior pressure, keeps water out
- Easy open Double Throw latches
- Lifetime Guarantee of Excellence
- O-ring seal
- Open cell core with solid wall design - strong, light weight
- Pick N Pluck™ with convoluted lid foam
- Stainless steel hardware



### CONFIGURATIONS



**1200**  
Standard



**1200NF**  
No Foam



**1200WF**  
With Foam

### DIMENSIONS

<b>Interior (L×W×D)</b>	9.25 x 7.12" x 4.12 (23.5 x 18.1 x 10.5 cm)
<b>Exterior (L×W×D)</b>	10.62 x 9.68" x 4.87 (27 x 24.6 x 12.4 cm)
<b>Lid Depth</b>	1.18" (3 cm)
<b>Bottom Depth</b>	2.93" (7.4 cm)
<b>Total Depth</b>	4.11" (10.4 cm)
<b>Int Volume</b>	0.16 ft <sup>3</sup> (0.005 m <sup>3</sup> )

### MATERIALS

<b>Body</b>	Polypropylene
<b>Latch</b>	ABS
<b>O-Ring</b>	Polymer
<b>Pins</b>	Stainless Steel
<b>Foam</b>	1.3 lb Polyurethane
<b>Purge Body</b>	ABS
<b>Purge Vent</b>	3 Micron Hydrophobic Non-Woven

COLORS

 Black	 Desert Tan	 Orange	 OD Green
 Silver	 Yellow		

WEIGHT

<b>Weight With Foam</b>	2.87 lbs (1.3 kg)
<b>Weight Empty</b>	2.65 lbs (1.2 kg)
<b>Buoyancy</b>	12.02 lbs (5.5 kg)
<b>Master Pack Weight</b>	25.00 lbs (11.3 kg)

TEMPERATURE

<b>Minimum Temperature</b>	-40°F (-40 °C)
<b>Maximum Temperature</b>	210°F (98.9 °C)

CERTIFICATIONS

<b>IP67</b>
<b>Def Stan 81-41</b>
<b>STANAG 4280</b>









FOAM PROPERTIES

<b>Layer 1 (Lid)</b>	1.38" Convolute
<b>Layer 2 (Base)</b>	0.56" Pad
<b>Layer 3 (Base)</b>	2.19" Pick N Pluck

OTHER

<b>Master Pack</b>	6
<b>Military</b>	yes

ACCESSORIES

				
<b>1201</b> 3 pc. Replacement Foam Set	<b>1203</b> Replacement O-ring	<b>1200PF</b> Special Application Panel Frame	<b>1200TPKIT</b> TrekPak Case Divider Kit	<b>1120TPDIV</b> Extra TrekPak Dividers
				
<b>1507</b> Quick Mounts - set of 4	<b>1506TSA</b> TSA Lock	<b>1500D</b> Desiccant Silica Gel		

**Pelican**

23215 Early Ave • Torrance, CA 90505 USA • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311  
[sales@pelican.com](mailto:sales@pelican.com) • [www.pelican.com](http://www.pelican.com)

*Document created on 08-22-20*