

4




3

2

1

LOC	DIST	REVISIONS				
AF	50	P	LTR	DESCRIPTION	DATE	APVD
			E2	REVISED PER ECR-11-025270	20DEC11	KH GJ

- 1
- PRODUCT PROVIDED IN STRIP FORM ON REELS;
BREAKS MAY BE PRESENT
- 2
- REF CRIMPING INFO:
4.57 [.180] CRIMP WIDTH AT CRIMP HEIGHT = (CMA+23,100) /285,700
5.58 [.220] CRIMP WIDTH AT CRIMP HEIGHT = (CMA+24,500) /330,000
- 3
- REF SIMILAR SLICE P/N 1217967-X WITH SERRATIONS
- 4
- LUBRICATION MAY BE REQUIRED TO FACILITATE CRIMPING. A PRODUCT LUBRICANT APPLICATOR IS AVAILABLE FOR TE CONNECTIVITY TERMINATION EQUIPMENT.



TIN	2.5-8.1mm ²	63625-2
-	5,000-16,000 CMA	63625-1
FINISH	WIRE RANGE	PART NO
	4	
DWN P FORTNEY CHK MS FEHER APVD R WEAVILL	10/3/91 10/4/91 10/4/91	TE Connectivity
PRODUCT SPEC		SPLICE
APPLICATION SPEC		
114-2088	SIZE A3	CAGE CODE 00779
WEIGHT -	DRAWING NO C-63625	RESTRICTED TO -
CUSTOMER DRAWING	SCALE 5:1	SHEET 1 OF 1
		REV E2

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [.010] 3 PLC ± - 4 PLC ± - ANGLES ± -
MATERIAL BRASS	FINISH SEE TABLE