







Copyright FCI.


PRODUCT NUMBER SEE SHEET 2




spec ref		*		dr	Xie Bob	2013/06/14	projection		MM		size	A3	scale	3:2
tolerance std	ASME Y14.5	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Xie Bob					2013/06/24	ecn no	-	
					chr	LI- He					2013/06/20			
					appr	Pei-Ming Zheng					2013/06/24			product family
surface	✓	linear	0.X	±0.5		title	24S +8HP+3ACP		dwg no	10106265-B006006		rev	A	
			0.XX	±0.25										
			0.XXX	±0.10										
ASME Y14.5	angular	0°	±2°	www.fci.com	cat. no.		Product - Customer Drw				sheet 1 of 3			

PRODUCT NO.	ROWS	HIGH POWER				HIGH POWER								SIGNAL						E2
		E1	P11	P10	P9	P8	P7	P6	P5	P4	P3	P2	P1	6	5	4	3	2	1	
10106265-B006006LF	D C B A		H7	H7	H7	H7	H7	H7	H7	H7	H7	H7	H7	S	S	S	S	S	S	
			H7	H7	H7	H7	H7	H7	H7	H7	H7	H7	H7	R	R	R	R	R	R	
			H7	H7	H7	H7	H7	H7	H7	H7	H7	H7	H7	P	P	P	P	P	P	
			H7	H7	H7	H7	H7	H7	H7	H7	H7	H7	H7	N	N	N	N	N	N	


CODE	DESCRIPTION
H7	STD HIGH POWER CONTACT(3.02)
HA	METAL HOLD DOWN
N	STD SIGNAL CONTACT, ROW A
P	STD SIGNAL CONTACT, ROW B
R	STD SIGNAL CONTACT, ROW C
S	STD SIGNAL CONTACT, ROW D



dr	Xie Bob	2013/06/14	projection 	MM 	size	A3	scale	3:2
eng	Xie Bob	2013/06/24			ecn no	-		
chr	Li- He	2013/06/20			rel level	Released		
appr	Pei-Ming Zheng	2013/06/24	product family		PwrBlade+			
			title			24S +8HP+3ACP		rev
			RA PF RECEPTACLE					
www.fci.com			cat. no.		Product - Customer Drw			sheet 2 of 3
			dwg no			10106265-B006006		A

NOTES:

- 1) "FCI", PART NUMBER AND DATE CODE TO BE MARKED ON THIS SURFACE.
THE MARK CAN BE OMITTED IF THERE IS NOT ENOUGH SPACE ON THIS SURFACE.
- 2) MATERIALS:
 - HOUSING - GLASS FILLED WITH HIGH TEMP THERMOPLASTIC, UL94V-0.
 - SIGNAL CONTACT - COPPER ALLOY.
 - POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY.
- 3) PLATING SPECIFICATION REFER TO FCI 10116351
- 4) DENOTES CONNECTOR KEEP OUT ZONE.
- 5) DATUM AND BASIC DIMENIONS WERE ESTABLISHED BY CUSTOMER.
- 6) ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES.
- 7) 1.15 ± 0.025 MM DRILLED HOLE PLATED WITH 0.00762MM MIN Sn
OVER 0.0254-0.0762MM Cu PLATING TO ACHIEVE A 1.02 ± 0.07 MM HOLE.
- 8) PRODUCT SPECIFICATION REFER TO FCI GS-12-658.
APPLICATION SPECIFICATION REFER TO FCI GS-20-141.
PRODUCT PACKAGED IN TRAYS, REFER TO FCI GS-14-1502.
- 9) THE VOID CORING IN BETWEEN POWER MODULES, SIGNAL
MODULES AND END MODULES ARE OPTIONAL AND THE SHAPE
MAY BE DIFFERENT FOR OPTIMIZE THE MOLDING PROCESS. THE
VOID CORING WILL NOT EFFECT TO PRODUCT FUNCTION.

dr	Xie Bob	2013/06/14	projection 	MM 	size	scale
eng	Xie Bob	2013/06/24			A3	3:2
chr	Li- He	2013/06/20			ecn no	-
appr	Pei-Ming Zheng	2013/06/24	product family	PwrBlade+	rel level	Released
www.fci.com		title			dwg no	rev
		24S +8HP+3ACP			10106265-B006006	A
		RA PF RECEPTACLE				
cat. no.			Product - Customer Drw			sheet 3 of 3



Copyright FCI.