

8961726 TEXAS INSTR (OPTO)

62C 36768

D


TIP32, TIP32A, TIP32B, TIP32C,
TIP32D, TIP32E, TIP32F
P-N-P SILICON POWER TRANSISTORS

JULY 1968 - REVISED OCTOBER 1984


- Designed for Complementary Use With TIP31 Series
- 40 W at 25°C Case Temperature
- 3 A Continuous Collector Current
- 5 A Peak Collector Current
- Minimum f_T of 3 MHz at 10 V, 0.5 A
- Customer-Specified Selections Available

T-33-19

device schematic



TO-220AB PACKAGE



absolute maximum ratings at 25°C case temperature (unless otherwise noted)

	TIP32	TIP32A	TIP32B	TIP32C
Collector-base voltage	-80 V	-100 V	-120 V	-140 V
Collector-emitter voltage ($I_B = 0$)	-40 V	-60 V	-80 V	-100 V
Emitter-base voltage	-5 V			
Continuous collector current	-3 A			
Peak collector current (see Note 1)	-5 A			
Continuous base current	-1 A			
Safe operating areas at 25°C case temperature	See Figure 4			
Continuous device dissipation at 25°C case temperature (see Note 2)	40 W			
Continuous device dissipation at (or below) 25°C free-air temperature (see Note 3)	2 W			
Unclamped inductive load energy (see Note 4)	32 mJ			
Operating collector junction and storage temperature range	-65°C to 150°C			
Lead temperature 3,2 mm (0.125 inch) from case for 10 seconds	250°C			

- NOTES: 1. This value applies for $t_W \leq 0.3$ ms, duty cycle $\leq 10\%$.
 2. Derate linearly to 150°C case temperature at the rate of 0.32 W/°C.
 3. Derate linearly to 150°C free-air temperature at the rate of 16 mW/°C.
 4. This rating is based on the capability of the transistor to operate safely in the circuit of Figure 2.



TIP Devices

8961726 TEXAS INSTR (OPTO)

62C 36769 D

TIP32, TIP32A, TIP32B, TIP32C,
TIP32D, TIP32E, TIP32F
P-N-P SILICON POWER TRANSISTORS

T-33-19

absolute maximum ratings at 25°C case temperature (unless otherwise noted)

	TIP32D	TIP32E	TIP32F
Collector-base voltage	-160 V	-180 V	-200 V
Collector-emitter voltage ($I_B = 0$)	-120 V	-140 V	-160 V
Emitter-base voltage	-5 V		
Continuous collector current	-3 A		
Peak collector current (see Note 1)	-5 A		
Continuous base current	-1 A		
Safe operating area at 25°C case temperature	See Figure 4		
Continuous device dissipation at 25°C case temperature (see Note 2)	40 W		
Continuous device dissipation at (or below) 25°C free-air temperature (see Note 3)	2 W		
Unclamped inductive load energy (see Note 4)	32 mJ		
Operating collector junction and storage temperature range	-65°C to 150°C		
Lead temperature 3,2 mm (0.125 inch) from case for 10 seconds	250°C		

- NOTES: 1. This value applies for $t_W \leq 0.3$ ms, duty cycle $\leq 10\%$.
2. Derate linearly to 150°C case temperature at the rate of 0.32 W/°C.
3. Derate linearly to 150°C free-air temperature at the rate of 16 mW/°C.
4. This rating is based on the capability of the transistor to operate safely in the circuit in Figure 2.

electrical characteristics at 25°C case temperature (unless otherwise noted)

PARAMETER	TEST CONDITIONS	TIP32			TIP32A			TIP32B			TIP32C			UNIT
		MIN	TYP	MAX	MIN	TYP	MAX	MIN	TYP	MAX	MIN	TYP	MAX	
$V_{(BR)CEO}$	$I_C = -30$ mA, $I_B = 0$, See Note 5	-40			-60			-80			-100			V
I_{CEO}	$V_{CE} = -30$ V, $I_B = 0$ $V_{CE} = -60$ V, $I_B = 0$	-0.3			-0.3			-0.3			-0.3			mA
I_{CES}	$V_{CE} = -80$ V, $V_{BE} = 0$	-0.2												mA
	$V_{CE} = -100$ V, $V_{BE} = 0$				-0.2									
	$V_{CE} = -120$ V, $V_{BE} = 0$							-0.2						
	$V_{CE} = -140$ V, $V_{BE} = 0$										-0.2			
I_{EBO}	$V_{EB} = -5$ V, $I_C = 0$	-1			-1			-1			-1			mA
h_{FE}	$V_{CE} = -4$ V, $I_C = -1$ A, See Notes 5 and 6	25			25			25			25			
	$V_{CE} = -4$ V, $I_C = -3$ A, See Notes 5 and 6	10	50		10	50		10	50		10	50		
V_{BE}	$V_{CE} = -4$ V, $I_C = -3$ A, See Notes 5 and 6	-1.8			-1.8			-1.8			-1.8			V
$V_{CE(sat)}$	$I_B = -0.375$ A, $I_C = -3$ A, See Notes 5 and 6	-1.2			-1.2			-1.2			-1.2			V
h_{fe}	$V_{CE} = -10$ V, $I_C = -0.5$ A, $f = 1$ MHz	20			20			20			20			
$ h_{fe} $	$V_{CE} = -10$ V, $I_C = -0.5$ A, $f = 1$ MHz	3			3			3			3			

- NOTES: 5. These parameters must be measured using pulse techniques, $t_W = 300$ μ s, duty cycle $\leq 2\%$.
6. These parameters are measured with voltage-sensing contacts separate from the current-carrying contacts.

TIP Devices

8961726 TEXAS INSTR (OPTO)

62C 36770

D

TIP32, TIP32A, TIP32B, TIP32C,
TIP32D, TIP32E, TIP32F
P-N-P SILICON POWER TRANSISTORS

electrical characteristics at 25°C case temperature (unless otherwise noted)

7-33-19

PARAMETER	TEST CONDITIONS	TIP32D	TIP32E	TIP32F	UNIT
		MIN TYP MAX	MIN TYP MAX	MIN TYP MAX	
$V_{(BR)CEO}$	$I_C = -30 \text{ mA}$, See Note 5 $I_B = 0$	-120	-140	-160	V
I_{CEO}	$V_{CE} = -90 \text{ V}$, $I_B = 0$	-0.3	-0.3	-0.3	mA
I_{CES}	$V_{CE} = -160 \text{ V}$, $V_{BE} = 0$	-0.2			mA
	$V_{CE} = -180 \text{ V}$, $V_{BE} = 0$		-0.2		
	$V_{CE} = -200 \text{ V}$, $V_{BE} = 0$			-0.2	
I_{EBO}	$V_{EB} = -5 \text{ V}$, $I_C = 0$	-1	-1	-1	mA
h_{FE}	$V_{CE} = -4 \text{ V}$, See Notes 5 and 6 $I_C = -1 \text{ A}$	25	25	25	
	$V_{CE} = -4 \text{ V}$, See Notes 5 and 6 $I_C = -3 \text{ A}$	5	5	5	
V_{BE}	$V_{CE} = -4 \text{ V}$, See Notes 5 and 6 $I_C = -3 \text{ A}$	-1.8	-1.8	-1.8	V
$V_{CE(sat)}$	$I_B = -750 \text{ mA}$, See Notes 5 and 6 $I_C = -3 \text{ A}$	-2.5	-2.5	-2.5	V
h_{fe}	$V_{CE} = -10 \text{ V}$, $f = 1 \text{ MHz}$ $I_C = -0.5 \text{ A}$	20	20	20	
$ h_{fe} $	$V_{CE} = -10 \text{ V}$, $f = 1 \text{ MHz}$ $I_C = -0.5 \text{ A}$	3	3	3	

NOTES: 5. These parameters must be measured using pulse techniques, $t_W = 300 \mu\text{s}$, duty cycle $\leq 2\%$.
6. These parameters are measured with voltage-sensing contacts separate from the current-carrying contacts.

thermal characteristics

PARAMETER	MIN TYP MAX	UNIT
$R_{\theta JC}$	3.126	°C/W
$R_{\theta JA}$	62.5	

resistive-load switching characteristic at 25°C case temperature (unless otherwise noted)

PARAMETER	TEST CONDITIONS†	MIN TYP MAX	UNIT
t_{on}	$I_C = -1 \text{ A}$, $I_{B1} = -0.1 \text{ A}$, $I_{B2} = 0.1 \text{ A}$	0.3	μs
t_{off}	$V_{BE(off)} = 4.3 \text{ V}$, $R_L = 30 \Omega$, See Figure 1	1	

† Voltage and current values shown are nominal; exact values vary slightly with transistor parameters.

TIP Devices


8961726 TEXAS INSTR (OPTO)

62C 36771 D


T-33-19

TIP32, TIP32A, TIP32B, TIP32C,
TIP32D, TIP32E, TIP32F
P-N-P SILICON POWER TRANSISTORS

PARAMETER MEASUREMENT INFORMATION



TEST CIRCUIT



VOLTAGE WAVEFORMS

- NOTES:
- V_{gen} is a 30-V pulse into a 50 Ω termination.
 - The V_{gen} waveform is supplied by the following characteristics: $t_r \leq 15$ ns, $t_f \leq 15$ ns, $Z_{out} = 50 \Omega$, $t_w = 20 \mu$ s, duty cycle $\leq 2\%$.
 - Waveforms are monitored on an oscilloscope with the following characteristics: $t_r \leq 15$ ns, $R_{in} \geq 10$ M Ω , $C_{in} \leq 11.5$ pF.
 - Resistors must be noninductive types.
 - The d-c power supplies may require additional bypassing in order to minimize ringing.

FIGURE 1. RESISTIVE-LOAD SWITCHING

TIP Devices


8961726 TEXAS INSTR (OPTO)

62C 36772 D


TIP32, TIP32A, TIP32B, TIP32C,
TIP32D, TIP32E, TIP32F
P-N-P SILICON POWER TRANSISTORS

PARAMETER MEASUREMENT INFORMATION

T-33-19



TEST CIRCUIT



VOLTAGE AND CURRENT WAVEFORMS

NOTES: A. L1 and L2 are 10 mH, 0.11 Ω , Chicago Standard Transformer Corporation C-2688, or equivalent.
B. Input pulse duration is increased until $I_{CM} = -1.8$ A.

FIGURE 2. INDUCTIVE-LOAD SWITCHING



TIP Devices

8961726 TEXAS INSTR (OPTO)

62C 36773 D

T-33-19

TIP32, TIP32A, TIP32B, TIP32C,
TIP32D, TIP32E, TIP32F
P-N-P SILICON POWER TRANSISTORS

TYPICAL CHARACTERISTICS

STATIC FORWARD CURRENT TRANSFER RATIO
vs
COLLECTOR CURRENT




FIGURE 3

NOTES: 5. These parameters must be measured using pulse techniques, $t_W = 300 \mu s$, duty cycle $\leq 2\%$.

6. These parameters are measured with voltage-sensing contacts separate from the current-carrying contacts.

MAXIMUM SAFE OPERATING AREA

FORWARD-BIAS SAFE OPERATING AREA




FIGURE 4

NOTE 7: This combination of maximum voltage and current may be achieved only when switching from saturation to cutoff with a clamped inductive load.

TIP Devices

8961726 TEXAS INSTR (OPTO)

62C 36774 D

TIP32, TIP32A, TIP32B, TIP32C,
TIP32D, TIP32E, TIP32F
P-N-P SILICON POWER TRANSISTORS

THERMAL INFORMATION

T-33-19




FIGURE 5



TIP Devices