

Technical drawings of a mechanical part, including a side view, a top view, and an isometric view.

Side View (Top Left): Shows a vertical flange with a horizontal slot. The width of the flange is 1.025. The central hole has a diameter of .12 DIA.

Top View (Bottom Left): Shows a rectangular base with a central slot. The width of the base is 1.620. The central hole has a diameter of .31 DIA.

Top View (Bottom Right): Shows a rectangular base with a central slot. The width of the base is 1.825. The central slot has a width of .600 ± .005. The depth of the slot is .250.

Isometric View (Top Right): Shows the 3D shape of the part, including the flange and the central slot.

										CAD FILENAME/LAYERS		1006190C_C10083_PSL_00.prt		
										PANDUIT CORP. TINLEY PARK, ILLINOIS				
										PSL-P PLUG LOCKOUT CUSTOMER DRAWING				
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .1 (.XX) ± .005 (.XX) ± .015 ANGLES ± 1°		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.		
										DRAWN BY RVU	MAT'L;		SCALE NTS	
R	10-8-03	RVU		DRAWING RELEASE		2965	R			DATE 10-8-03	RED POLYCARBONATE		DRAWING NO. C10083	DWG A SIZE
REV	DATE	BY	CHK	DESCRIPTION		ECN	- R	CUST	SUP	CHK'D				