


## Lead (Pb)-Bearing Thick Film, Rectangular High Value Chip Resistor



### FEATURES

**HALOGEN  
FREE**

- High resistance values (up to 470M)
- Suitable for voltage dividers and hybrids
- Lead (Pb)-bearing termination plating on Ni barrier layer
- Metal glaze on high quality ceramic
- Material categorization: For definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)

### STANDARD ELECTRICAL SPECIFICATIONS

MODEL	CASE SIZE INCH	CASE SIZE METRIC	POWER RATING $P_{70}$ W	LIMITING ELEMENT VOLTAGE $U_{max. AC_{RMS}/DC}$ V	TEMPERATURE COEFFICIENT ppm/K	TOLERANCE %	RESISTANCE RANGE $\Omega$	SERIES
D11/CRCW0603-HR	0603	RR 1608M	0.10	75	$\pm 500$	$\pm 5$	11M to 470M	E24
D12/CRCW0805-HR	0805	RR 2012M	0.125	150	$\pm 500$	$\pm 5$	11M to 470M	E24
D25/CRCW1206-HR	1206	RR 3216M	0.25	200	$\pm 500$	$\pm 5$	11M to 470M	E24

#### Notes

- These resistors do not feature a limited lifetime when operated within the limits of rated dissipation, permissible operating voltage, and permissible film temperature. However, the resistance typically increase due to the resistor's film temperature over operating time, generally known as drift. The drift may exceed the stability requirements of an individual application circuit and thereby limits the functional time.
- Marking and packaging: See datasheet "Surface Mount Resistor Marking" ([www.vishay.com/doc?20020](http://www.vishay.com/doc?20020))
- Power rating depends on the max. temperature at the solder point, the component placement density and the substrate material.

### TECHNICAL SPECIFICATIONS


PARAMETER	UNIT	D11/CRCW0603-HR	D12/CRCW0805-HR	D25/CRCW1206-HR
Rated Dissipation at $P_{70}$ <sup>(1)</sup>	W	0.1	0.125	0.25
Operating Voltage $U_{max. AC_{RMS}/DC}$	V	75	150	200
Voltage Coefficient	%/V		< 100M: < 0.1 > 100M: < 0.3	
Insulation Voltage $U_{ins}$ (1 min)	V	100	200	300
Insulation Resistance	$\Omega$		$> 10^9$	
Operating Temperature Range	$^{\circ}C$		- 55 to + 155	
Weight	mg	2	5.5	10

#### Note

<sup>(1)</sup> The power dissipation on the resistor generates a temperature rise against the local ambient, depending on the heat flow support of the printed-circuit board (thermal resistance). The rated dissipation applies only if the permitted film temperature of 155 °C is not exceeded.

## PART NUMBER AND PRODUCT DESCRIPTION

Part Number: CRCW060316M0JPTBHR



MODEL/SIZE	RESISTANCE	TOLERANCE	TCR	PACKAGING	SPECIAL
CRCW0603	M = Million	J = $\pm 5\%$	P = $\pm 500 \text{ ppm/K}$	TA, TB	Up to 2 digits
CRCW0805				TC	HR = High value
CRCW1206					


Product Description: CRCW0603-HR 500 16M 5% RT5

CRCW0603-HR	500	16M	J	RT5
MODEL	TCR	RESISTANCE	TOLERANCE	PACKAGING
CRCW0603-HR	$\pm 500 \text{ ppm/K}$	68M = 68 M $\Omega$ 220M = 220 M $\Omega$	$\pm 5\%$	RT1, RT5 RT6
CRCW0805-HR				
CRCW1206-HR				


## PACKAGING

MODEL	CODE	QUANTITY	CARRIER TAPE	WIDTH	PITCH	REEL DIAMETER
CRCW0603-HR	TA = RT1	5000	Paper tape acc. to IEC 60068-3 Type I	8 mm	4 mm	180 mm/7"
	TB = RT5	10 000				285 mm/11.25"
	TC = RT6	20 000				330 mm/13"
CRCW0805-HR	TA = RT1	5000		8 mm	4 mm	180 mm/7"
	TB = RT5	10 000				285 mm/11.25"
	TC = RT6	20 000				330 mm/13"
CRCW1206-HR	TA = RT1	5000		8 mm	4 mm	180 mm/7"
	TB = RT5	10 000				285 mm/11.25"
	TC = RT6	20 000				330 mm/13"

## DIMENSIONS



SIZE		DIMENSIONS in millimeters					SOLDER PAD DIMENSIONS in millimeters					
							REFLOW SOLDERING			WAVE SOLDERING		
INCH	METRIC	L	W	H	T1	T2	a	b	I	a	b	I
0603	1608	1.55 <sup>+ 0.10</sup> <sub>- 0.05</sub>	0.85 $\pm 0.1$	0.45 $\pm 0.05$	0.3 $\pm 0.2$	0.3 $\pm 0.2$	0.5	0.9	1.0	0.9	0.9	1.0
0805	2012	2.0 <sup>+ 0.20</sup> <sub>- 0.10</sub>	1.25 $\pm 0.15$	0.45 $\pm 0.05$	0.3 <sup>+ 0.20</sup> <sub>- 0.10</sub>	0.3 $\pm 0.2$	0.7	1.3	1.2	0.9	1.3	1.3
1206	3216	3.2 <sup>+ 0.10</sup> <sub>- 0.20</sub>	1.6 $\pm 0.15$	0.55 $\pm 0.05$	0.45 $\pm 0.2$	0.4 $\pm 0.2$	0.9	1.7	2.0	1.1	1.7	2.3

**DERATING**

**TEST PROCEDURES AND REQUIREMENTS**

EN 60115-1 CLAUSE	IEC 60068-2 TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE ( $\Delta R$ )
				STABILITY CLASS 2 OR BETTER
Stability for product types:			<b>D/CRCW-HR</b>	11 MΩ to 470 MΩ
4.5	–	Resistance		± 5 %
4.13	–	Short time overload	$U = 2.5 \times \sqrt{P_{70} \times R} \leq 2 \times U_{\max.}$ Duration acc. to style	± (0.5 % $R + 0.05 \Omega$ )
4.17.2	58 (Td)	Solderability	Solder bath method; Sn60Pb40	Good tinning ( $\geq 95\%$ covered); no visible damage
4.8.4.2	–	Temperature coefficient	20 °C/- 55 °C/20 °C and 20 °C/125 °C/20 °C	± 500 ppm/K
4.32	21 (Uu <sub>3</sub> )	Shear (adhesion)	RR 1608: 9 N RR 2012 and RR 3216: 45 N	No visible damage
4.33	21 (Uu <sub>1</sub> )	Substrate bending	Depth 2 mm; 3 times	No visible damage, no open circuit in bent position ± (0.25 % $R + 0.05 \Omega$ )
4.19	14 (Na)	Rapid change of temperature	30 min. at - 55 °C; 30 min. at 125 °C 5 cycles 1000 cycles	± (0.5 % $R + 0.05 \Omega$ ) ± (1 % $R + 0.05 \Omega$ )
4.23 4.23.2 4.23.3	2 (Ba) 30 (Db)	Climatic sequence: Dry Heat Damp heat, cyclic	– 125 °C; 16 h 55 °C; $\geq 90\%$ RH; 24 h; 1 cycle	± (2 % $R + 0.1 \Omega$ )
4.23.4 4.23.5 4.23.6	1 (Aa) 13 (M) 30 (Db)	Cold Low air pressure	– - 55 °C; 2 h 1 kPa; (25 ± 10) °C; 1 h	
4.23.7	–	Damp heat, cyclic	55 °C; $\geq 90\%$ RH 24 h; 5 cycle	
		D.C. Load	$U = \sqrt{P_{70} \times R} \leq U_{\max.}$	
4.25.1	–	Endurance at 70 °C	1.5 h on; 0.5 h off; 70 °C; 1000 h 70 °C; 8000 h	± (2 % $R + 0.1 \Omega$ ) ± (4 % $R + 0.1 \Omega$ )

**TEST PROCEDURES AND REQUIREMENTS**

EN 60115-1 CLAUSE	IEC 60068-2 TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE ( $\Delta R$ )		
				STABILITY CLASS 2 OR BETTER		
			Stability for product types:	11 M $\Omega$ to 470 M $\Omega$		
			<b>D/CRCW-HR</b>			
4.18.2	58 (Td)	Resistance to soldering heat	Solder bath method (260 $\pm$ 5) °C; (10 $\pm$ 1) s	$\pm$ (0.5 % $R$ + 0.05 $\Omega$ )		
4.24	78 (Cab)	Damp heat, steady state	(40 $\pm$ 2) °C; (93 $\pm$ 3) % RH; 56 days	$\pm$ (2 % $R$ + 0.1 $\Omega$ )		
4.25.3	–	Endurance at upper category temperature	155 °C; 1000 h	$\pm$ (2 % $R$ + 0.1 $\Omega$ )		

All tests are carried out in accordance with the following specifications:

- EN 60115-1, generic specification
- EN 140400, sectional specification
- EN 140401-802, detail specification
- IEC 60068-2-x, variety of environmental test procedures

Packaging of components is done in paper or blister tapes according to IEC 60286-3.

## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

## Material Category Policy

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.**

**Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.**

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay](#):

[CRCW0805100M](#)