

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

.19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

CE

16

P

LTR

DESCRIPTION

DATE

DWN

APVD


F

REVISE PER 0A00-0370-99

20APR99


CK

NM



1. DIMENSIONS IN [] ARE IN INCHES.

6.1±0.08 [240±3]	1-504972-2
100±1.0 [3937±39]	1-504972-1
70±0.70 [2756±28]	1-504972-0
60±0.60 [2362±24]	504972-9
50±0.50 [1969±20]	504972-8
20±0.3 [787±12]	504972-7
15±0.15 [591±6]	504972-6
10±0.15 [394±6]	504972-5
5±0.08 [197±3]	504972-4
3±0.05 [118±2]	504972-3
2±0.05 [79±2]	504972-2
1±0.05 [39±2]	504972-1
L	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.URICH 20APR99	AMP AMP Incorporated Harrisburg, PA 17105-3608	
		CHK R.PAUL 23APR96		
DIMENSIONS: METERS ■ [INCHES]		APVD N.MILLER 24APR96	NAME CABLE ASSY, FIBER OPTIC, 62.5/125µm LDS,ds, AMP SC (NG) TO 2.5mm OVERMOLDED CERAMIC BAYONET, OPTIMATE	
		PRODUCT SPEC —	SIZE A3	
		APPLICATION SPEC —	CAGE CODE 00779	
MATERIAL —		WEIGHT —	DRAWING NO C=504972	
FINISH —		CUSTOMER DRAWING		RESTRICTED TO —
		SCALE NTS	SHEET 1 OF 1	REV F