

TLRE53T, TLRME53T, TLSE53T, TLOE53T, TLYE53T, TLPYE53T, TLGE53T, TLFGE53T, TLPGE53T


Panel Circuit Indicators

- $\phi 3$ mm package
- InGaA/P technology
- All plastic mold
- Transparent lens
- Line-up: 6 colors (red, orange, yellow, pure yellow, green and pure green)
- High intensity light emission
- Excellent low current light output
- Applications: message boards, security devices and dashboard displays

Line-up

Product Name	Color	Material
TLRE53T	Red	InGaA/P
TLRME53T	Red	
TLSE53T	Red	
TLOE53T	Orange	
TLYE53T	Yellow	
TLPYE53T	Pure Yellow	
TLGE53T	Green	
TLFGE53T	Green	
TLPGE53T	Pure Green	

Unit: mm



Weight: 0.14 g

Maximum Ratings (Ta = 25°C)

Product Name	Forward Current I _F (mA)	Reverse Voltage V _R (V)	Power Dissipation P _D (mW)	Operating Temperature T _{opr} (°C)	Storage Temperature T _{stg} (°C)
TLRE53T	50	4	120	-40~100	-40~120
TLRME53T	50	4	120		
TLSE53T	50	4	120		
TLOE53T	50	4	120		
TLYE53T	50	4	120		
TLPYE53T	50	4	120		
TLGE53T	50	4	120		
TLFGE53T	50	4	120		
TLPGE53T	50	4	120		

Electrical and Optical Characteristics (Ta = 25°C)







Product Name	Typ. Emission Wavelength				Luminous Intensity I _V			Forward Voltage V _F			Reverse Current I _R	
	λ _d	λ _p	Δλ	I _F	Min	Typ.	I _F	Typ.	Max	I _F	Max	V _R
TLRE53T	630	(644)	20	20	153	400	20	1.9	2.4	20	50	4
TLRME53T	626	(636)	23	20	272	600	20	1.9	2.4	20	50	4
TLSE53T	613	(623)	20	20	272	800	20	1.9	2.4	20	50	4
TLOE53T	605	(612)	20	20	272	1000	20	2.0	2.4	20	50	4
TLYE53T	587	(590)	17	20	272	800	20	2.0	2.4	20	50	4
TLPYE53T	580	(583)	14	20	153	450	20	2.0	2.4	20	50	4
TLGE53T	571	(574)	17	20	153	400	20	2.0	2.4	20	50	4
TLFGE53T	565	(568)	15	20	85	200	20	2.0	2.4	20	50	4
TLPGE53T	558	(562)	14	20	47.6	130	20	2.1	2.4	20	50	4
Unit	nm			mA	mcd		mA	V		mA	μA	V

Precautions







Please be careful of the following:

- Soldering temperature: 260°C max, soldering time: 3 s max
(soldering portion of lead: up to 2 mm from the body of the device)
- If the lead is formed, the lead should be formed up to 5 mm from the body of the device without forming stress to the resin. Soldering should be performed after lead forming.
- This visible LED lamp also emits some IR light.
If a photodetector is located near the LED lamp, please ensure that it will not be affected by this IR light.







TLRE53T









TLRME53T









TLSE53T









TLOE53T









TLYE53T









TLPYE53T









TLGE53T



TLFGE53T



TLPGE53T



RESTRICTIONS ON PRODUCT USE

000707EAC

- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property.
In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc..
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.
- Gallium arsenide (GaAs) is a substance used in the products described in this document. GaAs dust and fumes are toxic. Do not break, cut or pulverize the product, or use chemicals to dissolve them. When disposing of the products, follow the appropriate regulations. Do not dispose of the products with other industrial waste or with domestic garbage.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA CORPORATION for any infringements of intellectual property or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any intellectual property or other rights of TOSHIBA CORPORATION or others.
- The information contained herein is subject to change without notice.